



201 Series Water Valves (Nylon 6)



GC Valves 201 Series water valves are an excellent choice for potable water applications where supply pressure can drop to zero, such as emptying a tank. These valves are certified to NSF/ANSI 61 and have Nylon 6 bodies and NSF approved EPDM diaphragms. Ported for 3/8, 1/2 or 3/4 inch NPT, valves are available with either 120VAC, 24VAC or 24VDC solenoids.

Features

- 2-Ports (2-way), 2-position
- Normally closed (N.C.) configuration
- Piloted diaphragm operator
- Zero differential action
- 18mm (DIN 43650A) style wiring plug
- 3/8", 1/2" or 3/4" NPT ports
- 120VAC, 24VAC or 24VDC solenoids
- Made in the USA



Also, see our website
www.AutomationDirect.com
 for a variety of fitting options



Made
in the
USA

201 Series Water Valve								
Model	NS201YF02CPCG4	NS201YF02CPEG5	NS201YF24CPCG4	NS201YF24CPDG4	NS201YF24CPEG5	NS201YF16CPCG4	NS201YF16CPDG4	NS201YF16CPEG5
Price	\$180.00	\$181.00	\$180.00	\$180.00	\$181.00	\$180.00	\$180.00	\$181.00
Drawing Link	PDF	PDF	PDF	PDF	PDF	PDF	PDF	PDF
Weight (lbs)	1.0	1.1	1.0	1.0	1.1	1.0	1.0	1.1
Valve Type	2-Ports (2-way), 2-position							
Acting	Piloted diaphragm, normally closed							
Port Size	1/2" FNPT	3/4" FNPT	3/8" FNPT	1/2" FNPT	3/4" FNPT	3/8" FNPT	1/2" FNPT	3/4" FNPT
Orifice Size	5/8"	3/4"	5/8"	5/8"	3/4"	5/8"	5/8"	3/4"
Cv	4.3	6.7	4.3	4.3	6.7	4.3	4.3	6.7
Media	Water							
Pressure Range	0-100 psi	0-100 psi	0-100 psi	0-100 psi	0-100 psi	0-90 psi	0-90 psi	0-90 psi
Voltage (± 10%)	120/110 VAC 50/60 Hz	120/110 VAC 50/60 Hz	24VAC 50/60 Hz	24VAC 50/60 Hz	24VAC 50/60 Hz	24VDC	24VDC	24VDC
Inrush AC	54VA					-		
Power Consumption	10W							
Max Cycles per Minute**	15							
Insulation	Class N (200°C - 392°F)							
Min Response	25-100 ms					38-150 ms		
Temperature	32°F to 125°F (0°C to 51.7°C); Max. Fluid Temp. 295°F (146.1°C)							
Lubrication	Not required							
Protection	NEMA 4/4X Encapsulated							
Connection	18mm (DIN 43650A) terminal							
Construction	Nylon 6 plastic body; NSF Approved EPDM seals; Stainless Steel pilot orifice							
Life Cycle	1 Million							
Agency Approvals*	NSF/ANSI - 61-G/NSF-372, CE, CSA, UL Recognized							

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

** Cannot be used in PWM (pulse width modulation) applications



201 Series Water Valves (Stainless Steel)



GC Valves 201 Series water valves are an excellent choice for potable water applications where supply pressure can drop to zero, such as emptying a tank. These valves are certified to NSF/ANSI 61 and have 316 stainless steel bodies and NSF approved EPDM diaphragms. Ported for 1/2, 3/4, 1, 1-1/4 or 1-1/2 inch NPT, valves are available with either 120VAC, 24VAC or 24VDC solenoids.

Features

- 2-Ports (2-way), 2-position
- Normally closed (N.C.) configuration
- Piloted diaphragm operator
- Zero differential action
- 18mm (DIN 43650A) style wiring plug
- 1/2", 3/4", 1", 1-1/4" or 1-1/2" NPT ports
- 120VAC, 24VAC or 24VDC solenoids
- Made in the USA



Made
in the
USA

Also, see our website
www.AutomationDirect.com
for a variety of fitting options

201 Series Water Valves							
Model	NS201YF02C7DG4	NS201YF02C7EG5	NS201YF02C7EG9	NS201YF02C7GJ2	NS201YF02C7HJ2	NS201YF24C7DG4	NS201YF24C7EG5
Price	\$426.00	\$457.00	\$576.00	\$687.00	\$704.00	\$426.00	\$458.00
Drawing Link	PDF	PDF	PDF	PDF	PDF	PDF	PDF
Weight (lbs)	1.9	2.0	4.0	6.5	6.3	1.9	2.0
Valve Type	2-Ports (2-way), 2-position						
Acting	Piloted diaphragm, normally closed						
Port Size	1/2" FNPT	3/4" FNPT	1" FNPT	1-1/4" FNPT	1-1/2" FNPT	1/2" FNPT	3/4" FNPT
Orifice Size	5/8"	3/4"	1"	1-1/4"	1-1/4"	5/8"	3/4"
Cv	4.3	6.7	11.0	18.0	23.0	4.3	6.7
Media	Water						
Pressure Range	0-100 psi	0-100 psi	0-100 psi	0-100 psi	0-100 psi	0-100 psi	0-100 psi
Voltage (± 10%)	120/110 VAC 50/60 Hz	120/110 VAC 50/60 Hz	120/110 VAC 50/60 Hz	120/110 VAC 50/60 Hz	120/110 VAC 50/60 Hz	24VAC 50/60 Hz	24VAC 50/60 Hz
Inrush AC	54VA						
Power Consumption	10W						
Max Cycles per Minute**	15						
Insulation	Class N (200°C - 392°F)						
Min Response	25-100 ms						
Temperature	32°F to 125°F (0°C to 51.7°C); Max. Fluid Temp. 295°F (146.1°C)						
Lubrication	Not required						
Protection	NEMA 4/4X Encapsulated						
Connection	18mm (DIN 43650A) terminal						
Construction	316 Stainless steel body; NSF Approved EPDM seals; Stainless Steel orifice						
Life Cycle	1 Million						
Agency Approvals	NSF/ANSI - 61-G/NSF-372, CE, CSA, UL Recognized						

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

** Cannot be used in PWM (pulse width modulation) applications



201 Series Water Valves (Stainless Steel) Cont.





201 Series Water Valves Cont.					
Model	NS201YF16C7DG4	NS201YF16C7EG5	NS201YF16C7FG9	NS201YF16C7GJ2	NS201YF16C7HJ2
Price	\$426.00	\$457.00	\$578.00	\$688.00	\$705.00
Drawing Link	PDF	PDF	PDF	PDF	PDF
Weight (lbs)	1.9	2.0	4.0	6.5	6.3
Valve Type	2-Ports (2-way), 2-position				
Acting	Piloted diaphragm, normally closed				
Port Size	1/2" FNPT	3/4" FNPT	1" FNPT	1-1/4" FNPT	1-1/2" FNPT
Orifice Size	5/8"	3/4"	1"	1-1/4"	1-1/4"
Cv	4.3	6.7	11.0	18.0	23.0
Media	Water				
Pressure Range	0-90 psi	0-90 psi	0-100 psi	0-100 psi	0-100 psi
Voltage (± 10%)	24VDC	24VDC	24VDC	24VDC	24VDC
Inrush AC	-				
Power Consumption	10W				
Max Cycles per Minute**	15				
Insulation	Class N (200°C - 392°F)				
Min Response	38-150 ms				
Temperature	32°F to 125°F (0°C to 51.7°C); Max. Fluid Temp. 295°F (146.1°C)				
Lubrication	Not required				
Protection	NEMA 4/4X Encapsulated				
Connection	18mm (DIN 43650A) terminal				
Construction	316 Stainless steel body; NSF Approved EPDM seals; Stainless Steel orifice				
Life Cycle	1 Million				
Agency Approvals	NSF/ANSI - 61-G/NSF-372, CE, CSA, UL Recognized				

* To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

** Cannot be used in PWM (pulse width modulation) applications







201 Series Water Valve Accessories

201 Series Water Valve Accessories				
<i>Kit Photo</i>	<i>Part No.</i>	<i>Description</i>	<i>Price</i>	<i>Weight (lbs)</i>
	<u>KS201AF02G4-NSF</u>	GC Valves rebuild kit, for use with NS201 series AC valves ending CG4 and DG4, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, connecting spring, body o-ring and operator o-ring.	\$89.00	0.4
	<u>KS201AF15G4-NSF</u>	GC Valves rebuild kit, for use with NS201 series DC valves ending CG4 and DG4, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, connecting spring, body o-ring and operator o-ring.	\$89.00	0.4
	<u>KS201AF02G5-NSF</u>	GC Valves rebuild kit, for use with NS201 series AC valves ending EG5, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, connecting spring, body o-ring and operator o-ring.	\$89.00	0.4
	<u>KS201AF15G5-NSF</u>	GC Valves rebuild kit, for use with NS201 series DC valves ending EG5, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, connecting spring, body o-ring and operator o-ring.	\$89.00	0.4

















201 Series Water Valve Accessories

201 Series Water Valve Accessories				
Kit Photo	Part No.	Description	Price	Weight (lbs)
	<u>KS201AF02G9-NSF</u>	GC Valves rebuild kit, for use with NS201 series AC valves ending G9, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, plunger connecting spring, body O-rings and operator O-ring.	\$145.00	0.4
	<u>KS201AF02J2-NSF</u>	GC Valves rebuild kit, for use with NS201 series AC valves ending J2, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, plunger connecting spring, body O-rings and operator O-ring.	\$146.00	0.4
	<u>KS201AF15G9-NSF</u>	GC Valves rebuild kit, for use with NS201 series DC valves ending G9, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, plunger connecting spring, body O-rings and operator O-ring.	\$145.00	0.4
	<u>KS201AF15J2-NSF</u>	GC Valves rebuild kit, for use with NS201 series DC valves ending J2, includes diaphragm assembly, plunger assembly, plunger tube, plunger spring, plunger connecting spring, body O-rings and operator O-ring.	\$146.00	0.4



GCV Valves Replacement Coils

Water Valve Accessory Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS4YN02</u>	120VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN04</u>	240VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN24</u>	24VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN16</u>	24VDC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN02A24</u>	120VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN04A24</u>	240VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN24A24</u>	24VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN16A24</u>	24VDC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves	\$49.00	0.6
	<u>HS3YN02</u>	120VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3YN04</u>	240VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3YN24</u>	24VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN02A24</u>	120VAC	88W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN04A24</u>	240VAC	8W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN24A24</u>	24VAC	8W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5