

Interrupt Input Module

Interrupt Input Module


D4-INT \$94.50



Overview

The D4-INT is an 8-point interrupt module. This module is intended for applications that have a high-priority event that requires special operations to be performed. When this high priority event occurs, the interrupt module senses a DC level input signal. The module automatically informs the CPU to interrupt its present operation. The CPU immediately suspends its routine scan cycle and jumps to a subroutine identified with that particular interrupt input signal point. The CPU then executes the logic in the subroutine (subroutines can even use immediate I/O instructions to immediately read and write I/O points if a time-critical update is necessary). When the subroutine is complete, the CPU automatically resumes its routine scan cycle starting at the exact location where it was interrupted. The CPU continues the routine scan until another interrupt signal is sensed.

Module Specifications	
Modules per CPU	1 for D4-430, 2 for D4-440, D4-450, and D4-454 (modules must be in 1st then 2nd slot of the CPU base)
Input Points	8 (requires 16 points from I/O)
Input Voltage Range	10.20-26.4VDC
Maximum Input Current	10.0mA
Impedance	~ 2.7K Ω
Input Current	4.4mA at 12VDC, 9.0 mA at 24VDC
ON Level Voltage	9.5VDC
OFF Level Voltage	3.0VDC
Maximum OFF Current	1.5mA
Minimum ON Current	4.0mA
OFF to ON Response	0.08 - 0.59ms or 0.88 - 6.47ms
ON to OFF Response	0.15 - 0.89ms or 1.64 - 9.81ms
Terminal Type	Removable connector
Operating Environment	0°C to 60°C (32°F to 140°F), 5% to 95% humidity (non-condensing)
Internal Power Consumption	100mA max
Manufacturer	Koyo Electronics



Hardware features

The D4-INT is designed to accept eight input signals. These inputs are labeled 0 through 7. If multiple inputs are received at the same time, they are prioritized by their respective label number, 0 being first and 7 being last.

Input points not used as interrupt points can be used as normal DC input points. This is accomplished with an 8-bit dipswitch located on the back of the module.

Interrupt signals can be triggered with a rising or falling edge signal. This is selectable via a dipswitch.

Two ranges of input filtering for response times are available via a dipswitch.

Check the Power Budget

Verify your power budget requirements

Your I/O configuration choice can be affected by the power requirements of the I/O modules you choose. When determining the types and quantity of I/O modules you will be using, it is important to remember there is a limited amount of power available from the power supply.

The chart on the opposite page indicates the power supplied and used by each DL405 device. The adjacent chart shows an example of how to calculate the power used by your particular system. These two charts should make it easy for you to determine if the devices you have chosen fit within the power budget of your system configuration.

If the I/O you have chosen exceeds the maximum power available from the power supply, you can resolve the problem by shifting some of the modules to an expansion base or remote I/O base (if you are using remote I/O).

Warning: It is extremely important to calculate the power budget correctly. If you exceed the power budget, the system may operate in an unpredictable manner which may result in a risk of personal injury or equipment damage.

Use ZIPLinks to reduce power requirements

If your application requires a lot of relay outputs, consider using the ZipLink AC or DC relay output modules. These modules can switch high current (10A) loads without putting a load on your base power budget. Refer to Wiring System for DL405 PLCs later in this section for more information.

This logo is placed next to I/O modules that are supported by the ZIPLink connection systems.

See the I/O module specifications at the end of this section.



Calculating your power usage

The following example shows how to calculate the power budget for the DL405 system. The example is constructed around a single 8-slot base using the devices shown. It is recommended you construct a similar table for each base in your system.

A			
Base Number	Device Type	5 VDC (mA)	External 24 VDC Power (mA)
0			
B CURRENT SUPPLIED			
CPU/Expansion Unit /Remote Slave	D4-440 CPU	3700	400
C CURRENT REQUIRED			
SLOT 0	D4-16ND2	+150	+0
SLOT 1	D4-16ND2	+150	+0
SLOT 2	F4-04DA	+120	+100
SLOT 3	D4-08ND3S	+100	+0
SLOT 4	D4-08ND3S	+100	+0
SLOT 5	D4-16TD2	+100	+0
SLOT 6	D4-16TD2	+100	+0
SLOT 7	D4-16TR	+1000	+0
D OTHER			
BASE	D4-08B-1	+80	+0
Handheld Programmer	D4-HPP-1	+320	+0
E Maximum Current Required		2820	100
F Remaining Current Available		3700-2820=880	400-100=300
1. Using a chart similar to the one above, fill in column 2. 2. Using the tables on the opposite page, enter the current supplied and used by each device (columns 3 and 4). Pay special attention to the current supplied by the CPU, Expansion Unit, and Remote Slave since they differ. Devices which fall into the "Other" category (Row D) are devices such as the Base and the Handheld programmer, which also have power requirements, but do not plug directly into the base. 3. Add the current used by the system devices (columns 3 and 4) starting with Slot 0 and put the total in the row labeled "maximum current required" (Row E). 4. Subtract the row labeled "Maximum current required" (Row E), from the row labeled "Current Supplied" (Row B). Place the difference in the row labeled "Remaining Current Available" (Row F). 5. If "Maximum Current Required" is greater than "Current Supplied" in either column 3 or 4, the power budget will be exceeded. It will be unsafe to use this configuration and you will need to restructure your I/O configuration. Note the auxiliary 24 VDC power supply does not need to supply all the external power. If you need more than the 400mA supplied, you can add an external 24VDC power supply. This will help keep you within your power budget for external power.			

DL405 CPU power supply specifications and power requirements

Specification	AC Powered Units	24 VDC Powered Units	125 VDC Powered Units
Part Numbers	D4-454, D4-450, D4-440, D4-430, D4-EX (expansion base unit), D4-RS (remote slave unit)	D4-454DC-1, D4-450DC-1, D4-440DC-1, D4-EXDC (expansion base unit), D4-RSDC (remote slave unit)	D4-450DC-2
Voltage Withstand (dielectric)	1 minute @ 1,500 VAC between primary, secondary, field ground, and run relay		
Insulation Resistance	> 10MΩ at 500VDC		
Input Voltage Range	85-132 VAC (110 range) 170-264 VAC (220 range)	20-28 VDC (24 VDC) with less than 10% ripple	90-146 VDC (125 VDC) with less than 10% ripple
Maximum Inrush Current	20 A	20 A	20 A
Maximum Power	50 VA	38 W	30 W

Power Requirements

Power Supplied					
<i>CPUs/Remote Units/ Expansion Units</i>	<i>5 VDC Current Supplied in mA</i>	<i>24V Aux Power Supplied in mA</i>	<i>CPUs/Remote Units/ Expansion Units</i>	<i>5V Current Supplied in mA</i>	<i>24V Aux Power Supplied in mA</i>
D4-430 CPU	3700	400	D4-EX	4000	400
D4-440 CPU	3700	400	D4-EXDC	4000	NONE
D4-440DC-1 CPU	3700	NONE	D4-RS	3700	400
D4-450 CPU	3700	400	D4-RSDC	3700	NONE
D4-454 CPU	3100	400	H4-EBC	3470	400
D4-450DC-1 CPU	3100	NONE	H4-EBC-F	3300	400
D4-450DC-2 CPU	3100	NONE			
D4-454DC-1	3100	NONE			
Power Consumed					
<i>Power-consuming Device</i>	<i>5V Current Consumed</i>	<i>External 24VDC Current Required</i>	<i>Power-consuming Device</i>	<i>5V Current Consumed</i>	<i>External 24VDC Current Required</i>
<i>I/O Bases</i>			<i>Analog Modules (continued)</i>		
D4-04B-1	80	NONE	F4-16AD-1	75	100
D4-06B-1	80	NONE	F4-16AD-2	75	100
D4-08B-1	80	NONE	F4-04DA-1	70	75+20per circuit
			F4-04DA-2	90	90
			F4-04DAS-1	60	60 per circuit
			F4-04DAS-2	60	60 per circuit
			F4-08DA-1	90	100+20 per circuit
			F4-08DA-2	80	150
D4-08ND3S	100	NONE	F4-16DA-1	90	100+20 per circuit
D4-16ND2	150	NONE	F4-16DA-2	80	25 max.
D4-16ND2F	150	NONE	F4-08RTD	80	NONE
D4-32ND3-1	150	NONE	F4-08THM-n	120	50
D4-64ND2	300 max.	NONE	F4-08THM	110	60
<i>DC Input Modules</i>			<i>Remote I/O</i>		
			H4-ERM100	320(300)	NONE
			H4-ERM-F	450	NONE
			D4-RM	300	NONE
<i>AC Input Modules</i>			<i>Communications and Networking</i>		
D4-08NA	100	NONE	H4-ECOM100	300	NONE
D4-16NA	150	NONE	H4-ECOM-F	670	NONE
			D4-DCM	500	NONE
			F4-MAS-MB	235	NONE
			FA-UNICON	NONE	65
<i>AC/DC Input Modules</i>			<i>CoProcessors</i>		
D4-16NE3	150	NONE	F4-CP128-1	305	NONE
F4-08NE3S	90	NONE	F4-CP128-T	350	NONE
<i>DC Output Modules</i>			<i>Specialty Modules</i>		
F4-08TD1S	295	NONE	H4-CTRIO	400	NONE
D4-16TD1	200	125	D4-INT	100	NONE
D4-16TD2	400	NONE	D4-HSC	300	NONE
D4-32TD1	250	140	F4-16PID	160	NONE
D4-32TD1-1	250	140 (15V)	F4-8MPI	225	170
D4-32TD2	350	120 (4A max including loads)	D4-16SIM	150	NONE
D4-64TD1	800	NONE	F4-4LTC	280	75
<i>AC Output Modules</i>			<i>Programming</i>		
D4-08TA	250	NONE	D4-HPP-1 (Handheld Prog.)	320	NONE
D4-16TA	450	NONE			
<i>Relay Output Modules</i>			<i>Operator Interface</i>		
D4-08TR	550	NONE	DV-1000	150	NONE
F4-08TRS-1	575	NONE			
F4-08TRS-2	575	NONE	C-more Micro-Graphic	210	NONE
D4-16TR	1000	NONE			
<i>Analog Modules</i>					
F4-04AD	150	100			
F4-04ADS	370	120			
F4-08AD	75	90			