


DINnectors® Accessories

Steel DIN Rails Features



35mm wide

- Available in 1-meter lengths
- 7.5 mm-high rails primarily used to mount terminal blocks, relays, timers and small PLCs such as the DL05, DL06, DL105, DL205, CLICK, and Productivity3000
- 15mm-high rails for mounting larger and heavier components such as contactors and larger PLCs

15mm wide

- Available in 1-meter lengths
- DN-R15S1 exclusively for mounting mini terminal blocks such as the DN-M10-A

	Part Number	Pcs/Pkg	Price/Pkg	Part#	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35S1	10	\$28.00	DN-R35HS1	10	\$50.00	DN-R15S1	10	\$26.00
	DN-R35S1-2	2	\$9.25	DN-R35HS1-2	2	\$12.50	DN-R15S1-2	2	\$8.25
Steel DINnectors Accessories Specifications									
Description	Steel, slotted, 3'3" [1m] length, 35mm [1.38 in] wide, 7.5 mm [0.30 in] high			Steel, slotted, 3'3" [1m] length, 35mm [1.38 in] wide, 15mm [0.59 in] high			Steel, slotted, 3'3" [1m] length, 15mm [0.59 in] wide, 5.5 mm [0.22 in] high		
Plating	Zinc-plated and chromated								
International Standards	EN60715. RoHS								
Suggested Mounting Screw Type	M6			M6			M4		

Aluminum DIN Rail Features



35mm wide

- Non-anodized finish
- Zinc plating and passivation (minimum thickness 6 microns)
- Lightweight, easy to cut and deburr
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in 1-meter lengths




35mm wide raised

- Non-anodized finish
- Zinc plating and passivation (minimum thickness 6 microns)
- Enables users to raise terminal blocks 2¼" above the back panel
- Terminal blocks only
- Available in 1-meter lengths
- Bushing or grommet recommended for wire access hole (example Heyco UB-875 not sold by ADC)


	Part Number	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35SAL1	10	\$38.50	DN-R35SAL2-2	2	\$25.00
	DN-R35SAL1-2	2	\$8.25			
Aluminum DIN Rail Specifications						
Description	Aluminum, slotted, 3'3" [1m] length, 35mm [1.38 in] wide, 10mm [0.39 in] high			Aluminum, slotted, 3'3" [1m] length, 35mm [1.38 in] wide, 58mm [2.28 in] high		
Plating	Galvanic zinc plating, non-anodized finish					
International Standards	DIN 50960, RoHS					
Suggested Mounting Screw Type	#10-32 or M5					

DINnectors[®] Accessories




Dimensions mm [inches]



**DN-R35SAL1
DN-R35SAL1-2**



DN-R35SAL2-2



DINnectors Accessories

DIN rail support brackets

- Angled support brackets raise and tilt mounting rails 30 degrees from mounting surface for easier wiring
- DN-ASB1 plated steel support bracket
- DN-ASB2-10 cold-rolled steel treated with galvanic zinc plating and passivation

DIN rail mounting clips

- Snap small devices not made for mounting onto 35mm DIN rails
- Zinc plated steel

DIN Rail Support Brackets and Mounting Clips			
Part Number	Description	Pcs/Pkg	Price Each
DN-ASB1	30° angled DIN rail support bracket (M6-1.0 screws not included)	50	\$50.00
DN-ASB2-10	30° angled DIN rail support bracket (M6-1.0 screws included)	10	\$13.50
DN-SSB25-10	1" [25mm] DIN rail support bracket (M6-1.0 screws included)	10	\$18.50
DN-SSB50-10	2" [50mm] DIN rail support bracket (M6-1.0 screws included)	10	\$19.50
DN-SSB70-10	2.75" [70mm] DIN rail support bracket (M6-1.0 screws included)	10	\$24.50
DN-SSB90-10	3.5" [90mm] DIN rail support bracket (M6-1.0 screws included)	10	\$25.00
DN-CLIP-FM4	DIN rail mounting clip with M4 x 0.7 mm threaded hole (Screws not included)	40	\$47.50
DN-CLIP-FM4-5		5	\$7.25
DN-CLIP-FM5	DIN rail mounting clip with M5 x 0.8 mm threaded hole (Screws not included)	40	\$52.00
DN-CLIP-FM5-5		5	\$7.25



DN-ASB1



DN-ASB2-10



DN-SSB25-10



DN-SSB50-10



DN-SSB70-10



DN-SSB90-10



DN-CLIP-FM4
DN-CLIP-FM4-5






DN-CLIP-FM5
DN-CLIP-FM5-5

DINnectors® Accessories

DIN Rail Support Brackets and Mounting Clips

Dimensions mm [inches]



DIN Rail Support Brackets		
Part Number	DIM A mm [inches]	DIM B mm [inches]
DN-SSB25-10	15.0 [0.59]	25.0 [0.98]
DN-SSB50-10	40.0 [1.58]	50.0 [1.97]
DN-SSB70-10	60.0 [2.36]	70.0 [2.76]
DN-SSB90-10	80.0 [3.15]	90.0 [3.54]

