


DIN Rail and Accessories

Steel DIN Rails Features



35 mm wide

- Available in 1-meter lengths
- 7.5 mm-high rails primarily used to mount terminal blocks, relays, timers and small PLCs such as the DL05, DL06, DL105, DL205, CLICK, Do-more, and Productivity3000
- 15 mm-high rails for mounting larger and heavier components such as contactors and larger PLCs

15 mm wide

- Available in 1-meter lengths
- DN-R15S1 exclusively for mounting mini terminal blocks.

	Part Number	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35S1	10	\$28.00	DN-R35HS1	10	\$49.50	DN-R15S1	10	\$26.00
	DN-R35S1-2	2	\$9.00	DN-R35HS1-2	2	\$12.00	DN-R15S1-2	2	\$8.00
Steel DIN Rails Specifications									
Description	Steel, slotted, 3'3" (1 m) length, 35 mm (1.38 in) wide, 7.5 mm (0.30 in) high			Steel, slotted, 3'3" (1 m) length, 35 mm (1.38 in) wide, 15 mm (0.59 in) high			Steel, slotted, 3'3" (1 m) length, 15 mm (0.59 in) wide, 5.5 mm (0.22 in) high		
Plating	Zinc-plated and chromated								
International Standards	EN 60715, RoHs								
Suggested Mounting Screw Type	M6			M6			M4		

Aluminum DIN Rails Features



35 mm wide

- Non-anodized finish
- Galvanic zinc plating and passivation (minimum thickness 6 microns)
- Lightweight, easy to cut and deburr
- Terminal blocks only
- Maximum mounting screw #10-32 or M5
- Available in 1-meter lengths

35 mm wide raised

- Non-anodized finish
- Galvanic zinc plating and passivation (minimum thickness 6 microns)
- Enables users to raise terminal blocks 2¼" above the back panel
- Terminal blocks only
- Available in 1-meter lengths
- Bushing or grommet recommended for wire access hole


(example Heyco UB-875 not sold by ADC)

	Part Number	Pcs/Pkg	Price/Pkg	Part Number	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35SAL1	10	\$36.00	DN-R35SAL2-2	2	\$24.25
	DN-R35SAL1-2	2	\$8.00			
Aluminum DIN Rails Specifications						
Description	Aluminum, slotted, 3'3" (1 m) length, 35 mm (1.38 in) wide, 10 mm (0.39 in) high			Aluminum, slotted, 3'3" (1 m) length, 35 mm (1.38 in) wide, 58 mm (2.28 in) high		
Plating	Galvanic zinc plating, non-anodized finish					
International Standards	DIN 50960, RoHs					
Suggested Mounting Screw Type	#10-32 or M5					


DIN Rail and Accessories

Dimensions mm [inches]


DN-R35S1




DN-R35HS1




DN-R15S1





**DN-R35SAL1
DN-R35SAL1-2**



DN-R35SAL2-2



**VIEW A-A
ROTATED 90°**



DIN Rail and Accessories

DIN rail support brackets

- Angled support brackets raise and tilt mounting rails 30 degrees from mounting surface for easier wiring
- DN-ASB1 plated steel support bracket
- DN-ASB2-10 cold-rolled steel treated with galvanic zinc plating and passivation

DIN rail mounting clips

- Snap small devices not made for mounting onto 35mm DIN rails
- Zinc plated steel


DIN Rail Support Brackets and Mounting Clips			
Part Number	Description	Pcs/Pkg	Price Each
DN-ASB1	30° angled DIN rail support bracket (M6-1.0 screws not included)	50	\$49.50
DN-ASB2-10	30° angled DIN rail support bracket (M6-1.0 screws included)	10	\$12.00
DN-SSB25-10	1" (25 mm) DIN rail support bracket (M6-1.0 screws included)	10	\$17.00
DN-SSB50-10	2" (50 mm) DIN rail support bracket (M6-1.0 screws included)	10	\$18.25
DN-SSB70-10	2.75" (70 mm) DIN rail support bracket (M6-1.0 screws included)	10	\$23.00
DN-SSB90-10	3.5" (90 mm) DIN rail support bracket (M6-1.0 screws included)	10	\$24.25
DN-CLIP-FM4	DIN rail mounting clip with M4 x 0.7 mm threaded hole (Screws not included)	40	\$45.00
DN-CLIP-FM4-5		5	\$6.25
DN-CLIP-FM5	DIN rail mounting clip with M5 x 0.8 mm threaded hole (Screws not included)	40	\$49.50
DN-CLIP-FM5-5		5	\$7.00



DN-ASB1



DN-ASB2-10



DN-SSB25-10



DN-SSB50-10



DN-SSB70-10



DN-SSB90-10






**DN-CLIP-FM4
DN-CLIP-FM4-5**



**DN-CLIP-FM5
DN-CLIP-FM5-5**

DIN Rail and Accessories

Dimensions mm [inches]



DIN Rail Support Brackets		
Part Number	DIM A mm [inches]	DIM B mm [inches]
DN-SSB25-10	15.0 [0.59]	25.0 [0.98]
DN-SSB50-10	40.0 [1.58]	50.0 [1.97]
DN-SSB70-10	60.0 [2.36]	70.0 [2.76]
DN-SSB90-10	80.0 [3.15]	90.0 [3.54]

