


NEMA 3R, 4, 4X, 12, & 13 Stainless Steel Double-Door Freestanding Disconnect with Slope Top



Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

Construction

- Formed 12-gauge 304 stainless steel.
- Flange trough collar (FTC) around door opening excludes liquids and contaminants.
- Heavy-duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with bullet-style, heavy duty, lift off hinges.
- Formed 10-gauge steel inner panel is provided on collar studs.
- Panel supports are provided.
- Center post is removable, providing easy panel installation.
- Heavy-duty three-point latching mechanism with heavy-duty roller ends is provided for ease of door closing.
- Seamless poured-in place gasket.
- Right hand master door handle complete with screwdriver defeater and padlock hasp.
- Additional door handle complete with padlock hasp.
- A mechanical interlock activated by the master door prevents the auxiliary door from being opened first.
- The pre-installed flange cutout provides mounting for disconnect operators (verify compatibility in advance) - interlock hardware included with enclosure.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

Listings

- UL 508A Type 3R, 4X, & 12 [File E65324]
- CSA Type 3R, 4, 4X and 12 [File LR21001]
- Complies with:
 - NEMA Type 3R, 4X, 12, & 13
 - IEC 60529, IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 3R, 4, 4X, 12, & 13 Stainless Steel Double-Door Freestanding Disconnect with Slope Top

304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Drawing Link
2STFSD747512SS	\$12,928.00	2STFSD747512S16	\$15,466.00	78.54 x 75.13 x 13.38 [1995 x 1908 x 340]	PDF
2STFSD747518SS	\$14,095.00	2STFSD747518S16	\$16,870.00	80.72 x 75.13 x 19.38 [2050 x 1908 x 492]	PDF
2STFSD747524SS	\$15,190.00	2STFSD747524S16	\$18,186.00	82.91 x 75.13 x 25.38 [2106 x 1908 x 645]	PDF

Note: Dimensions in inches [millimeters].