

# Instruction Set

## Boolean Instructions

- Store (STR)**  
Begins a new rung or an additional branch in a rung with a normally open contact.
- Store Not (STR NOT)**  
Begins a new rung or an additional branch in a rung with a normally closed contact.
- Or (OR)**  
Logically ors a normally open contact in parallel with another contact in a rung.
- Or Not (OR NOT)**  
Logically ors a normally closed contact in parallel with another contact in a rung.
- And (AND)**  
Logically ands a normally open contact in series with another contact in a rung.
- And Not (AND NOT)**  
Logically ands a normally closed contact in series with another contact in a rung.
- And Store (AND STR)**  
Logically ands two branches of a rung in series.
- Or Store (OR STR)**  
Logically ors two branches of a rung in parallel.
- Out (OUT)**  
Reflects the status of the rung (on/off) and outputs the discrete (on/off) state to the specified image register point or memory location.
- Or Out (OR OUT)**  
Reflects the status of the rung and outputs the discrete (ON/OFF) state to the image register. Multiple OR OUT instructions referencing the same discrete point can be used in the program.
- Not (NOT)**  
Inverts the status of the rung at the point of the instruction.
- Set (SET)**  
An output that turns on a point or a range of points. The reset instruction is used to turn the point(s) OFF that were set ON with the set instructions.
- Reset (RST)**  
An output that resets a point(s).
- Pause outputs (PAUSE)**  
Disables the update for a range of specified output points.

## Comparative Boolean Instructions

- Store if Equal (STR E)**  
Begins a new rung or additional branch in a rung with a normally open comparative contact. The contact will be on when A=B.
- Store if Not Equal (STR NOT E)**  
Begins a new rung or additional branch in a rung with a normally closed comparative contact. The contact will be on when A is not equal to B.
- Or if Equal (OR E)**  
Connects a normally open comparative contact in parallel with another contact. The contact will be on when A=B.
- Or if Not Equal (OR NOT E)**  
Connects a normally closed comparative contact in parallel with another contact. The contact will be on when A is not equal to B.
- And if Equal (AND E)**  
Connects a normally open comparative contact in series with another contact. The contact will be on when A=B.
- And if Not Equal (AND NOT E)**  
Connects a normally closed comparative contact in series with another contact. The contact will be on when A is not equal to B.
- Store (STR)**  
Begins a new rung or additional branch in a rung with a normally open comparative contact. The contact will be on when A ≥ B.
- Store Not (STR NOT)**  
Begins a new rung or additional branch in a rung with a normally closed comparative contact. The contact will be on when A < B.
- Or (OR)**  
Connects a normally open comparative contact in parallel with another contact. The contact will be on when A ≥ B.
- Or Not (OR NOT)**  
Connects a normally open comparative contact in parallel with another contact. The contact will be on when A < B.
- And (AND)**  
Connects a normally open comparative contact in series with another contact. The contact will be on when A ≥ B.
- And Not (AND NOT)**  
Connects a normally open comparative contact in series with another contact. The contact will be on when A < B.

## Bit of Word Boolean Instructions

- Store Bit of Word (STRB)**  
D4-450 & D4-454 Only Begins a new rung or an additional branch in a rung with a normally open contact that examines a single bit of a V-memory location.
- Store Not Bit of Word (STRNB)**  
D4-450 & D4-454 Only Begins a new rung or an additional branch in a rung with a normally closed contact that examines a single bit of a V-memory location.
- Or Bit of Word (ORB)**  
D4-450 & D4-454 Only Logically ors a normally open bit of word contact in parallel with another contact in a rung.
- Or Not Bit of Word (ORNb)**  
D4-450 & D4-454 Only Logically ors a normally closed bit of word contact in parallel with another contact in a rung.
- And Bit of Word (ANDB)**  
D4-450 & D4-454 Only Logically ands a normally open bit of word contact in series with another contact in a rung.
- And Not Bit of Word (ANDNB)**  
D4-450 & D4-454 Only Logically ands a normally closed bit of word contact in series with another contact in a rung.
- Out Bit of Word (OUTB)**  
D4-450 & D4-454 Only Reflects the status of the rung (on/off) and outputs the discrete (on/off) state to the specified bit of a

V-memory location.

- Set Bit of Word (SETB)**  
D4-450 & D4-454 Only An output that turns on a single bit of a V-memory location. The bit remains on until it is reset. The reset bit of word instruction is used to turn off the bit.
- Reset Bit of Word (RSTB)**  
D4-450 & D4-454 Only An output that resets a single bit of a V-memory location.

## Differential Instructions

- Positive differential (PD)**  
One-shot output coil. When the input logic produces an off to on transition, the output will energize for one CPU scan.
- Store Positive Differential (STRD)**  
D4-450 & D4-454 Only Leading edge triggered one-shot contact. When the corresponding memory location transitions from low to high, the contact comes on for one CPU scan.
- Store Negative Differential (STRND)**  
D4-450 & D4-454 Only Trailing edge triggered one-shot contact. When the corresponding memory location transitions from high to low, the contact comes on for one CPU scan.
- Or Positive Differential (ORD)**  
D4-450 & D4-454 Only Logically ors a leading edge triggered one-shot contact in parallel with another contact in a rung.
- Or Negative Differential (ORNND)**  
D4-450 & D4-454 Only Logically ors a trailing edge triggered one-shot contact in parallel with another contact in a rung.
- And Positive Differential (ANDD)**  
D4-450 & D4-454 Only Logically ands a leading edge triggered one-shot contact in series with another contact in a rung.
- And Negative Differential (ANDND)**  
D4-450 & D4-454 Only Logically ands a trailing edge triggered one-shot contact in series with another contact in a rung.

## Immediate Instructions

- Store immediate (STR I)**  
Begins a rung/branch of logic with a normally open contact. The contact will be updated with the current input field status when processed in the program scan.
- Store Not Immediate (STR NOT I)**  
Begins a rung/branch of logic with a normally closed contact. The contact will be updated with the current input field status when processed in the program scan.
- Or Immediate (OR I)**  
Connects a normally open contact in parallel with another contact. The contact will be updated with the current input field status when processed in the program scan.
- Or Not Immediate (OR NOT I)**  
Connects a normally closed contact in parallel with another contact. The contact will be updated with the current input field status when processed in the program scan.
- And Immediate (AND I)**  
Connects a normally open contact in series with another contact. The contact will be updated with the current input field status when processed in the program scan.
- And Not Immediate (AND NOT I)**  
Connects a normally closed contact in series with another contact. The contact will be updated with the current input field status when processed in the program scan.
- Out Immediate (OUT I)**  
Reflects the status of the rung. The output field device status is updated when the instruction is processed in the program scan.
- Or Out Immediate (OR OUT I)**  
Reflects the status of the rung and outputs the discrete (ON/OFF) state to the image register. Multiple OR OUT instructions referencing the same discrete point can be used in the program. The output field device status is updated when the instruction is processed in the program scan.
- Set Immediate (SET I)**  
An output that turns on a point or a range of points. The reset instruction is used to turn the point(s) off that were set. The output field device status is updated when the instruction is processed in the program scan.
- Reset Immediate (RST I)**  
An output that resets a point or a range of points. The output field device status is updated when the instruction is processed in the program scan.
- Load Immediate (LDI)**  
D4-450 & D4-454 Only Loads the accumulator with the contents of a specified 16-bit V-memory location. The status for each bit of the specified V-memory location is loaded into the accumulator. Typically used for input module V-memory addresses. Allows you to specify the V location instead of the X location and the number of points as with the LDIF.

- Load immediate Formatted (LDIF)**  
D4-440, D4-450, and D4-454 Only Loads the accumulator with a specified number of consecutive inputs. The field device status for the specified inputs points is loaded into the accumulator when the instruction is executed.
- Out Immediate (OUT I)**  
D4-450 & D4-454 Only Outputs the contents of the accumulator to a specified V-memory location. The status for each bit of the specified V-memory location will reflect the status of the lower 16 bits of the accumulator. Typically used for output module V-memory addresses. Allows you to specify the V location instead of the Y location and the number of points as with the OUTIF.
- Out immediate Formatted (OUTIF)**  
D4-440, D4-450 & D4-454 Only Outputs the contents of the accumulator to a specified number of consecutive outputs. The output field devices are updated when the instruction is processed by the program scan.

## Timer, Counter, and Shift Register Instructions

- Timer (TMR)**  
Single input incrementing timer with 0.1 second resolution (0-9999.99 sec.).
- Fast Timer (TMRF)**  
Single input incrementing timer with 0.01 second resolution (0-99.99 seconds).
- Accumulating Timer (TMRA)**  
Two input incrementing timer with 0.1 second resolution (0-9999.99 sec.). Time and enable/reset inputs control the timer.
- Accumulating Fast Timer (TMRAF)**  
Two input incrementing timer with 0.01 second resolution (0-9999.99 sec.). Time input and enable/reset input control timer.
- Counter (CNT)**  
Two input incrementing counter (0-9999). Count and reset inputs control the counter.
- Stage Counter (SGCNT)**  
Single input incrementing counter (0-9999). RST instruction must be used to reset count.
- Up Down Counter (UDC)**  
Three input counter (0-99999999). Up, down, and reset inputs control the counter.
- Shift Register (SR)**  
Shifts data through a range of control relays with each clock pulse. The data, clock, and reset inputs control the shift register.

## Accumulator/Data Stack Load and Output

- Load (LD)**  
Loads a 16 bit word into the lower 16 bits of the accumulator/stack.
- Load Double (LDD)**  
Loads a 32 bit word into the accumulator/stack.
- Load Real Number (LDR)**  
D4-450 & D4-454 Only Loads a real number contained in two consecutive V-memory locations or an 8-digit constant into the accumulator.
- Load Formatted (LDF)**  
D4-440, D4-450 & D4-454 Only Loads the accumulator with a specified number of consecutive discrete memory bits.
- Load Address (LDA)**  
Loads the accumulator with the HEX value for an octal constant (address).
- Load Accumulator indexed (LDX)**  
Loads the accumulator with a V memory address to be offset by the value in the accumulator stack.
- Load Accumulator indexed from Data Constants (LDSX)**  
D4-440, D4-450 & D4-454 Only Loads the accumulator with an offset constant value (ACON/NCON) from a data label area (DLBL).
- Out (OUT)**  
Copies the value in the lower 16 bits of the accumulator to a specified V memory location.
- Out Double (OUTD)**  
Copies the value in the accumulator to two consecutive V memory locations.
- Out Formatted (OUTF)**  
D4-440, D4-450 & D4-454 Only Outputs a specified number of bits (1-32) from the accumulator to the specified discrete memory locations.
- Out Least (OUTL)**  
D4-450 & D4-454 Only Copies the value in the lower 8 bits of the accumulator to the lower 8 bits of a specified V memory location.
- Out Most (OUTM)**  
D4-450 & D4-454 Only Copies the value in the upper 8 bits of the lower accumulator word (16 bits) to the upper 8 bits of a specified V memory location.
- Output indexed (OUTX)**  
Copies a 16 bit value from the first level of the accumulator stack to a source address offset by the value in the accumulator.
- Pop (POP)**  
Moves the value from the first level of the accumulator stack to the accumulator and shifts each value in the stack up one level.

# Instruction Set

## Accumulator Logic Instructions

**And (AND)**  
Logically ands the lower 16 bits in the accumulator with a V memory location.

**And Double (ANDD)**  
Logically ands the value in the accumulator with two consecutive V memory locations.

**And Formatted (ANDF)**  
D4-440, D4-450 & D4-454 Only Logically ands the value in the accumulator and a specified range of discrete memory bits (1-32).

**And with Stack (ANDS)**  
D4-440, D4-450 & D4-454 Only Logically ands the value in the accumulator with the first value in the accumulator stack.

**Or (OR)**  
Logically ors the lower 16 bits in the accumulator with a V memory location.

**Or Double (ORD)**  
Logically ors the value in the accumulator with two consecutive V memory locations.

**Or Formatted (ORF)**  
D4-440, D4-450 & D4-454 Only Logically ors the value in the accumulator with a range of discrete bits (1-32).

**Or with Stack (ORS)**  
D4-440, D4-450 & D4-454 Only Logically ors the value in the accumulator with the first value in the accumulator stack.

**Exclusive Or (XOR)**  
Performs an exclusive or of the value in the lower 16 bits of the accumulator and a V memory location.

**Exclusive Or Double (XORD)**  
Performs an exclusive or of the value in the accumulator and two consecutive V memory locations.

**Exclusive Or Formatted (XORF)**  
D4-440, D4-450 & D4-454 Only Performs an exclusive or of the value in the accumulator and a range of discrete bits (1-32).

**Exclusive Or with Stack (XORS)**  
D4-440, D4-450 & D4-454 Only Performs an exclusive or of the value in the accumulator and the first accumulator stack location.

**Compare (CMP)**  
Compares the value in the lower 16 bits of the accumulator with a V memory location.

**Compare Double (CMPD)**  
Compares the value in the accumulator with two consecutive V memory locations or an 8-digit constant.

**Compare Formatted (CMPF)**  
D4-440, D4-450 & D4-454 Only Compares the value in the accumulator with a specified number of discrete bits (1-32).

**Compare with Stack (CMPs)**  
Compares the value in the accumulator with the first accumulator stack location.

**Compare Real Number (CMPR)**  
D4-450 & D4-454 Only Compares the real number in the accumulator with two consecutive V memory locations or a real number constant.

## Math Instructions

**Add (ADD)**  
Adds a BCD value in the lower 16 bits in the accumulator with a V memory location. The result resides in the accumulator.

**Add Double (ADD D)**  
Adds a BCD value in the accumulator with two consecutive V memory locations or an 8-digit constant. The result resides in the accumulator.

**Add Real Number (ADDR)**  
D4-450 & D4-454 Only Adds a real number in the accumulator with a real number constant or a real number contained in two consecutive V-memory locations. The result resides in the accumulator.

**Subtract (SUB)**  
Subtracts a BCD value in a V memory location from the lower 16 bits in the accumulator. The result resides in the accumulator.

**Subtract Double (SUBD)**  
Subtracts a BCD value, which is either two consecutive V memory locations or a real number constant, from a value in the accumulator. The result resides in the accumulator.

**Subtract Real Number (SUBR)**  
D4-450 & D4-454 Only Subtract a real number, which is either two consecutive V memory locations or an 8-digit constant, from the real number in the accumulator. The result resides in the accumulator.

**Multiply (MUL)**  
Multiplies a BCD value, which is either a V memory location or a 4-digit constant, by the value in the lower 16 bits in the accumulator. The result resides in the accumulator.

**Multiply Double (MULD)**  
D4-450 & D4-454 Only Multiplies a BCD value contained in two consecutive V memory locations by the value in the accumulator. The result resides in the accumulator.

**Multiply Real Number (MULR)**  
D4-450 & D4-454 Only Multiplies a real number, which is either two consecutive V memory locations or a real number constant, by the real number in the accumulator. The result resides in the accumulator.

**Divide (DIV)**  
Divides a BCD value in the lower 16 bits of the accumulator by a BCD value which is either a V memory location or a 4-digit constant. The result resides in the accumulator.

**Divide Double (DIVD)**  
D4-440, D4-450 & D4-454 Only Divides a BCD value in the accumulator by a BCD value in two consecutive V memory locations. The result resides in the accumulator.

**Divide Real Number (DIVR)**  
D4-450 & D4-454 Only Divides a real number in the accumulator by a real number which is either two consecutive V memory locations or a real number constant. The result resides in the accumulator.

**Increment Binary (INCB)**  
Increments a binary value in a specified V memory location by 1 each time the instruction is executed.

**Decrement Binary (DECB)**  
Decrements a binary value in a specified V memory location by 1 each time the instruction is executed.

**Add Binary (ADDB)**  
Adds the binary value in the lower 16 bits of the accumulator to a value which is either a V memory location or a 16 bit constant. The result resides in the accumulator.

**Add Binary Double (ADDD)**  
D4-440, D4-450 & D4-454 Only Adds the binary value in the accumulator to a value which is either two consecutive V memory locations or a 32 bit constant. The result resides in the accumulator.

**Subtract Binary (SUBB)**  
Subtract a 16 bit binary value, which is either a V memory location or a 16 bit constant, from the lower 16 bits in the accumulator. The result resides in the accumulator.

**Subtract Binary Double (SUBBD)**  
D4-440, D4-450 & D4-454 Only Only Subtracts a 32 bit binary value, which is either two consecutive V memory locations or a 32 bit constant, from the value in the accumulator. The result resides in the accumulator.

**Multiply Binary (MULB)**  
Multiplies a 16 bit binary value, which is either a V memory location or a 16 bits constant, by the lower 16 bits in the accumulator. The result resides in the accumulator.

**Divide Binary (DIVB)**  
Divides the binary value in the lower 16 bits in the accumulator by a value which is either a V memory location or a 16 bit constant. The result resides in the accumulator.

**Add Formatted (ADDF)**  
D4-440, D4-450 & D4-454 Only Adds the BCD value in the accumulator to a value which is a range of discrete bits (1-32). The result resides in the accumulator.

**Subtract Formatted (SUBF)**  
D4-440, D4-450 & D4-454 Only Subtracts a BCD value which is a range of discrete bits (1-32) from the BCD value in the accumulator. The result resides in the accumulator.

**Multiply Formatted (MULF)**  
D4-440, D4-450 & D4-454 Only Multiplies a BCD value in the lower 16 bits in the accumulator by a BCD value which is a range of discrete bits (1-16). The result resides in the accumulator.

**Divide Formatted (DIVF)**  
D4-440, D4-450 & D4-454 Only Divides the BCD value in the lower 16 bits in the accumulator by the BCD value which is a range of discrete bits (1-16). The result resides in the accumulator.

**Add Top of Stack (ADD S)**  
Adds the BCD value in the accumulator with the BCD value in the first level of the accumulator stack. The result resides in the accumulator.

**Subtract Top of Stack (SUBS)**  
Subtracts the BCD value in the first level of the accumulator stack from the BCD value in the accumulator. The result resides in the accumulator.

**Multiply Top of Stack (MULS)**  
Multiplies a 4-digit BCD value in the first level of the accumulator stack by a 4-digit BCD value in the accumulator. The result resides in the accumulator.

**Divide by Top of Stack (DIVS)**  
Divides the 8-digit BCD value in the accumulator by the 4-digit BCD value in the first level of the accumulator stack. The result resides in the accumulator.

**Add Binary Top of Stack (ADDBS)**  
D4-440, D4-450 & D4-454 Only Adds the binary value in the accumulator with the binary value in the first accumulator stack location. The result resides in the accumulator.

**Subtract Binary Top of Stack (SUBBS)**  
D4-440, D4-450 & D4-454 Only Subtracts the binary value in the first level of the accumulator stack from the binary value in the accumulator. The result resides in the accumulator.

**Multiply Binary Top of Stack (MULBS)**  
D4-440, D4-450 & D4-454 Only Multiplies the 16 bit binary value in the first level of the accumulator stack by the 16 bit binary value in the accumulator. The result resides in the accumulator.

**Divide Binary Top of Stack (DIVBS)**  
D4-440, D4-450 & D4-454 Only Divide a value in the accumulator by the binary value in the top location of the stack. The accumulator contains the result.

**Increment (INC)**  
Increments a BCD value in a specified v memory location by 1 each time the instruction is executed.

**Decrement (DEC)**  
Decrements a BCD value in a specified V memory location by 1 each time the instruction is executed.

## Number Conversion Instructions

**Binary (BIN)**  
Converts the BCD value in the accumulator to the equivalent binary value. The result resides in the accumulator.

**Binary Coded Decimal (BCD)**  
Converts the binary value in the accumulator to the equivalent BCD value. The result resides in the accumulator.

**Invert (INV)**  
Takes the one's complement of the 32 bit value in the accumulator. The result resides in the accumulator.

**Ten's Complement (BCDCPL)**  
Takes the ten's complement of the BCD value in the accumulator. The result resides in the accumulator.

**ASCII to HEX (ATH)**  
D4-440, D4-450 & D4-454 Only Converts a table of ASCII values to a table of hexadecimal values.

**HEX to ASCII (HTA)**  
D4-440, D4-450 & D4-454 Only Converts a table of hexadecimal values to a table of ASCII values.

**Segment (SEG)**  
Converts a 4-digit HEX number in the accumulator to a corresponding bit pattern for interfacing to seven segment displays. The result resides in the accumulator.

**Gray code to BCD (GRAY)**  
D4-440, D4-450 & D4-454 Only Converts a 16 bit GRAY code value in the accumulator to a corresponding BCD value. The result resides in the accumulator.

**Shuffle digits (SFLDGT)**  
D4-440, D4-450 & D4-454 Only Shuffles a maximum of 8 digits, rearranging them in a specified order. The result resides in the accumulator.

**Binary to Real Number (BTOR)**  
D4-450 & D4-454 Only Converts the binary value in the accumulator into a real number. The result resides in the accumulator.

**Real to Binary (RTOB)**  
D4-450 & D4-454 Only Converts the real number in the accumulator into a binary value. The result resides in the accumulator.

**Radian Real Conversion (RADR)**  
D4-450 & D4-454 Only Converts the real degree value in the accumulator to the equivalent real number in radians. The result resides in the accumulator.

**Degree Real Conversion (DEGR)**  
D4-450 & D4-454 Only Converts the real radian value in the accumulator to the equivalent real number of degrees. The result resides in the accumulator.

## Trigonometric Instructions

**Square Root Real (SQRTR)**  
D4-450 & D4-454 Only Takes the square root of the real number stored in the accumulator. The result resides in the accumulator.

**Sine Real (SINR)**  
D4-450 & D4-454 Only Takes the sine of the real number stored in the accumulator. The result resides in the accumulator.

**Cosine Real (COSR)**  
D4-450 & D4-454 Only Takes the cosine of the real number stored in the accumulator. The result resides in the accumulator.

**Tangent Real (TANR)**  
D4-450 & D4-454 Only Takes the tangent of the real number stored in the accumulator. The result resides in the accumulator.

**Arc Sine Real (ASINR)**  
D4-450 & D4-454 Only Takes the inverse sine of the real number stored in the accumulator. The result resides in the accumulator.

**Arc Cosine Real (ACOSR)**  
D4-450 & D4-454 Only Takes the inverse cosine of the real number stored in the accumulator. The result resides in the accumulator.

**Arc Tangent real (ATANR)**  
D4-450 & D4-454 Only Takes the inverse tangent of the real number stored in the accumulator. The result resides in the accumulator.

# Instruction Set

## Bit Operation Instructions

### Sum (SUM)

Counts the number of bits in set to "1" in the accumulator. The HEX result resides in the accumulator.

### Shift Left (SHFL)

Shifts the bits in the accumulator a specified number of places to the left.

### Shift Right (SHFR)

Shifts the bits in the accumulator a specified number of places to the right.

### Rotate Left (ROTL)

Rotates the bits in the accumulator a specified number of places to the left.

### Rotate Right (ROTR)

Rotates the bits in the accumulator a specified number of places to the right.

### Set Bit (SETBIT)

D4-450 and D4-454 Only Sets a single bit (to a 1) in a V-memory location.

### Reset Bit (RSTBIT)

D4-450 and D4-454 Only Resets a single bit (to a 0) in a V-memory location.

### Encode (ENCO)

Encodes the bit position set to 1 in the accumulator, and returns the appropriate binary representation in the accumulator.

### Decode (DECO)

Decodes a 5 bit binary value (0-31) in the accumulator by setting the appropriate bit position to 1 in the accumulator.

## Table Instructions

### Fill (FILL)

Fills a table of specified V memory locations with a value which is either a V memory location or a 4-digit constant.

### Find (FIND)

D4-440, D4-450 & D4-454 Only Finds a value in a V memory table and returns the table position, containing the value, to the accumulator.

### Find Greater Than (FDGT)

D4-440, D4-450 & D4-454 Only Finds a value in a V memory table which is greater than the specified search value. The table position containing the value is returned to the accumulator.

### Find Block (FINDB)

D4-450 and D4-454 Only Finds a block of data values in a V memory table and returns the starting address of the table containing the values to the accumulator.

### Move (MOV)

D4-440, D4-450 & D4-454 Only Moves the values from one V memory table to another V memory table.

### Table To Destination (TTD)

D4-440, D4-450 & D4-454 Only Moves a value from the top of a V memory table to a specified V memory location. The table pointer increments each scan.

### Remove From Bottom (RFB)

D4-440, D4-450 & D4-454 Only Moves a value from the bottom of a V memory table to a specified V memory location. The table pointer decrements each scan.

### Source To Table (STT)

D4-440, D4-450 & D4-454 Only Moves a value from a specified V memory location to a V memory table. The table pointer increments each scan.

### Remove From Table (RFT)

D4-440, D4-450 & D4-454 Only Pops a value from the top of a V memory table and stores it in a specified V memory location. The values in the V memory table are shifted up each time a value is moved.

### Add To Top of Table (ATT)

D4-440, D4-450 & D4-454 Only Pushes a value from a specified V memory location onto the top of a V memory table. All other values in the V memory table are shifted down each time a value is pushed onto the table.

### Table Shift Left (TSHFL)

D4-450 and D4-454 Only Shifts a specified number of bits to the left in a V-memory table.

### Table Shift Right (TSHFR)

D4-450 and D4-454 Only Shifts a specified number of bits to the right in a V-memory table.

### Move Block (MOVBLK)

D4-450 and D4-454 Only copies a specified number of words from a Data Label Area of program memory (ACON, NCON) to a V-memory area.

### Move Memory Cartridge/Load Label (MOVMC/LDLBL)

D4-440, D4-450 & D4-454 Only copies data between V memory and program ladder memory.

## Program Control Instructions

### Goto/Label (GOTO/LBL)

D4-440, D4-450 & D4-454 Only Skips (does not execute) all instructions between the GOTO and the corresponding label (LBL) instruction.

### For/Next (FOR/NEXT)

D4-440, D4-450 & D4-454 Only Executes the logic between the FOR and NEXT instructions a specified number of times.

### Goto Subroutine/Subroutine Return Conditional/

### Subroutine Return (GTS/SBR w/RTC or RT)

D4-440, D4-450 & D4-454 Only When a GTS instruction is executed, the program jumps to the SBR (subroutine). The subroutine is terminated with an RT instruction (unconditional return). An RTC (conditional return) can be used in conjunction with the RT. When a conditional/unconditional return is executed, the program continues from the instruction after the calling GTS instruction.

### Master Line Set/Master Line Reset (MLS/MLR)

Allows the program to control sections of ladder logic by forming a new power rail. The MLS marks the beginning of a power rail and the MLR marks the end of the power rail control.

## Interrupt Instructions

### Interrupt Routine/Interrupt Conditional/Interrupt Return (INT/IRTC/IRT)

When a hardware or software interrupt has occurred, the interrupt routine will be executed. The INT instruction is the beginning of the interrupt routine. The interrupt routine is terminated with an IRT instruction (unconditional interrupt return). An IRTC (conditional interrupt return) can be used in conjunction with the IRT. When a conditional/unconditional interrupt return is reached, the execution of the program continues from the instruction where the program execution was prior to the interrupt.

### Enable Interrupt (ENI)

Enables hardware and software interrupts to be acknowledged.

### Disable Interrupt (DISI)

Disables hardware and software interrupts from being acknowledged.

## Message Instructions

### Fault/Data Label (FAULT/DLBL)

D4-440, D4-450 & D4-454 Only Displays a V memory value or a Data label constant to the handheld programmer or personal computer using DirectSOFT.

### Numerical Constant/ASCII constant (NCON/ACON)

D4-440, D4-450 & D4-454 Only Stores constants in numerical or ASCII form for use with other instructions.

### Print Message (PRINT)

D4-450 and D4-454 only Prints the embedded text or text / data variable message to the specified communications port. Maximum message length is 255 words.

## Clock/Calendar Instructions

### Date (DATE)

D4-440, D4-450 & D4-454 Only Sets the date (year, month, day, day of the week) in the CPU calendar using two consecutive V memory locations.

### Time (TIME)

D4-440, D4-450 & D4-454 Only Sets the time (hour, seconds, and minutes) in the CPU using two consecutive V memory locations.

## CPU Control Instructions

### No Operation (NOP)

Inserts a no operation coil at specified program address.

### End (END)

Marks the termination point for the normal program scan. An End instruction is required at the end of the main program body.

### Stop (STOP)

Changes the operational mode of the CPU from Run to Program (Stop).

### Break (BREAK)

D4-440, D4-450 & D4-454 Only Changes the operational mode of the CPU from Run to the Test Program mode.

### Reset Watchdog Timer (RSTWT)

Resets the CPU watchdog timer.

## Intelligent I/O Instructions

### Read from Intelligent Module (RD)

Reads a block of data (1-128 bytes max.) from an intelligent I/O module.

### Write to Intelligent Module (WT)

Writes a block of data (1-128 bytes max.) to an intelligent I/O module.

## Network Instructions

### Read from network (RX)

Reads a block of data from another CPU on the network.

### Write to network (WX)

Writes a block of data from the master device to a slave device on the network.

## RLL PLUS Programming Instructions

### Initial stage (ISG)

The initial stage instruction is used for a starting point for user application program. The ISG instruction will be active on power up and PROGRAM to RUN transitions.

### Stage (SG)

Stage instructions are used to create structured programs. They are program segments which can be activated or deactivated with control logic.

### Jump (JMP)

Normally open coil that deactivates the active stage and activates a specified stage when there is power flow to the coil.

### Not Jump (NJMP)

Normally closed coil that deactivates the active stage and activates a specified stage when there is no power flow to the coil.

### Converge Stages (CV)

D4-440, D4-450 & D4-454 Only Converge stages are a group of stages that when all stages are active the associated converge jump(s) (CVJMP) will activate another stage(s). One scan after the CVJMP is executed, the converge stages will be deactivated.

### Converge jump (CVJMP)

D4-440, D4-450 & D4-454 Only Normally open coil that deactivates the active CV stages and activates a specified stage when there is power flow to the coil.

### Block Call/Block/Block End (BCALL w/BLK and BEND)

D4-440, D4-450 & D4-454 Only BCALL is a normally open coil that activates a block of stages when there is power flow to the coil. BLK is the label which marks the beginning of a block of stages. BEND is a label used to mark the end of a block of stages.

## Drum Instructions

### Timed Drum with Discrete Outputs (DRUM)

D4-450 and D4-454 Only Time driven drum with up to 16 steps and 16 discrete output points. Output status is written to the appropriate output during each step. Specify a time base per count (in milliseconds). Each step can have a different number of counts to trigger the transition to the next step. Also define preset step as destination when reset occurs.

### Time & Event Drum with Discrete Outputs (EDRUM)

D4-450 and D4-454 Only Time and/or event driven drum with up to 16 steps and 16 discrete output points. Output status is written to the appropriate output during each step. Specify a time base per count (in milliseconds). Each step can have a different number of counts and an event to trigger the counting. Once the time has expired, a transition to the next step occurs. Also define preset step as destination when reset occurs.

### Time & Event Drum with Discrete Outputs and Output Mask (MDRMD)

D4-450 and D4-454 Only Time and/or event driven drum with up to 16 steps and 16 discrete output points. Actual output status is the result of a bit-by-bit AND between the output mask and the bit mask in the step. Specify a time base per count (in milliseconds). Each step can have a different number of counts and an event to trigger the counting. Once the time has expired, a transition to the next step occurs. Also define preset step as destination when reset occurs.

### Time & Event Drum with Word Output & Output Mask (MDRMDW)

D4-450 and D4-454 Only time and/or event driven drum with up to 16 steps and a single V-memory output location. Actual output word is the result of a bit-by-bit AND between the word mask and the bit mask in the step. Specify a time base per count (in milliseconds). Each step can have a different number of counts and an event to trigger the counting. Once the time has expired, a transition to the next step occurs. Also define preset step as destination when reset occurs.

