

IDEM Explosion-Proof Safety Cable-Pull Switches



IDEM's range of explosion-proof cable-pull switches has been developed to satisfy the latest IECEx and ATEX Standards and provide explosion-proof switching for use in hazardous locations created within the oil, chemical, pharmaceutical, food processing, packaging and other hazardous industries.

These switches provide positively operated switching contacts. They combine explosion-proof protection and satisfy high functional safety requirements all in one device.

These switches are manufactured with ATEX Exd IIC T6 certified explosion proof contact blocks. All electrical switching elements are fully encapsulated.

Features

- 3m [9.84ft] prewired pigtail cable
- Includes one tamper-proof T20 Torx bit
- Rope Pull kits sold separately and recommended for increased reliability
- 80m [262ft], 100m [328ft], 125m [410ft] and 250m [820ft] maximum length systems



IDEM Explosion-Proof Safety Cable-Pull Switches									
Part Number	Price	Maximum Rope Length	Construction Material	Mounting Profile	E-Stop	LED	Contact Configuration	Weight (lb [kg])	Drawings
GLS-EX-142030	\$873.00	80m [262ft]	Die-cast aluminum	100mm [3.94in]	Yes	No	2 N.O., 2 N.C.	2.34 [1.06]	PDF
GLS-SS-EX-144030	\$1,144.00	100m [328ft]	316 stainless steel	100mm [3.94in]	Yes	No	2 N.O., 2 N.C.	4.59 [2.08]	PDF
GLHL-EX-141020	\$890.00	125m [410ft]	Die-cast aluminum	100mm [3.94in] Left-hand head	Yes	No	2 N.O., 2 N.C.	2.89 [1.31]	PDF
GLHR-EX-141022	\$890.00	125m [410ft]	Die-cast aluminum	100mm [3.94in] Right-hand head	Yes	No	2 N.O., 2 N.C.	2.89 [1.31]	PDF
GLHD-EX-141018	\$1,107.00	250m [820ft]	Die-cast aluminum	100mm [3.94in] Dual head	Yes	No	2 N.O., 2 N.C.	3.39 [1.54]	PDF

*See Recommended Rope Span Options and Fittings for number of switches recommended with specific maximum rope lengths.



GLHD-EX-141018
Dual head



GLHL-EX-141020
Left-hand



GLHR-EX-141022
Right-hand




GLS-EX-142030



GLS-SS-EX-144030

Connection Colors



IDEM Cable-Pull Safety Rope Switches



Cable Kits for IDEM Cable-Pull Safety Switches					
Part Number	Price	Description	Cable Length (m [ft])	Construction Material	Weight (lb [kg])
140002	\$122.00	Includes (1) cable, (5) eyebolts, (1) tensioner / gripper and (1) allen key.	10 [32]	Galvanized steel	0.8 [0.36]
140011	\$172.00			Stainless steel	1.3 [0.59]
140004	\$171.00	Includes (1) cable, (9) eyebolts, (1) tensioner / gripper and (1) allen key.	20 [65]	Galvanized steel	2.2 [1.0]
140013	\$208.00			Stainless steel	2.9 [1.32]
140005	\$193.00	Includes (1) cable, (12) eyebolts, (1) tensioner / gripper and (1) allen key.	30 [98]	Galvanized steel	2.8 [1.27]
140014	\$246.00			Stainless steel	3.9 [1.77]
140006	\$231.00	Includes (1) cable, (20) eyebolts, (1) tensioner / gripper and (1) allen key.	50 [164]	Galvanized steel	4.5 [2.04]
140015	\$278.00			Stainless steel	6.0 [2.72]
140007	\$258.00	Includes (1) cable, (30) eyebolts, (2) tensioner / grippers and (1) allen key.	80 [262]	Galvanized steel	7.0 [3.18]
140016	\$351.00			Stainless steel	9.5 [4.31]
140009	\$309.00	Includes (1) cable, (45) eyebolts, (2) tensioner / grippers and (2) allen keys.	126 [413]	Galvanized steel	13.9 [6.28]
140018	\$440.00			Stainless steel	14.0 [6.35]



140002



140033

Steel Cable for IDEM Cable-Pull Safety Switches				
Part Number	Price	Description	Cable Length (m [ft])	Weight (lb [kg])
140033	\$26.00	5m length steel cable, 4mm diameter, red	5 [16]	0.35 [0.16]
140034	\$38.00	10m length steel cable, 4mm diameter, red	10 [32]	0.7 [0.32]
140036	\$58.00	20m length steel cable, 4mm diameter, red	20 [65]	1.4 [0.64]
140037	\$75.00	30m length steel cable, 4mm diameter, red	30 [98]	2.1 [0.95]
140038	\$103.00	50m length steel cable, 4mm diameter, red	50 [164]	3.5 [1.59]
140039	\$155.00	80m length steel cable, 4mm diameter, red	80 [262]	5.4 [2.45]
140040	\$178.00	100m length steel cable, 4mm diameter, red	100 [328]	6.6 [2.99]
140041	\$203.00	126m length steel cable, 4mm diameter, red	126 [413]	8.42 [3.82]

IDEM Cable-Pull Safety Switch Accessories					
Part Number	Price	Description	Construction Material	Weight (lb [kg])	Drawings
140019	\$128.00	Cable tensioner / gripper. Includes 4mm allen wrench	Stainless steel	0.5 [0.27]	PDF
140020	\$79.00		Galvanized steel	0.3 [0.14]	PDF
140021	\$45.00	Pulley assembly	Stainless steel	0.3 [0.14]	PDF
140064	\$29.00		Galvanized steel	0.2 [0.09]	PDF
140045	\$57.00	Eye bolt 84mm long, M8 x 1.25 threads. Includes (2) flat washers and (2) nuts per eye bolt. Package of 8.	Stainless steel	0.8 [0.36]	PDF
140046	\$28.50		Galvanized steel	0.5 [0.27]	PDF
140043	\$37.50	Spring, 220mm long	Stainless steel	0.4 [0.18]	PDF
140132-AS	\$57.00	Replacement LED assembly, 24 VDC, bi-color steady green and red. Use with GL series cable pull switches.	NA	0.08 [0.04]	PDF
140132-BS	\$67.00	Replacement LED assembly, 110V AC, bi-color steady green and red. Use with GL series cable pull switches.	NA	0.08 [0.04]	PDF



140019



140021



140045



140043



140132-AS


IDEM Cable-Pull Rope Span Options and Fittings



Recommended Rope Span Installations


GLM 30m

Up to 30m [98ft]
1 switch / 1 spring




GLM 50m

30 to 60m [98 to 197ft]
2 switches




GLS 60m

Up to 60m [197ft]
1 switch / 1 spring




GLS 80m

60 to 80m [197 to 262ft]
2 switches




GLS-SS 80m

Up to 80m [262ft]
1 switch / 1 spring



GLS-SS 100m


80 to 100m [262 to 328ft]
2 switches



GLHL/R 100m


With Safety Springs

Up to 100m [328ft]
1 switch / 1 spring



GLHL/R 125m

Up to 125m [410ft]
2 switches




IDEM Cable-Pull Rope Span Options and Fittings



Recommended Rope Span Installations (continued)


GLHD 200m With Safety Springs

Up to 200m [656ft]
(100m [328ft] on each side)
1 switch / 2 springs






GLHD/L/R 250m

Up to 250m [820ft]
(125m [410ft] on each side)
2 switches



Universal Pulley Examples


- Use two switches when using two pulleys
- When using a safety spring, use a maximum of one corner pulley



LED

When power is applied to the Red wire (terminal 1), the lamp will illuminate red. When power is applied to the Green Wire (terminal 3), the lamp will illuminate green. Black is 0 VDC or neutral for 110 VAC and 230 VAC versions.

LED Steady Red - Stopped
LED Steady Green - Run



IDEM Explosion-Proof Safety Switches

Specifications



Specifications					
	HLM-EX / HLM-SS-EX	KM-EX / KM-SS-EX	KP-EX / K-SS-EX	GLS-EX / GLS-SS-EX	GLHx-EX
Safety Classification and Reliability Data					
Switching Reliability (B10_d)	2.5 x 10 ⁶ operations at 100 mA load			1.5 x 10 ⁶ operations at 100 mA load	
ISO 13849-1	Up to PLe depending upon system architecture				
EN 62061	Up to SIL3 depending upon system architecture				
Safety Data—Annual Usage	8 cycles per hour / 24 hours per day / 365 days				
MTTF_d	356 years			214 years	
Agency Approvals	ATEX, IECEx, CE The contact block is cURus Hazardous Location rated (E358295)				
Electrical and General Specifications					
Utilization Category	B300 (pilot duty)				
Minimum Switch Current	5 mA, 5 VDC				
Thermal Current	2.5A max				
Maximum Switching Current	250VAC/DC, 2.5A maximum				
Maximum Approach/Withdrawal Speed	600 mm/s [23.6 in/s]			NA	
Enclosure Protection	IP67 (IP69K on all models with both stainless steel head and body)				
Operating Temperature	-20 to 60 °C [-4 to +140 °F]				
Vibration	IEC 68-2-6, 10 Hz to 55 Hz 0.35mm [0.01in]	IEC 68-2-6, 10 Hz to 55 Hz + 1 Hz			
Lid Screws/Torque	Plated brass 1 N•m [0.74 lb•ft]	Stainless steel T20 Torx 1 N•m [0.74 lb•ft]	Stainless steel 1 N•m [0.74 lb•ft]	Stainless steel T20 Torx 1.5 N•m [1.11 lb•ft]	
Recommended Mounting Screws/Torque	M4 2 N•m [1.48 lb•ft]	M5 4 N•m [2.95 lb•ft]			
Head Screws/Torque	Stainless steel, except snap (plated brass) 1 N•m [0.74 lb•ft]	Stainless steel T20 Torx 1 N•m [0.74 lb•ft]	Stainless steel; 1 N•m [0.74 lb•ft]		

IDEM Interlock/Hinge Safety Travel Charts



Interlock Safety Switch Types

Slow-make/slow-break contacts:

A contact element in which the contact motion is dependent on the actuator speed.


Snap-action contact:

A contact element in which the contact motion is independent of the speed of the actuator. This feature ensures reliable electrical performance even in applications involving very slow moving actuators.

Contacts Configuration


1 N.O. and 2 N.C.

Slow-make/slow-break contacts




3 N.C.

Slow-make/slow-break contacts




1 N.O. and 1 N.C.

Snap action contacts




1 N.O. and 3 N.C.

Slow-make/slow-break contacts




1 N.O. and 1 N.C.

Slow-make/slow-break contacts




2 N.O. and 2 N.C.

Slow-make/slow-break contacts



2 N.C.

Slow-make/slow-break contacts



Travel Charts



Interlock Switches

2NC 1NO 6.8 6.0 0 mm

11/12	Open	
21/22	Open	
33/34		Open

3NC 6.0 0 mm

11/12	Open	
21/22	Open	
31/32	Open	

3NC 1NO 6.8 6.0 0 mm

11/12	Open	
21/22	Open	
31/32	Open	
43/44		Open


2NC 2NO 6.8 6.0 0 mm

11/12	Open	
21/22	Open	
33/34		Open
43/44		Open

1NC 1NO (SNAP) 6.5 0 mm

11/12	Open	
23/24		Open

Hinge Switch



User to ensure that by correct positioning of the shaft at installation causes the safety contacts to open such that no hazard exists to the operator when the door is opened a few degrees.

Safety Rope Switches

0 mm 3.5 mm 14.5 mm 17.0 mm

EX	1 N.O./2 N.C.	1 N.O./3 N.C.	2 N.O./2 N.C.	Latched off - Rope Slack	Tension Range (Switch Reset)	Rope Pulled
N.C.	11/12	11/12	11/12	Open		Open
	21/22	21/22	21/22	Open		Open
		31/32		Open		Open
N.O.	33/34	43/44	33/44		Open	
			43/44		Open	

Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application.

AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.