



# Fuse Blocks for Class R Fuses



Dimensions in [mm]



**RM60100 Series**




**RM60200 Series**

Please see our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


# Fuse Blocks for Class R Fuses



Dimensions in [mm]



**RM60400 Series**



**RM60600 Series**

Please see our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

# Modular Ferrule Fuse Blocks for Midget Class and CC Fuses



## Description

BCM Series for use with Class CC fuses EDCC, HCTR and HCLR  
 BMM Series for use with Midget Class Midget fuses  
 MCL, MEQ, MEN & MOL

## Mounting

35mm DIN rail or panel mount

## Specifications

### Materials:

Base – Thermoplastic  
 Terminals – Tin-plated bimetallic copper  
 Covers – Thermoplastic  
 Screws and pressure plates – Zinc-plated steel

**SCCR:** 200kA

### Flammability rating:

Blocks – UL 94V0, self-extinguishing  
 Covers – UL 94HB, self-extinguishing

### Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]  
 Covers – indicating -20° to 90°C [-4° to 194°F]  
 non-indicating -40° to 120°C [-40° to 248°F]

### Wire:

Cu – 75°/90°C [ 167°/194°F]  
 Ring or Fork terminal to fit a #10-32 screw

## Agency Approvals


### Fuse Blocks

- BCM – UL<sup>®</sup> Listed E14853 - IZLT  
 BMM and BCCM UL Recognized E14853-IZLT2
- CSA<sup>®</sup> Certified 47235-6225-01
- CE
- RoHS Compliant
- Conflict mineral free
- REACH Compliant

### Covers

- Covers are included in the overall UL Listing/Recognition and CSA Certification
- IP20 finger-safe
- RoHS compliant
- REACH Compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Pressure Plate (with Quick Connect***) Modular Ferrule Fuse Blocks for Midget Class and CC Fuses													
Class	Part Number	Pc/ pkg	Price	Volts	Amps	Poles	Wire Range <sup>1</sup>		Torque lb-in [N·m]	Wt. lb [kg]	Covers* (Sold Separately)		
							solid and stranded	fine stranded			w/o Indication	w/ Indication <sup>3</sup>	Pc/ pkg
Midget	BMM603-1PQ	15	\$68.75	600V AC/DC	30	1	18-10 AWG	18-10 AWG	20 [2.3]	0.05 [0.04]	CVR-CCM-QC \$14.00	CVRI-CCM-QC \$18.75	3
	BMM603-2PQ	5	\$39.25			2				0.15 [0.06]			
	BMM603-3PQ	5	\$50.00			3				0.20 [0.10]			
	BMM603-1PQ-1	1	\$5.00			1				0.05 [0.04]			
CC	BCM603-1PQ	15	\$94.25			1				0.05 [0.04]			
	BCM603-2PQ	5	\$47.25			2				0.15 [0.06]			
	BCM603-3PQ	5	\$62.25			3				0.20 [0.10]			
	BCM603-1PQ-1	1	\$6.75			1				0.05 [0.04]			
Combo	BCCMM603-3PQ <sup>2</sup>	5	\$66.00			3			0.20 [0.10]				

<sup>1</sup> Ratings are for copper wire only.

<sup>2</sup> Combination modular fuse block for use with transformers. Accepts two (2) Class CC and one (1) Midget class fuse.

<sup>3</sup> Open fuse indication requires 90V minimum and closed circuit to operate.

\*Once installed, the cover cannot be removed.

\*\*Quick connect terminal rated for 20A maximum.