

Fuse Blocks for Class J Fuses



J60060-1C

Description

For use with Edison JDL class J fuses

Terminal type:

- C = Box lug type
- CR = Box lug type, with retaining clip
- P = Pressure plate. Clip reinforcing springs are standard on fuseblocks rated 100A and above.

Specifications

Construction: Thermoplastic,
UL Flammability; 94V-0

Voltage Ratings: 600 Volts AC

Ampere Ratings: 0.50 - 600 Amps

Short-circuit current Rating: 200,000 RMS
Symmetrical Amps

Agency Approvals

- UL Listed, UL 512, Guide IZLT, File E14853
- CSA, certified, C22.2 No. 39, Class 6225-01, File 47235

Class J Fuse Blocks							
Part Number	Amps	Poles	Maximum Wire Size	Fig #	Pcs/ Pkg	Wt. (lbs.)	Price
J60030-1P	0.5 to 30	1	#10-14 Cu	1	1	0.44	\$18.50
J60060-1C	31 to 60	1	#2-14 Cu-Al	1		0.44	\$20.50
J60060-2C		2		0.35		\$39.00	
J60100-1CR	61 to 100	1	1/0-8 Cu-Al	4		0.98	Retired
J60200-1CR	101 to 200	1	250MCM-6 Cu-Al	5		1.70	Retired
J60200-3CR		3		6.70		Retired	
J60400-1CR	201 to 400	1	500MCM-4 Cu-Al	6		3.10	Retired
J60400-3CR		3		14.0		Retired	
J60600-3CR*	401 to 600	3	(2) 500MCM-4/0 Cu-Al	10		8.0	Retired

* Not UL

Class J Fuseholder Dimensions

0.5 Amp to 60 Amp




Figure 1

Figure 2


Figure 3

Note: All dimensions shown in inches [mm]

Fuse Blocks for Class J Fuses



61 Amp to 100 Amp



101 Amp to 200 Amp

Figure 4




Figure 5





Figure 6



201 Amp to 400 Amp




Figure 7





Figure 8



401 Amp to 600 Amp




Figure 9





Figure 10



Note: All dimensions shown in inches [mm]