

Medium Duty Absolute Encoders (Metric Dimension Encoders)

TRD-NA series


Features

Why use an absolute encoder? Absolute encoders provide their exact position at all times, allowing monitoring equipment to read the correct position, even when power cycles. Features include:

- Small body with 50mm diameter and 35mm depth
- Splash proof (IP65 rating)
- 8mm solid shaft
- Absolute resolution available from 32 pulses per revolution to 2048 pulses per revolution
- Open collector output
- Up to 20kHz response frequency



Standard shaft (TRD-NA) model



| Absolute Medium Duty Solid Shaft Encoders | | | | | |
|---|----------|--|---------------|--------------------|-----------|
| Part Number | Price | Resolution | Input Voltage | Output | Body Dia. |
| TRD-NA32NWD | \$271.00 | 5 bit gray code, 32 pulses per revolution | 10-26 VDC | NPN open collector | 50 mm |
| TRD-NA64NWD | \$271.00 | 6 bit gray code, 64 pulses per revolution | | | |
| TRD-NA128NWD | \$271.00 | 7 bit gray code, 128 pulses per revolution | | | |
| TRD-NA180NWD | \$271.00 | 8 bit gray code, 180 pulses per revolution | | | |
| TRD-NA256NWD | \$271.00 | 8 bit gray code, 256 pulses per revolution | | | |
| TRD-NA360NWD | \$271.00 | 9 bit gray code, 360 pulses per revolution | | | |
| TRD-NA512NWD | \$271.00 | 9 bit gray code, 512 pulses per revolution | | | |
| TRD-NA720NWD | \$271.00 | 10 bit gray code, 720 pulses per revolution | | | |
| TRD-NA1024NWD | \$271.00 | 10 bit gray code, 1024 pulses per revolution | | | |
| TRD-NA2048NWD | \$271.00 | 11 bit gray code, 2048 pulses per revolution | | | |

| Wiring Connections | | | | | | | | |
|--------------------|-------------------|-----------------------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|---------------------------------|
| Wire color | Connector Pin No. | Resolution | | | | | | |
| | | 2048 | 1024 / 720 | 512 / 360 | 256 / 180 | 128 | 64 | 32 |
| Blue | 1 | 0V | | | | | | |
| Brown | 2 | 12/24V | | | | | | |
| Black | 3 | bit 0 (2 ⁰) * | bit 0 (2 ⁰) * | no connection | | | | |
| Red | 4 | bit 1 (2 ¹) * | bit 1 (2 ¹) * | bit 0 (2 ⁰) * | no connection | | | |
| Orange | 5 | bit 2 (2 ²) * | bit 2 (2 ²) * | bit 1 (2 ¹) * | bit 0 (2 ⁰) * | no connection | | |
| Yellow | 6 | bit 3 (2 ³) * | bit 3 (2 ³) * | bit 2 (2 ²) * | bit 1 (2 ¹) * | bit 0 (2 ⁰) * | no connection | |
| Green | 7 | bit 4 (2 ⁴) * | bit 4 (2 ⁴) * | bit 3 (2 ³) * | bit 2 (2 ²) * | bit 1 (2 ¹) * | bit 0 (2 ⁰) * | no connection |
| Purple | 8 | bit 5 (2 ⁵) * | bit 5 (2 ⁵) * | bit 4 (2 ⁴) * | bit 3 (2 ³) * | bit 2 (2 ²) * | bit 1 (2 ¹) * | bit 0 (2 ⁰) * |
| Gray | 9 | bit 6 (2 ⁶) * | bit 6 (2 ⁶) * | bit 5 (2 ⁵) * | bit 4 (2 ⁴) * | bit 3 (2 ³) * | bit 2 (2 ²) * | bit 1 (2 ¹) * |
| White | 10 | bit 7 (2 ⁷) * | bit 7 (2 ⁷) * | bit 6 (2 ⁶) * | bit 5 (2 ⁵) * | bit 4 (2 ⁴) * | bit 3 (2 ³) * | bit 2 (2 ²) * |
| Black / White | 11 | bit 8 (2 ⁸) * | bit 8 (2 ⁸) * | bit 7 (2 ⁷) * | bit 6 (2 ⁶) * | bit 5 (2 ⁵) * | bit 4 (2 ⁴) * | bit 3 (2 ³) * |
| Red / White | 12 | bit 9 (2 ⁹) * | bit 9 (2 ⁹) * (MSB) | bit 8 (2 ⁸) * (MSB) | bit 7 (2 ⁷) * (MSB) | bit 6 (2 ⁶) * (MSB) | bit 5 (2 ⁵) * (MSB) | bit 4 (2 ⁴) * (MSB) |
| Orange / White | 13 | bit 10 (2 ¹⁰) * (MSB) | no connection | | | | | |
| Shield | - | GND ** | | | | | | |

* Numbers in parentheses () are the bits corresponding to binary code.
 ** GND (cable shield) is not connected to encoder body; the enclosure is grounded through the 0VDC line.
 Note: Numbers in parentheses () are the bits corresponding to binary code.

Medium Duty Absolute Encoders (Metric Dimension Encoders)

Specifications – TRD-NA series

| Electrical Specifications | | |
|-------------------------------------|--|---|
| Model | TRD-NAxxx-NWD | |
| Power Supply | Operating Voltage * | 12–24 VDC (nominal) * Range: 10.8–26.4 VDC |
| | Allowable Ripple | 3% rms max. |
| | Current Consumption | 70mA max. |
| Output Code | Gray binary (38 gray codes at 180 resolution, 76 at 360 resolution, and 152 at 720 resolution) | |
| Max. Response Frequency | 20kHz (Maximum revolution speed = (max. response frequency / resolution) x 60). (The encoder does not respond to revolution faster than the maximum speed.) | |
| Accuracy | $\frac{360}{\text{Resolution}} = \text{degree of accuracy}$ | |
| Direction of Rotation | Normal (CW) or reversed (CCW) (When viewed from the shaft, CW is clockwise direction, and CCW is counterclockwise direction) | |
| Rise/Fall Time | 2µs max. (at 1kW load resistance and when cable length is 2m or less) | |
| Output | Output Type | NPN open collector |
| | Output Logic | Negative logic (active low) |
| | Sinking Current | 32mA max. |
| | Residual Voltage | 16mA or less: 0.4 V max. 16mA → 32mA: 1.5 V max. |
| | Load Power Voltage | 35VDC max. |
| * To be supplied by Class II source | | |
| Mechanical Specifications | | |
| Starting Torque | 0.03 N·m [0.02 lb·ft] | |
| Max. Allowable Shaft Load | Radial: 50N [11.24 lbs]; Axial: 30N [6.74 lbs] | |
| Max. Allowable Speed | Continuous: 3000 rpm, instantaneous: 5000 rpm; (highest speed that can support the mechanical integrity of encoder) | |
| Wire Size | 26 AWG | |
| Weight | Approx. 300g (10.58 oz) with 2m cable | |
| Environmental Specifications | | |
| Ambient Temperature | -10 to 60 °C [14 to 140 °F] | |
| Storage Temperature | -25 to 85 °C [-13 to 185 °F] | |
| Operating Humidity | 25–85% RH (with no condensation) | |
| Insulation Resistance | 10MΩ min. | |
| Vibration Resistance | Durable for one hour along three axes at 10 to 55 Hz with 0.75 mm amplitude | |
| Shock Resistance | 11ms with 980m/s ² applied three times along three axes | |
| Mounting Orientation | Can be mounted in any orientation | |
| Protection | IP65 | |
| Agency Approvals | CE, RoHS, cUL _{US} (E189395) | |

Accessories

Couplings

For encoders with a solid shaft, please select a coupling that fits your encoder. All couplings are typically in stock, ready to ship.

See the “Encoder Couplings” section for more information.

Mounting Bracket & Clamps

| Mounting Accessories | | |
|--|---------|---|
| Part # | Price | Description |
| JT-035D | \$10.50 | Mounting Bracket: Metal; for use with all TRD-N/NH/NA encoders |
| NM-9D* | \$6.00 | Mounting Clamp: Metal; for use with all TRD-N/NA encoders * |
| NF-55D* | \$15.00 | Mounting Flange Kit: includes aluminum flange & NM-9D clamp; for use with all TRD-N/NA encoders * |
| * Order NF-55D (flange & clamp) for new installations. Order NM-9D (clamp) for replacement parts only. | | |

JT-035D



NM-9D



NF-55D




Medium Duty Absolute and Incremental Encoders (Metric Dimension Encoders)


Dimensions – TRD-N(H) & TRD-NA series

The following are the external dimensions of both incremental and absolute medium duty encoders and optional mounting accessories.

Solid Shaft Incremental and Absolute Encoders (TRD-N, TRD-NA)




Hollow Shaft Incremental Encoders only (TRD-NH)




Optional Mounting Flange and Brackets for Medium Duty Encoders

NOTE: NF-55D flange & included NM-9D bracket: Requires (3) M4 x 0.7 tapped holes equally spaced on a 64mm bolt circle in the mounting surface.


JT-035D (bracket)




NF-55D (flange)



TRD-NH-BKT (bracket)



NM-9D (clamp)(included with NF-55D)




Encoder Accessories – Couplings

Encoder Couplings

Couplings provide a connection between solid-shaft encoders and solid shafts. We offer aluminum, fiberglass, and polymer couplings for metric, S.A.E. and metric-to-S.A.E. applications.

Misalignment compensation




| Couplings Selection Guide and Dimensions | | | | | | | | | | | | | | | | |
|--|--------------------|---------|---|----------------|-----------|-------------|-------------|------------|------------|--------------|---------|-------------|--------------|----------------|--------------------|--|
| Type | Part Number | Price | Applicable Encoders (shaft size) | Shaft Diameter | | D | L | F | C | M | a | E | S | Working Torque | Torsional Rigidity | Material |
| | | | | d1 | d2 | | | | | | | | | | | |
| | | | | max | | | (mm [in]) | | | | (N-m) | | | | | |
| Fiberglass (metric) | GJ-4D | \$9.00 | TRD-MX (4mm) | 4mm | 4mm | 13 [0.51] | 21 [0.83] | 5.3 [0.21] | 3 [0.12] | M3 set screw | 5° | 0.4 [0.02] | 0.4 [0.02] | 0.6 N-m | 6 N-m/rad | Glass-fiber reinforced resin |
| | GJ-6D | \$7.00 | TRD-S (6mm) | 6mm | 6mm | 15 [0.59] | 22 [0.87] | 5.2 [0.20] | 3 [0.12] | M3 set screw | 6° | 0.5 [0.02] | 0.12 [0.005] | 0.8 N-m | 10 N-m/rad | |
| | GJ-8D | \$7.00 | TRD-N/NA (8mm) | 8mm | 8mm | 19 [0.75] | 24 [0.94] | 6.8 [0.27] | 3.5 [0.14] | M4 set screw | 5° | 0.5 [0.02] | 0.4 [0.016] | 1.5 N-m | 20 N-m/rad | |
| | GJ-10D | \$9.25 | TRD-GK (10 mm) | 10 mm | 10 mm | 22 [0.87] | 26 [1.02] | 7.1 [0.28] | 4 [0.16] | M4 set screw | 5° | 0.5 [0.02] | 0.12 [0.005] | 2.0 N-m | 32 N-m/rad | |
| Fiberglass (SAE) | GJ-635D | \$10.00 | TRDA-2E (0.25 in) | 0.25 in | 0.25 in | 15 [0.59] | 22 [0.87] | 5.2 [0.20] | 3 [0.12] | M3 set screw | 5° | 0.5 [0.02] | 0.12 [0.005] | 0.8 N-m | 10 N-m/rad | Glass-fiber reinforced resin |
| | GJK-953D | \$15.00 | TRDA-20/25 (0.375 in) | 0.375 in | 0.375 in | 25 [0.98] | 32 [1.26] | 7.3 [0.29] | 3.5 [0.14] | M4 set screw | 5° | 0.5 [0.02] | 0.12 [0.005] | 2.0 N-m | 32 N-m/rad | |
| Polymer (SAE) | STP-MTRA-SC-1412 | \$19.00 | TRDA-2E (0.25 in) | 0.25 in | 0.50 in | 25 [0.98] | 38 [1.50] | 9.9 [0.39] | 5.4 [0.21] | M3 cap screw | 5° | 0.3 [0.01] | 0.12 [0.005] | 3.7 N-m | 0.36 °/lb-in | Engineered polymer |
| | STP-MTRA-SC-3812 | \$19.00 | TRDA-20/25 (0.375 in) | 0.375 in | 0.50 in | 25 [0.98] | 38 [1.50] | 9.9 [0.39] | 5.4 [0.21] | M3 cap screw | 5° | 0.3 [0.01] | 0.12 [0.005] | 3.7 N-m | 0.36 °/lb-in | |
| Aluminum (metric) | ARM-075-5-4D | \$28.00 | TRD-MX (4mm) | 4mm | 5mm | 19.1 [0.75] | 19.1 [0.75] | 4.6 [0.18] | 2.4 [0.09] | M3 set screw | 5° | 0.25 [0.01] | 0.25 [0.01] | 2.3 N-m | 8.2 N-m/rad | Aluminum alloy |
| | RU-075D | \$43.50 | TRD-S (6mm) | 6mm | 6mm | 19.1 [0.75] | 19.1 [0.75] | 4.6 [0.18] | 2.4 [0.09] | M3 set screw | 5° | 0.25 [0.01] | 0.12 [0.005] | 1.0 N-m | 8.2 N-m/rad | |
| | JU-100D | \$39.50 | TRD-N/NA (8mm) | 8mm | 8mm | 25.4 [1.00] | 25.4 [1.00] | 6.6 [0.26] | 3.8 [0.15] | M5 set screw | 5° | 0.25 [0.01] | 0.25 [0.01] | 1.6 N-m | 14.3 N-m/rad | |
| | RU-100D | \$42.50 | TRD-GK (10 mm) | 10 mm | 10 mm | 25.4 [1.00] | 25.4 [1.00] | 6.6 [0.26] | 3.8 [0.15] | M5 set screw | 5° | 0.25 [0.01] | 0.12 [0.005] | 1.6 N-m | 14.3 N-m/rad | |
| Aluminum (metric-to-SAE) | ML13P-4-476D | \$28.00 | TRD-MX (4mm) | 4mm | 0.1875 in | 13 [0.51] | 19 [0.75] | 5.5 [0.22] | 2.5 [0.10] | M2 set screw | 5° | 0.4 [0.02] | 0.2 [0.01] | 0.25 N-m | 44 N-m/rad | Aluminum alloy (Bent plate: Polyimide) |
| | ML16P-4-635D | \$28.00 | TRD-MX (4mm) TRDA-2E (0.25 in) | 4mm | 0.25 in | 16 [0.63] | 23 [0.91] | 7 [0.28] | 3 [0.12] | M3 set screw | 5° | 0.6 [0.02] | 0.3 [0.01] | 0.4 N-m | 70 N-m/rad | |
| | MCGL16-6-635 | \$19.00 | TRD-S (6mm) TRDA-2E (0.25 in) | 6mm | 0.25 in | 16 [0.63] | 23.2 [0.91] | 7 [0.28] | 3 [0.12] | M3 set screw | 3.5° | 0.3 [0.01] | 0.3 [0.01] | 0.4 N-m | 70 N-m/rad | |
| | MCGL20-8-635 | \$27.50 | TRD-N/NA (8mm) TRDA-2E (0.25 in) | 8mm | 0.25 in | 20 [0.79] | 26 [1.02] | 7.5 [0.30] | 3.7 [0.15] | M3 set screw | 3.5° | 0.3 [0.01] | 0.4 [0.02] | 0.6 N-m | 130 N-m/rad | |
| | MCGL20-8-952 | \$27.50 | TRD-N/NA (8mm) TRDA-20/25 (0.375 in) | 8mm | 0.375 in | 20 [0.79] | 26 [1.02] | 7.5 [0.30] | 3.7 [0.15] | M3 set screw | 3.5° | 0.3 [0.01] | 0.4 [0.02] | 0.6 N-m | 130 N-m/rad | |
| | MCGL25-10-635 | \$31.00 | TRD-GK (10 mm) TRDA-2E (0.25 in) | 10 mm | 0.25 in | 25 [0.98] | 30.2 [1.19] | 9 [0.35] | 4 [0.16] | M4 set screw | 3.5° | 0.3 [0.01] | 0.5 [0.02] | 1.4 N-m | 240 N-m/rad | |
| | MCGL25-10-952 | \$31.00 | TRD-GK (10 mm) TRDA-20/25 (0.375 in) | 10 mm | 0.375 in | 25 [0.98] | 30.2 [1.19] | 9 [0.35] | 4 [0.16] | M4 set screw | 3.5° | 0.3 [0.01] | 0.5 [0.02] | 1.4 N-m | 240 N-m/rad | |
| Aluminum (SAE) | ARM-075-635-635D | \$26.00 | TRDA-2E (0.25 in) | 0.25 in | 0.25 in | 19.1 [0.75] | 19.1 [0.75] | 4.6 [0.18] | 2.4 [0.09] | M3 set screw | 5° | 0.25 [0.01] | 0.25 [0.01] | 1.0 N-m | 8.2 N-m/rad | Aluminum alloy |
| | ARM-100-9525-9525D | \$28.00 | TRDA-20/25 (0.375 in) | 0.375 in | 0.375 in | 25.4 [1.00] | 25.4 [1.00] | 6.6 [0.26] | 3.8 [0.15] | M5 set screw | 5° | 0.25 [0.01] | 0.25 [0.01] | 1.6 N-m | 14.3 N-m/rad | |

* mm ÷ 25.4 = inches


Encoder Accessories – Couplings

Encoder Couplings – Dimensions


GJ-xxD Fiberglass Couplings (metric) & GJx-xxxD Fiberglass Couplings (SAE)




STP-MTRA-SC-xxxx Polymer Couplings




ARM-xxxxxD Aluminum Couplings (metric & SAE)



MCGLxx Aluminum Couplings & ML1xP-4-xxxD Aluminum Couplings



RU-075D, RU-100D, and JU-100D Aluminum Couplings



Great Encoder Selection at Great Prices

Koyo



Heavy-duty TRD-GK

Medium Duty TRD-NH

Medium Duty TRD-N

Medium Duty TRDA-25 (w/MS connector)

Light-duty TRD-MX

| Duty | Family | Size | Encoder diameter | Shaft diameter | Solid or Hollow Shaft | Operating Voltage (VDC) and Electrical Output* | IP Rating | Max Radial Load (N) | Max Axial Load (N) | Available resolutions | |
|-------------|----------------------|---------|---------------------|----------------------------|-----------------------|--|---|---------------------|--------------------|---|---|
| Incremental | Light Duty | TRD-MX | 10 | 25mm | 4mm | solid | 5V Line Driver or 5-12V OC or 12-24V OC | IP50 | 10 | 5 | 100, 360, 500, 1000, 1024 |
| | | TRDA-2E | 15 | 1.5" | 1/4" | solid | 5V Line Driver or 12-24V OC | IP50 | 30 | 20 | 100, 360, 500, 1000, 1024, 2500 |
| | | TRD-S | 15 | 38mm | 6mm | solid | 5V Line Driver or 5-12V OC or 12-24V OC | IP40 | 20 | 10 | 100, 200, 250, 300, 360, 400, 500, 600, 800, 1000, 1024, 1200, 2000, 2500 |
| | | TRD-SH | 15 | 38mm | 8mm | hollow | 5V Line Driver or 5-12V OC or 12-24V OC | IP40 | 20 | 10 | 100, 200, 250, 300, 360, 400, 500, 600, 800, 1000, 1024, 1200, 2000, 2500 |
| | Medium Duty | TRDA-20 | 20 | 2" | 3/8" | solid | 5V Line Driver or 5-30V P/P | IP50 | 50 | 30 | 100, 360, 500, 1000, 1024, 2500 |
| | | TRDA-25 | 25 (w/size 20 body) | 2.5" flange (w/ 2.0" body) | 3/8" | solid | 5V Line Driver or 5-30V P/P | IP65 | 50 | 30 | 100, 360, 500, 1000, 1024, 2500 |
| | | TRD-N | 20 | 50mm | 8mm | solid | 5V Line Driver or 5-30V P/P | IP65 | 50 | 30 | 3, 4, 5, 10, 30, 40, 50, 60, 100, 120, 200, 240, 250, 300, 360, 400, 480, 500, 600, 750, 1000, 1024, 1200, 2000, 2500, 3000, 3600, 5000 |
| | TRD-NH | 20 | 50mm | 8mm | hollow | 5V Line Driver or 5-30V P/P | IP65 | 50 | 30 | 3, 4, 5, 10, 30, 40, 50, 60, 100, 120, 200, 240, 250, 300, 360, 400, 480, 500, 600, 750, 1000, 1024, 1200, 2000, 2500, 3000, 3600, 5000 | |
| | Heavy Duty | TRD-GK | 30 | 78mm | 10mm | solid | 10-30V P/P | IP65 | 100 | 50 | 30, 100, 120, 200, 240, 250, 300, 360, 400, 500, 600, 800, 1000, 1200, 1500, 1800, 2000, 2500, 3600, 5000 |
| | Medium Duty Absolute | TRD-NA | 20 | 50mm | 8mm | solid | 10-30V OC | IP65 | 50 | 30 | 32, 64, 128, 180, 256, 360, 512, 720, 1024, 2048 (Gray code) |

All our encoders feature an integral 2m cable except for the TRDA-25 series which has an MS connector

*Operating Voltage and Electrical Output:

- LD = Line Driver (all Line Drivers require 5VDC supply)
- OC = NPN Open Collector (at Operating Voltage)
- P/P = Push Pull or Totem Pole (at Operating Voltage)

Accessories

Couplings

A variety of couplings - metric-to-metric, inch-to-inch (SAE - SAE), and metric-to-inch are in stock, ready to ship.



Flanges

A collection of flanges that ease encoder mounting. Several models are available with round flanges, square flanges and miscellaneous mounting options.

Mounting brackets

Simplify your installation with a ready-to-use right-angle mounting bracket for light, medium and heavy-duty encoders



Cables

For encoders that require a connector cable, we have cables in stock, priced right and ready to ship.