



MTR2 & MTRP Series Rolled-Steel AC Motors – 3-Phase

56C/56HC-Frame TEFC Motors – 3-phase – 0.33 to 3 hp

Features

- Totally Enclosed Fan Cooled (TEFC) enclosure
- NEMA 56C or 56HC flange mount (56HC are suitable for 56, 143T, or 145T frame mounting dimensions)
- Rolled steel shell frame / cast aluminum end bell
- No mounting orientation restrictions
- Removable base / bolt-on/bolt-off mounting feet
- Steel fan cover
- Large easy-to-wire junction box with rubber gasket
- Heavy duty oversized ball bearings
- High tensile strength steel shaft
- Electrically reversible
- Inverter capable (3-phase only)
- NEMA design B
- Class F winding insulation
- Service Factor: 1.15 across-the-line (1.0 for 3-phase with AC drive)
- Two year warranty
- CCSAUS certified, CE

Accessories Available

- Junction boxes (replacement/spare)
- Fans (replacement/spare)
- Fan shrouds (replacement/spare)
- Motor bases (replacement/spare)
- Adjustable mounting slide bases

Applications

- Conveyors
- Fans
- Gear reducers
- Pumps



MTR Series 3-phase motor



MTRP Series 3-phase motor



MTR2 Series 3-phase motor



MTR2 & MTRP Series Rolled-Steel AC Motors – 3-Phase

56C/56HC-Frame TEFC Motors – 3-phase – 0.33 to 3 hp

Motor Specifications – 3-phase MTR2 & MTRP Series Motors – 1800 & 3600 RPM										
Part Number	Price	HP	Base RPM	Phase	Voltage	Housing	NEMA Frame	Service Factor	F.L. Amps @ 230V/460V	Approx Weight (lb)
MTR2-P33-3BD18	\$189.00	1/3	1800	3	230/460	TEFC rolled steel frame with cast aluminum end bell F1 conduit box location	56C flange mount (MTRP = 56HC)*	1.15	1.4 / 0.7	18
MTR2-P33-3BD36	\$167.00		3600						1.3 / 0.65	18
MTR2-P50-3BD18	\$198.00	1/2	1800						1.9 / 0.95	19
MTR2-P50-3BD36	\$175.00		3600						1.7 / 0.85	19
MTR2-P75-3BD18	\$216.00	3/4	1800						2.6 / 1.3	22
MTR2-P75-3BD36	\$185.00		3600						2.4 / 1.2	21
MTRP-001-3BD18	\$272.00	1	1800						3.2 / 1.6	35
MTRP-001-3BD36	\$223.00		3600						3.0 / 1.50	23
MTRP-1P5-3BD18	\$299.00	1-1/2	1800						4.5 / 2.25	43
MTRP-1P5-3BD36	\$252.00		3600						4.0 / 2.0	31
MTRP-002-3BD18	\$349.00	2	1800						6.0 / 3.0	49
MTRP-002-3BD36	\$272.00		3600						5.2 / 2.6	33
MTRP-003-3BD36	\$356.00	3	3600	7.4 / 3.7	39					

Note: Please review the AutomationDirect Terms & Conditions for warranty and service on this product.

IronHorse Motors with product numbers ending in P are Premium Efficiency motors and meet or exceed all current efficiency guidelines.

*56HC motors are capable of 56C C-face mounting, and are also compatible with 56, 143T, and 145T foot mounting dimensions.



MTR2 & MTRP Series Rolled-Steel AC Motors – 3-Phase

56C/56HC-Frame TEFC Motors – 3-phase – 0.33 to 3 hp – Performance Data

Performance Data – 3-phase MTR2 & MTRP Series Motors (460V data except as indicated) – 1800 & 3600 RPM

Part Number	HP	NEMA Design	FL RPM	Minimum Speed (rpm)		Current @ 230V/460V (Amps)			Torque (lb-ft)			Maximum Speed (rpm)		FL Efficiency (%)	FL Power Factor	Rotor Inertia (lb-ft ²)	Drawing Links
				CT	VT	No Load	Full Load	Locked Rotor	Full Load	Locked Rotor	Break-down	CHP*	Safe				
MTR2-P33-3BD18	1/3	B	1725	431	172	1.10 / 0.55	1.4 / 0.7	7 / 3.5	1.03	2.93	3.77	2700	5400	67.0	0.65	0.0329	PDF
MTR2-P33-3BD36			3450	862	345	0.8 / 0.4	1.3 / 0.65	7.6 / 3.8	0.50	1.14	1.99	5400		60.0	0.75	0.0245	PDF
MTR2-P50-3BD18	1/2		1725	431	172	1.36 / 0.68	1.9 / 0.95	10 / 5	1.53	3.81	4.96	2700		70	0.69	0.038	PDF
MTR2-P50-3BD36			3450	862	345	1.0 / 0.5	1.7 / 0.85	10.8 / 5.4	0.74	1.81	2.96	5400		67.5	0.74	0.0277	PDF
MTR2-P75-3BD18	3/4		1725	431	172	1.60 / 0.80	2.6 / 1.3	12.2 / 6.6	2.31	5.41	7.17	2700		73.0	0.73	0.048	PDF
MTR2-P75-3BD36			3450	862	345	1.3 / 0.7	2.4 / 1.2	16 / 8	1.14	2.95	4.25	5400		71.5	0.78	0.031	PDF
MTRP-001-3BD18	1		1760	440	176	2.18 / 1.09	3.22 / 1.61	31 / 16	3	12.35	14.51	2700	2700	85.5	0.69	0.107	PDF
MTRP-001-3BD36			3500	875	350	1.52 / 0.76	3.00 / 1.50	22 / 11	1.51	3.98	4.93	5400	5400	77	0.83	0.034	PDF
MTRP-1P5-3BD18	1-1/2		1760	440	176	2.8 / 1.4	4.52 / 2.26	47 / 24	4.4	21.68	21.76	2700	2700	86.5	0.72	0.135	PDF
MTRP-1P5-3BD36			3500	875	350	1.8 / 0.9	3.96 / 1.98	38 / 19	2.21	7.94	9.03	5400	5400	84.0	0.85	0.048	PDF
MTRP-002-3BD18	2		1760	440	176	3.62 / 1.81	5.92 / 2.96	61 / 31	6.03	27.3	27.46	2700	2700	86.5	0.74	0.158	PDF
MTRP-002-3BD36			3500	875	350	2.28 / 1.14	5.22 / 2.61	53 / 27	3.02	12.23	12.8	5400	5400	85.5	0.86	0.056	PDF
MTRP-003-3BD36	3	3500	875	350	3.54 / 1.77	7.38 / 3.69	89 / 45	4.49	19.44	20.39	5400	5400	86.5	0.85	0.069	PDF	

* Maximum Constant HP RPM is for direct coupled loads.



MTR2 / MTRP / MTRJ Series AC Motor Accessories – 3-Phase

56C-Frame TEFC Motors – 3-phase – 0.33 to 3 hp – Motor Accessories



Motor Base
MTAR-BASE-56



Fan
MTAR-FAN-56



Fan
MTA2-FAN-56



Fan
MTA2-FAN-56-1



Junction Box
MTAR-JBOX-56



Fan Shroud
MTAR-SHROUD-56

MTR Series 3-phase Motor Spare/Replacement Parts*				
<i>Part Number</i>	<i>Price</i>	<i>Accessory Type</i>	<i>Applicable MTR Motor Number</i>	<i>MTR Motor HP : RPM</i>
<u>MTAR-BASE-56</u>	\$14.50	Motor base	MTR-xxx-xBDxx	All
<u>MTAR-FAN-56</u>	Retired	Fan		
<u>MTAR-JBOX-56</u>	Retired	Junction box		
<u>MTAR-SHROUD-56</u>	\$14.50	Fan shroud		

* These accessories are spare/replacement components only for MTR series IronHorse motors.

MTR2/MTRP/MTRJ Series 3-phase Motor Spare/Replacement Parts				
<i>Part Number</i>	<i>Price</i>	<i>Accessory Type</i>	<i>Applicable MTRP Motor Number</i>	<i>MTRP Motor HP : RPM</i>
<u>MTA2-BASE-56</u>	\$22.00	Motor base	MTRP-xxx-3BDxx MTR2-Pxx-3BDxx MTRJ-Xxx-3BDxx	All
<u>MTA2-SHROUD-56</u>	\$22.00	Fan shroud		
<u>MTA2-JBOX-56</u>	\$22.00	Junction box		
<u>MTA2-FAN-56</u>	\$22.00	Fan		
<u>MTA2-FAN-56-1</u> *	\$14.00	Fan	MTRP-xxx-3BDxx MTRJP-Xxx-3BDxx	

* This accessory is a spare/replacement component only for MTRP series IronHorse motors.



AC Motor Selection – IronHorse[®] General Purpose Motors

IronHorse [®] 3-Phase Motor Selection					
Motor Series	MTR2/MTRP	MTRJ/MTRJP	MTDP	MTSP/MTSN	MTCP2
Paint Color	Black	Black	Blue	Stainless	Gray
Main Characteristics	General Purpose Rolled Steel	Jet Pump	Rolled Steel Open Drip Proof	Stainless Steel Premium Efficiency IP69K	Cast-Iron Hazardous Duty
Electrical Characteristics					
Horsepower range	1/3 - 3	1/3 - 3	1 - 50	1 - 20	1 - 300(T) 1 - 30(TC)
Base speed	1800; 3600	3600	1800; 3600	1200; 1800; 3600	1200; 1800; 3600
Standard Voltage	208-230/460 VAC; 230/460 VAC	208-230/460 VAC; 230/460 VAC	208-230/460 VAC	208-230/460 VAC	208-230/460 VAC; 460VAC
Phase / Base Frequency (Hz)	3-phase / 60 Hz				
Service Factor	1.15	1.15	1.15 (sine), 1.0 (drive)		1.25 (1-200) 1.15 (250-300) 1.0 (all w/ drive)
Design Code (NEMA)	B				
Insulation Class	Class F				
Insulation System	Dip and Bake	Dip and Bake Twice	VPI	Dip and Bake	Vacuum Impregnation
Duty Cycle	Continuous				
Thermal protection	None				
Hazard Classification	None			Class 1 / Div 2	
Mechanical Characteristics					
Frame size	56C or HC - 326T	56J	56C - 326T	56C - 256TC	143T/TC - 449T
Enclosure	ODP / TEFC	TEFC	ODP / TEFC	TEFC / TENV	TEFC
Enclosure Rating	IP43		IP23	IP69K	IP55
Frame material	Rolled steel		Rolled steel	304 Stainless steel	Cast iron
End bracket material	Aluminum	Aluminum	≤256 frame- Aluminum >256- Cast iron	304 Stainless steel	Cast iron
Junction box material	Steel	Steel	Steel	304 Stainless steel	Cast iron
Fan guard material	Steel	Steel	N/a	304 Stainless steel	Steel
Fan material	Polypropylene plastic	Plastic	N/a	Heat-Resistant Polyethylene	Plastic
Lead termination	Junction Box				
standard mounting	C-face with removable rigid base		Rigid base	C-face round body and C-face with rigid base	Rigid base, c-face with rigid base (1-100 hp)
Drive end shaft slinger	Yes	Yes	None	Yes	Yes
Bearings	Ball				1-300 hp - 2p, 1-75 hp - 4p & 6p: Ball 100-300 hp - 4p & 6p: Roller
Grease	Mobil Polyrex EM		NS7 ENS	Mobil Polyrex EM	
Standard junction box assembly position	F1				F1 (field convertible F2)
Performance Characteristics					
Constant Torque speed range	4:1	4:1	10:1	10:1	10:1
Variable Torque speed range	10:1	10:1	20:1	20:1	20:1
Constant Horsepower speed range	1.5:1	1.5:1	1.5:1	1.5:1	1.5:1
Temperature rise	B				
Encoder provisions	None				
Other Characteristics					
Warranty*	2 years	2 years	2 years	1 year	2 years
Agency Approvals **	CSA, CE	CSA,CE	CSA	NEMA, CSA, UR, CE, BISCC	CSA, ISO9001, CE

* See Terms and Conditions for motor warranty explanation.

1) For warranty on IronHorse motors below 50hp, warranty service can be arranged through AutomationDirect.

2) For warranty on IronHorse motors 50hp and above, motors must be inspected by a local EASA motor repair or service center; (see AutomationDirect Terms & Conditions).

** To obtain the most current agency approval information, see the Agency Approval Checklist on the specific part number's web page.

*** 56HC motors are capable of 56C C-face mounting, and are also compatible with 56, 143T, and 145T foot mounting dimensions.