


# Temperature Input Modules

<b>F4-08THM-J-n 8-Channel Thermocouple Input \$759.00</b>	
When you order the module, replace the "n" with the type of Thermocouple needed. For example, to order a Type J thermocouple module, order part number F4-08THM-J.	
<b>Number of channels</b>	8, differential inputs
<b>Input Ranges</b>	Type J -210/760°C, -350/1390°F
<b>Resolution</b>	12 bit (1 in 4,096)
<b>Input Impedance</b>	27kΩ
<b>Absolute Maximum Ratings</b>	Fault protected input, 130 Vrms or 100VDC
<b>Cold Junction Compensation</b>	Automatic
<b>Conversion Time</b>	15ms per channel, minimum 1 channel per CPU scan
<b>Converter Type</b>	Successive Approximation, 574

<b>Linearity Error</b>	± 1 count (0.03% of full scale) maximum
<b>Full Scale Calibration Error</b>	± 0.35% of full scale
<b>Maximum Inaccuracy*</b>	± 1°C for type J
<b>PLC Update Rate</b>	1 ch. per scan min., 8 per scan max.
<b>Digital Input Points Required</b>	16 (X) input points (12 binary data bits, 3 channel ID bits, 1 sign bit)
<b>Base Power Required 5V</b>	120mA
<b>Terminal Type (included)</b>	Non-removable
<b>External Power Supply</b>	24VDC ±10%, 50mA current
<b>Operating Temperature</b>	32 to 140°F (0 to 60°C)
<b>Storage Temperature</b>	-4 to 158°F (-20 to 70°C)
<b>Accuracy vs Temperature*</b>	57 ppm/°C maximum full scale
<b>Relative Humidity</b>	5 to 95% (non-condensing)
<b>Environmental Air</b>	No corrosive gases permitted
<b>Vibration</b>	MIL STD 810C 514.2
<b>Shock</b>	MIL STD 810C 516.2
<b>Noise Immunity</b>	NEMA ICS3-304

Note 1: Terminate shields at the respective signal source  
 Note 2: Leave unused channels open (no connection)  
 Note 3: This module is not compatible with the ZIPLink wiring system.



\*Max. inaccuracy is not guaranteed for temperatures lower than: -200°C for type J

