



Power Supplies - Switching CPS Universal Series 1/2/3 Phase



Overview

The LUTZE Universal Compact power supply series provides high efficiency, compact size, and power boost while allowing maximum installation flexibility. These models can take 1-, 2-, or 3-phase inputs to help installations in any application.

Features

- Compact footprint
- Aluminum housing
- 35mm DIN rail mount
- IP20
- 5 year warranty



CPSB-123-240-24

Power Supplies - Switching CPS Universal Series 1/2/3 Phase Selection Chart

Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Dimensions (W x H x D)	Drawing Link
CPSB-123-240-24 *	\$230.00	24VDC	10A	240W	200-500 VAC	150% for 5s	54 x 115 x 110mm [2.12 x 4.52 x 4.33 in]	PDF
CPSB-123-480-24 *	\$355.00		20A	480W		140% for 5s	73 x 140 x 125mm [2.87 x 5.51 x 4.92 in]	PDF

* Requires an external fuse.

Power Supplies - Switching CPS Universal Series 1/2/3 Phase Input Specifications

Part Number	CPSB-123-240-24	CPSB-123-480-24
Operation Voltage Range	187-550 VAC 250-725 VDC	
Frequency Range	47-63Hz	
Rated Current	1-Phase/2-Phase 2.2 A @ 220VAC, 1.1 A @ 500VAC 3-Phase 1.5 A @ 220VAC, 0.8 A @ 500VAC	1-Phase/2-Phase 2.9 A @ 200VAC, 1.3 A @ 500VAC 3-Phase 1.8 A @ 200VAC, 0.8 A @ 500VAC
Inrush Current	≤ 45A / 1.31 A ² s	≤ 55A / 2.16 A ² s
Power Factor Correction	> 0.6 @ 230V, 0.5 @ 400V	> 0.9
Recommended Circuit Breaker	C-curve 6A or D-curve 4A	

Power Supplies - Switching CPS Universal Series 1/2/3 Phase Output Specifications

Part Number	CPSB-123-240-24	CPSB-123-480-24
Maximum Output Current	15A, 6A	28A, 5s
Power Dissipation	< 18W	< 42W
Setting Range	23-28 VDC	23-28 VDC
Load Regulation	< 1%	< 1%
Ripple And Noise	<100mV pp	<50mV pp
Hold-Up Time	15ms @ 230VAC > 100ms @ 500VAC	> 50ms
Parallel / Redundant Mode	Yes, via external decoupling diode	
Efficiency (Typical)	> 93% @ 240VAC	> 92% @ 240VAC
Short-Circuit	38A	50A
MTBF	500,000h	500,000h

Power Supplies - Switching CPS Series

Power Supplies - Switching CPS 3-Phase Series General Specifications				
Series	ECO Series 1-Phase	Ultra Series 1-Phase	Universal Series - 1/2/3 Phase	3-Phase Series
Overvoltage Protection	≤ 33VDC			CPSB3-120-24 <32V CPSB3-240-24 <32V CPSB3-960-24 <33VDC
Overtemperature Protection	Yes			
Status Indicators	DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≤ 21.6 V		CPSB-123-240-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≥ 21.6 V CPSB-123-480-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): I _{out} > 1.1I _n	CPSB3-120-24 CPSB3-240-24 DC OK LED (green) ON U _{out} > 95% U _{set} OFF U _{out} > 90% U _{se} CPSB3-960-24 DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≥ 21.6 V
Humidity	5 to 95%, non-condensing			
Vibration	IEC 60068-2-6			
Shock	IEC 60068-2-27			
Protection Rating	IP20			
Mounting	35mm DIN rail (vertical)			
Housing Material	Aluminum (enclosed)			
Agency Approval	CE, UKCA, cULus E249179			

Additional Data							
Part Number	Weight kg [lb]	Operating Temperature	Storage Temperature	Terminal Type	Solid Wire Size*		Tightening Torque
					Output	Input	
<u>CPSB1-120-24E</u>	0.45 [0.99]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
<u>CPSB1-240-24E</u>	0.75 [1.65]						
<u>CPSB1-480-24E</u>	1 [2.20]						
<u>CPS2B1-120-24</u>	0.45 [0.99]	-35 to 70°C [-31 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
<u>CPS2B1-240-24</u>	0.75 [1.65]						
<u>CPS2B1-480-24</u>	1.1 [2.42]						
<u>CPSB-123-240-24</u>	0.65 [1.43]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² [AWG 30-12]	0.20 – 2.5 mm ² [AWG 30-12]	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]
<u>CPSB-123-480-24</u>	1 [2.20]				0.20 – 2.5 mm ² [AWG 24-14]	0.20 – 2.5 mm ² [AWG 24-14]	
<u>CPSB3-120-24</u>	0.66 [1.45]	-25 to 70°C [-13 to 158°F]	-40 to 85°C [-40 to 185°F]	Push-in	0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	–
<u>CPSB3-240-24</u>	0.78 [1.71]				0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	–
<u>CPSB3-960-24</u>	1.3 [2.86]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 10mm ² [AWG 24-14]	0.20 – 10mm ² [AWG 24-14]	max. 62 N•m

* For other types of wire please see the insert.