


18AWG SOOW Portable Cord - 600 Volt

| 18AWG SOOW Portable Cord Specifications | | | |
|---|--|-----------------------------|--|
| Conductor Gauge | 18AWG | Conductor Color | Per UL 62 Annex B |
| Conductor Stranding | 16/30 bare copper, Class K stranding ASTM B 174 | | 2 conductor - Black, White |
| Voltage Rating | 600V | | 3 conductor - Black, White, Green |
| Outer Jacket Material | CPE (chlorinated polyethylene elastomers) thermoset rubber | | 4 conductor - Black, White, Red, Green |
| Outer Jacket Color | Black with white print | Temperature Rating | 75°C (167°F) Wet, 90°C (194°F) Dry |
| Outer Jacket Thickness | 0.060" [1.52 mm] Nominal | Applicable Standards | UL 62, FT2 |
| Overall Diameter | See table below | | CSA 22.2 No. 49 |
| Cold Bend | -40°C (-40°F) per UL 1277 | | NEC (NFPA 70) Article 400 |
| Min. Bend Radius | 4x diameter | | NEC (NFPA 70) 501.140 Class 1 Div 2 |
| Operating Temperature | -40°C to 90°C (-40°F to 194°F) | | MSHA |
| Conductor Insulation | EPDM (ethylene propylene diene monomer) thermoset rubber | Approvals* | UL (E46194), CSA (90458) |
| Conductor Nominal Insulation Thickness | 0.030" [0.76 mm] | Sample Print Legend | SOUTHWIRE® ROYAL® CORD XX/C XX AWG (XXmm ²) SOOW E46194 (UL) 600V -40C TO 90C -- CSA LL90458 SOOW 600V -40C TO 90C FT2 WATER RESISTANT |

** To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com*

| 18AWG SOOW Portable Cord | | | | | | |
|--------------------------|----------------------|----------------------------------|-----------|---------------------------|----------------------------|----------------|
| Part Number | AWG/ # of Conductors | Nominal Overall Diameter in [mm] | Ampacity* | Minimum Cut Length (ft)** | Approximate Weight (lb/ft) | Price per foot |
| SOOW-18-2BK-1 | 18/2 | 0.346 [8.79] | 10 | 20 | 0.07 | \$0.32 |
| SOOW-18-3BK-1 | 18/3 | 0.365 [9.27] | 10 | 20 | 0.08 | \$0.40 |
| SOOW-18-4BK-1 | 18/4 | 0.390 [9.91] | 7 | 20 | 0.10 | \$0.48 |

** Per NFPA 70 NEC Table 400.5 (A)(1)
** See web store for maximum cut lengths*




Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

16AWG SOOW Portable Cord - 600 Volt

| 16AWG SOOW Portable Cord Specifications | | | |
|--|--|-----------------------------|---|
| Conductor Gauge | 16AWG | Conductor Color | Per UL 62 Annex B |
| Conductor Stranding | 26/30 bare copper, Class K stranding ASTM B 174 | | 2 conductor - Black, White |
| Voltage Rating | 600V | | 3 conductor - Black, White, Green |
| Outer Jacket Material | CPE (chlorinated polyethylene elastomers) thermoset rubber | Temperature Rating | 4 conductor - Black, White, Red, Green |
| Outer Jacket Color | Black with white print | | 5 conductor - Black, White, Red, Green, Orange |
| Outer Jacket Thickness | 0.060" [1.52 mm] Nominal | Applicable Standards | 75°C (167°F) Wet, 90°C (194°F) Dry |
| Overall Diameter | See table below | | UL 62, FT2 |
| Cold Bend | -40°C (-40°F) per UL 1277 | | CSA 22.2 No. 49 |
| Min. Bend Radius | 4x diameter | | NEC (NFPA 70) Article 400 |
| Operating Temperature | -40°C to 90°C (-40°F to 194°F) | | NEC (NFPA 70) 501.140 Class 1 Div 2 |
| Conductor Insulation | EPDM (ethylene propylene diene monomer) thermoset rubber | Approvals* | MSHA |
| Conductor Nominal Insulation Thickness | 0.030" [0.76 mm] | Sample Print Legend | UL (E46194), CSA (90458) |
| | | | SOUTHWIRE® ROYAL® CORD XX/C XX AWG (XXmm2) SOOW E46194 (UL) 600V -40C TO 90C -- CSA LL90458 SOOW 600V -40C TO 90C FT2 WATER RESISTANT |
| * To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com | | | |

| 16AWG SOOW Portable Cord | | | | | | |
|--|----------------------|----------------------------------|-----------|---------------------------|----------------------------|----------------|
| Part Number | AWG/ # of Conductors | Nominal Overall Diameter in [mm] | Ampacity* | Minimum Cut Length (ft)** | Approximate Weight (lb/ft) | Price per foot |
| SOOW-16-2BK-1 | 16/2 | 0.370 [9.40] | 13 | 20 | 0.08 | \$0.36 |
| SOOW-16-3BK-1 | 16/3 | 0.390 [9.91] | 13 | 20 | 0.09 | \$0.47 |
| SOOW-16-4BK-1 | 16/4 | 0.415 [10.54] | 10 | 20 | 0.12 | \$0.56 |
| SOOW-16-5BK-1 | 16/5 | 0.500 [12.57] | 10 | 20 | 0.14 | \$0.82 |
| * Per NFPA 70 NEC Table 400.5 (A)(1) | | | | | | |
| ** See web store for maximum cut lengths | | | | | | |



Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

14AWG SOOW Portable Cord - 600 Volt

| 14AWG SOOW Portable Cord Specifications | | | |
|--|--|-----------------------------|--|
| Conductor Gauge | 14AWG | Conductor Color | Per UL 62 Annex B |
| Conductor Stranding | 41/30 bare copper, Class K stranding ASTM B 174 | | 2 conductor - Black, White |
| Voltage Rating | 600V | | 3 conductor - Black, White, Green |
| Outer Jacket Material | CPE (chlorinated polyethylene elastomers) thermoset rubber | Temperature Rating | 4 conductor - Black, White, Red, Green |
| Outer Jacket Color | Black with white print | | 5 conductor - Black, White, Red, Green, Orange |
| Outer Jacket Thickness | 0.080" [2.03 mm] Nominal | | 75°C (167°F) Wet, 90°C (194°F) Dry |
| Overall Diameter | See table below | Applicable Standards | UL 62, FT2 |
| Cold Bend | -40°C (-40°F) per UL 1277 | | CSA 22.2 No. 49 |
| Min. Bend Radius | 4x diameter | | NEC (NFPA 70) Article 400 |
| Operating Temperature | -40°C to 90°C (-40°F to 194°F) | | NEC (NFPA 70) 501.140 Class 1 Div 2 |
| Conductor Insulation | EPDM (ethylene propylene diene monomer) thermoset rubber | Approvals* | MSHA |
| Conductor Nominal Insulation Thickness | 0.045" [1.14 mm] | Sample Print Legend | UL (E46194), CSA (90458) |
| | | | SOUTHWIRE® ROYAL® CORD XX/C XX AWG (XXmm ²) SOOW E46194 (UL) 600V -40C TO 90C -- CSA LL90458 SOOW 600V -40C TO 90C FT2 WATER RESISTANT |
| * To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com | | | |

| 14AWG SOOW Portable Cord | | | | | | |
|--|----------------------|----------------------------------|-----------|---------------------------|----------------------------|----------------|
| Part Number | AWG/ # of Conductors | Nominal Overall Diameter in [mm] | Ampacity* | Minimum Cut Length (ft)** | Approximate Weight (lb/ft) | Price per foot |
| SOOW-14-2BK-1 | 14/2 | 0.500 [12.70] | 18 | 20 | 0.13 | \$0.58 |
| SOOW-14-3BK-1 | 14/3 | 0.525 [13.34] | 18 | 20 | 0.17 | \$0.72 |
| SOOW-14-4BK-1 | 14/4 | 0.570 [14.48] | 15 | 20 | 0.20 | \$0.90 |
| SOOW-14-5BK-1 | 14/5 | 0.670 [16.97] | 15 | 20 | 0.27 | \$0.90 |
| * Per NFPA 70 NEC Table 400.5 (A)(1) | | | | | | |
| ** See web store for maximum cut lengths | | | | | | |




Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

12AWG SOOW Portable Cord - 600 Volt

| 12AWG SOOW Portable Cord Specifications | | | |
|--|--|-----------------------------|--|
| Conductor Gauge | 12AWG | Conductor Color | Per UL 62 Annex B |
| Conductor Stranding | 65/30 bare copper, Class K stranding ASTM B 174 | | 2 conductor - Black, White |
| Voltage Rating | 600V | | 3 conductor - Black, White, Green |
| Outer Jacket Material | CPE (chlorinated polyethylene elastomers) thermoset rubber | Temperature Rating | 4 conductor - Black, White, Red, Green |
| Outer Jacket Color | Black with white print | | 5 conductor - Black, White, Red, Green, Orange |
| Outer Jacket Thickness | 0.095" [2.41 mm] Nominal | | 75°C (167°F) Wet, 90°C (194°F) Dry |
| Overall Diameter | See table below | Applicable Standards | UL 62, FT2 |
| Cold Bend | -40°C (-40°F) per UL 1277 | | CSA 22.2 No. 49 |
| Min. Bend Radius | 4x diameter | | NEC (NFPA 70) Article 400 |
| Operating Temperature | -40°C to 90°C (-40°F to 194°F) | | NEC (NFPA 70) 501.140 Class 1 Div 2 |
| Conductor Insulation | EPDM (ethylene propylene diene monomer) thermoset rubber | Approvals* | MSHA |
| Conductor Nominal Insulation Thickness | 0.045" [1.14 mm] | | UL (E46194), CSA (90458) |
| | | Sample Print Legend | SOUTHWIRE® ROYAL® CORD XX/C XX AWG (XXmm ²) SOOW E46194 (UL) 600V -40C TO 90C -- CSA LL90458 SOOW 600V -40C TO 90C FT2 WATER RESISTANT |
| * To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com | | | |

| 12AWG SOOW Portable Cord | | | | | | |
|--|----------------------|----------------------------------|-----------|---------------------------|----------------------------|----------------|
| Part Number | AWG/ # of Conductors | Nominal Overall Diameter in [mm] | Ampacity* | Minimum Cut Length (ft)** | Approximate Weight (lb/ft) | Price per foot |
| SOOW-12-2BK-1 | 12/2 | 0.570 [14.48] | 25 | 20 | 0.18 | \$0.85 |
| SOOW-12-3BK-1 | 12/3 | 0.595 [15.11] | 25 | 20 | 0.22 | \$1.00 |
| SOOW-12-4BK-1 | 12/4 | 0.650 [16.51] | 20 | 20 | 0.28 | \$1.18 |
| SOOW-12-5BK-1 | 12/5 | 0.710 [18.11] | 20 | 20 | 0.34 | \$1.65 |
| * Per NFPA 70 NEC Table 400.5 (A)(1) | | | | | | |
| ** See web store for maximum cut lengths | | | | | | |



Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.


10AWG SOOW Portable Cord - 600 Volt

| 10AWG SOOW Portable Cord Specifications | | | |
|---|--|-----------------------------|--|
| Conductor Gauge | 10AWG | Conductor Color | Per UL 62 Annex B |
| Conductor Stranding | 104/30 bare copper, Class K stranding ASTM B 174 | | 2 conductor - Black, White |
| Voltage Rating | 600V | | 3 conductor - Black, White, Green |
| Outer Jacket Material | CPE (chlorinated polyethylene elastomers) thermoset rubber | | 4 conductor - Black, White, Red, Green |
| Outer Jacket Color | Black with white print | | 5 conductor - Black, White, Red, Green, Orange |
| Outer Jacket Thickness | 0.095" [2.41 mm] Nominal | Applicable Standards | 75°C (167°F) Wet, 90°C (194°F) Dry |
| Overall Diameter | See table below | | UL 62, FT2 |
| Cold Bend | -40°C (-40°F) per UL 1277 | | CSA 22.2 No. 49 |
| Min. Bend Radius | 4x diameter | | NEC (NFPA 70) Article 400 |
| Operating Temperature | -40°C to 90°C (-40°F to 194°F) | | NEC (NFPA 70) 501.140 Class 1 Div 2 |
| Conductor Insulation | EPDM (ethylene propylene diene monomer) thermoset rubber | Approvals* | MSHA |
| Conductor Nominal Insulation Thickness | 0.045" [1.14 mm] | | UL (E46194), CSA (90458) |
| | | Sample Print Legend | SOUTHWIRE® ROYAL® CORD XX/C XX AWG (XXmm ²) SOOW E46194 (UL) 600V -40C TO 90C -- CSA LL90458 SOOW 600V -40C TO 90C FT2 WATER RESISTANT |

** To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com*


| 10AWG SOOW Portable Cord | | | | | | |
|--------------------------|----------------------|----------------------------------|-----------|---------------------------|----------------------------|----------------|
| Part Number | AWG/ # of Conductors | Nominal Overall Diameter in [mm] | Ampacity* | Minimum Cut Length (ft)** | Approximate Weight (lb/ft) | Price per foot |
| SOOW-10-2BK-1 | 10/2 | 0.620 [15.75] | 30 | 20 | 0.23 | \$1.05 |
| SOOW-10-3BK-1 | 10/3 | 0.660 [16.76] | 30 | 20 | 0.30 | \$1.38 |
| SOOW-10-4BK-1 | 10/4 | 0.710 [18.03] | 25 | 20 | 0.36 | \$1.63 |
| SOOW-10-5BK-1 | 10/5 | 0.770 [19.56] | 25 | 20 | 0.44 | \$2.25 |

** Per NFPA 70 NEC Table 400.5 (A)(1)
** See web store for maximum cut lengths*



Please Note: Our prices on flexible cord are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.

Flexible Portable Cord - Type SOOW, SJOOW, SEOOW & SJEOOW Type W



Use AutomationDirect's Flexible Portable Cord for temporary or portable power applications in industrial, OEM, utility, and commercial applications. Based on the type, portable cord is a great solution for ceiling drops, mobile machinery power supplies, pendants and lighting among other applications from the factory floor to mining and heavy construction. Our cord is highly flexible and suitable for harsh conditions, including temperature extremes, as well as, oil and chemicals that are common in the industrial environment.

You get the choice of CPE (chlorinated polyethylene elastomers) thermoset rubber or TPE (thermoplastic elastomer) portable cords that meet all of your requirements in either "Extra-Hard Use" (SOOW & SEOOW) or "Hard Use" (SJOOW & SJEOOW).

You should feel confident that AutomationDirect's Portable Cord meets or exceeds all the requirements to make it UL & CSA Listed and complies with NFPA 70 Articles 400 & 501.140 (Haz-Loc) and the Mine Safety and Health Administration.

Portable Cord Letter Codes Definitions:

S = Service cord - 600 Volt

J = Junior service - 300 Volt

E = Elastomer - thermoplastic that looks and feels like rubber

OO = Oil-Resistant outer jacket and oil-resistant interior insulation

W = Moisture and sunlight resistant (approved for indoor and outdoor use)

Features

- 18AWG to 8AWG
- 2, 3, 4 & 5 conductors
- Cut to length in 1 foot increments
- Low 20 foot minimum length
- 600V & 300V versions, Type W 2000V
- Multiple ratings and approvals
- Wide operating temperature range
- Thermoset rubber or thermoplastic jackets
- Suitable for outdoor use
- Excellent abrasion resistance



Conductor Colors:

2 Conductor ● ○

3 Conductor ● ○ ●

4 Conductor ● ○ ● ●

5 Conductor ● ○ ● ● ●