

MAUN Pliers & Cutting Tools

Parallel-Action Pliers

Maun has made precision British pliers since 1944. Their signature parallel-action jaws stay flat and parallel through the full range of travel, gripping square, round, hex, and flat stock evenly along the entire jaw. An open throat lets rod, bar, pipe, and cable pass through the tool, so the jaws can grip at any point along the material's length. Available in flat nose, snipe nose, and thin nose styles to match the job.

Features

- Parallel-action jaws grip evenly along the full jaw length
- Open throat passes rod, bar, pipe, and cable through the tool for gripping anywhere along its length
- Serrated or smooth-jaw finishes available, in flat nose, snipe nose, and needle nose styles
- Precision-machined jaws with a rust-resistant finish for lasting durability
- Red comfort-grip handles reduce hand fatigue



Pliers & Cutting Tools							
Part Number	Pliers Type	Overall Length	Jaw Length	Jaw Opening	Jaw Width	Jaw Thickness	Price
<u>4333-125</u>	Parallel Snipe Nose	4.9in [125mm]	1.18in [30.0mm]	0.43in [11.0mm]	1.00in [25.4mm]	0.07in [1.8mm]	\$76.00
<u>4867-125</u>	Parallel Flat Nose	4.9in [125mm]	1.18in [30.0mm]	0.43in [11.0mm]	1.00in [25.4mm]	0.25in [6.4mm]	\$55.00
<u>4867-160</u>	Parallel Flat Nose	6.3in [160mm]	1.33in [34.0mm]	0.55in [14.0mm]	1.16in [29.5mm]	0.37in [9.4mm]	\$62.00
<u>4867-200</u>	Parallel Flat Nose	7.9in [200mm]	1.57in [40.0mm]	0.67in [17.0mm]	1.53in [39.0mm]	0.49in [12.5mm]	\$79.00
<u>4886-160</u>	Parallel Thin Nose	6.3in [160mm]	1.18in [30.0mm]	0.51in [13.0mm]	1.16in [29.5mm]	0.12in [3.0mm]	\$79.00
<u>4887-160</u>	Parallel Flat Nose	6.3in [160mm]	1.33in [34.0mm]	0.55in [14.0mm]	1.16in [29.5mm]	0.37in [9.4mm]	\$62.00

Nose Profiles



4333



4867



4886



4887