

STABLE™ Motor Slide Bases

Mounting Slide Bases for 56 to 449T NEMA Motors Features

- Allows adjustment of motor mounting position
- Slide direction is perpendicular to motor shaft
- Double adjusting screws for frames 182T-449T
- Manufactured to precise dimensional standards
- Dimensionally interchangeable with existing major makes
- Heavy-duty steel construction
- Painted with oven-baked primer for better adhesion of customer's paint
- All "D" bolts (motor mounting bolts) are fixed to the exact motor foot pattern
- All "D" bolts are welded into position to prevent spinning and dropping from slots
- Nuts and washers are provided for securing the motor to the slide base



STABLE Motor Slide Bases for 3-Phase Motors										
Part Number	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor						
				IronHorse	Marathon					
					micro -MAX ---- Max+	Black Max 230/460V ---- Black Max 575V	Blue Max	XRI GP & NEMA Premium	Powerwash SXT & Jet Pump	Blue Chip XRI 230/460V ---- Blue Chip XRI 575V
MTA-BASE-W56 *	\$12.25	56*	2.8	MTPM-P3x-1x18 MTPM-P5x-1x18 MTPM-P7x-1x18 MTPM-0xx-1x18 MTPM-1xx-1x18 MTR(2)(P)-xxx-xxxxx*	Y500 Y502 Y360 Y362 Y364 Y280 Y281 Y282	Y592(-A772) Y534(-A772) Y535(-A772) Y555(-A772) Y556(-A772)	-	E2000 D390 G580 D391 G581 K705 D392 G582 K707 D393A K708A G583A K709A D394A K721A G584A D395A G585A K724A D396A K725A	J066A	-
MTA-BASE-W143T	\$21.00	143T/TC	4.6	MTC2-001-3BD18(C) MTC2-1P5-3BD36	-	Y536(-A772)	-	E2001A E2003		-
MTA-BASE-W145T	\$21.00	145T/TC	5.1	MTC2-001-3BD12 MTC2-1P5-3BD18(C) MTC2-002-3BD18(C) MTC2-002-3BD36	Y366 Y368 Y284 Y285	Y537(-A772) Y538(-A772) Y551(-A772) Y557(-A772)	-	E2002 E2004A E2007A		-
MTA-BASE-W182T	\$27.50	182T/TC	9.2	MTC2-1P5-3BD12 MTC2-003-3BD18(C) MTC2-003-3BD36	Y1999 Y286A	Y541A(-A772) Y558A(-A772)	-	E2009 E2010	C383B	-

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).

** Motors [MTC-250-3D18](#) and [MTC-300-3D18](#) are obsolete, and no longer available.

table continued on next page

STABLE™ Motor Slide Bases

table continued from previous page										
STABLE Motor Slide Bases for 3-Phase Motors										
Part Number	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor						
				IronHorse	Marathon					Blue Chip XRI 230/460V ---- Blue Chip XRI 575V
					micro-MAX ---- Max +	Black Max 230/460V ---- Black Max 575V	Blue Max	XRI GP & NEMA Premium	Powerwash SXT & Jet Pump	
MTA-BASE-W184T	\$27.50	184T/TC	10	MTCP2-002-3BD12 MTCP2-005-3BD18(C) MTCP2-005-3BD36 MTF-00x-1C18	Y1372 Y287A	Y540(-A772) Y543A(-A772) Y559A(-A772)	-	E2012 E2013	C387B	-
MTA-BASE-W213T	\$40.50	213T/TC	13	MTCP2-003-3BD12 MTCP2-7P5-3BD18(C) MTCP2-7P5-3BD36	Y994	Y542(-A772) Y545(-A772) Y560(-A772)	-	E2011 E2016A	C389B C390B C391B E2011A E2016B	-
MTA-BASE-W215T	\$40.50	215T/TC	15	MTCP2-005-3BD12 MTCP2-010-3BD18(C) MTCP2-010-3BD36	Y996	Y544(-A772) Y547(-A772) Y561(-A772)	-	E2018	C392B E2014A E2018A	-
MTA-BASE-W254T	\$57.00	254T/TC	18	MTCP2-7P5-3BD12 MTCP2-015-3BD18(C) MTCP2-015-3BD36	-	Y546(-A772) Y549(-A772) Y562(-A772)	-	-	-	-
MTA-BASE-W256T	\$57.00	256T/TC	19	MTCP2-010-3BD12 MTCP2-020-3BD18(C) MTCP2-20-3BD36	-	Y548(-A772) Y552(-A772) Y563(-A772)	-	-	-	-
MTA-BASE-W284T	\$62.00	284T/TC	20	MTCP2-015-3BD12 MTCP2-025-3BD18(C)	-	Y553(-A772)	-	-	-	E207
MTA-BASE-W286T	\$62.00	286T/TC	21	MTCP2-20-3BD12 MTCP2-030-3BD18(C)	-	Y393(-A772)	-	-	-	-
MTA-BASE-W324T	\$94.00	324T/TC	30	MTCP2-040-3BD18(C)	-	-	Y571(-A774) Y513(-A775)	-	-	E209
MTA-BASE-W326T	\$94.00	326T/TC	31	MTCP2-050-3BD18(C)	-	-	Y572(-A774) Y514(-A775)	-	-	-
MTA-BASE-W364T	\$127.00	364T/TC	43	MTCP2-060-3BD18(C)	-	-	Y573(-A774) Y515(-A775)	-	-	-
MTA-BASE-W365T	\$127.00	365T/TC	43	MTCP2-075-3BD18(C)	-	-	Y574(-A774) Y516(-A775)	-	-	E212
MTA-BASE-W404T	\$156.00	404T/TC	58	-	-	-	-	-	-	-
MTA-BASE-W405T	\$156.00	405T/TC	60	MTCP2-100-3BD18(C)	-	-	Y575(-A774) Y517(-A775)	-	-	-
MTA-BASE-W444T	\$182.00	444T	63	MTCP2-125-3BD18	-	-	-	-	-	-
MTA-BASE-W445T	\$182.00	445T	65	MTCP2-150-3BD18	-	-	-	-	-	-
MTA-BASE-W447T	\$239.00	447T	89	MTCP2-200-3BD18	-	-	-	-	-	-
MTA-BASE-W449T	\$239.00	449T	94	MTCP2-250-3D18 MTCP2-300-3D18	-	-	-	-	-	-

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).

STABLE™ Motor Slide Bases



Mounting Slide Bases for 56 to 449T NEMA Motors Features

STABLE Motor Slide Bases for Single-Phase Motors									
Part Number	Price	Fits Frame Type	Product Wt. (lb)	Fits Motor					
				IronHorse	Marathon				
					Marathon DP GP (NEMA Service Factor)	Marathon DP Air Compressor	Fan & Blower	Marathon TE GP 4-in-1	Powerwash SXT
<u>MTA-BASE-W56</u>	\$12.25	56*	2.8	MTR2-xxx-1AB18 MTR2-xxx-1AB36 MTPM-xxx-1L18 MTPM-xxx-1M18	C158A G915A C175A C167A C179A G937A C185A C187A C193A E261A E268A EG277A C1270A	D010 C169 C704 D017	C216 C1153 C1155 B319 D118 C1158 C235 D115 C1160 C1161 B352	G570 D311 G571 D312 G572 D313 G573 D314 G574 D315 G575 D316	N341
<u>MTA-BASE-W143T</u>	\$21.00	143T / TC	4.6	-	C188A	-	-	-	-
<u>MTA-BASE-W145T</u>	\$21.00	145TC / TC	5.1	-	C191 I127 C194	-	-	-	-
<u>MTA-BASE-W182T</u>	\$27.50	182T / TC	9.2	-	-	-	-	-	-
<u>MTA-BASE-W184T</u>	\$27.50	184 / TC	10	MTF-00x-1C18	-	Z502	-	-	-
<u>MTA-BASE-W213T</u>	\$40.50	213T / TC	13	-	-	-	-	-	-
<u>MTA-BASE-W215T</u>	\$40.50	215T T TC	15	-	-	-	-	-	-

* IronHorse MTR2 56HC motors have double-punched bases to fit on slide base [MTA-BASE-W56](#).

STABLE Motor Slide Bases

Dimensions – Mounting Slide Bases for NEMA Motors



Dimensions [inches, except as noted] - STABLE Motor Slide Bases															
MTA-BASE-Wxxxx	A	B	C	D	E	F	G	H	I	J	K(mm)	L	M	N	W
56	10-5/8	6-1/2	1-1/8	4-1/2	2-7/16	1-1/2	3-13/16	2-7/8	3/8	3	2 mm	7/8	5/16 x 1	3/8 x 4	n/a
143T	10-1/2	7-1/2	1-1/8	5-1/2	2-3/4	2	3-3/4	3-3/8	3/8	3	3 mm	13/16	5/16 x 1	3/8 x 4	n/a
145T	10-1/2	8-1/2	1-1/8	6-1/2	2-3/4	2-1/2	3-3/4	3-7/8	3/8	3	3 mm	13/16	5/16 x 1	3/8 x 4	n/a
182T	12-3/4	9-1/2	1-1/2	6-1/2	3-3/4	2-1/4	4-1/2	4-1/4	1/2	3	3.5 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	4-1/2
184T	12-3/4	10-1/2	1-1/2	7-1/2	3-3/4	2-3/4	4-1/2	4-3/4	1/2	3	3.5 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	5-1/2
213T	15	11	1-3/4	7-1/2	4-1/4	2-3/4	5-1/4	4-3/4	1/2	3-1/2	3.8 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	5-1/2
215T	15	12-1/2	1-3/4	9	4-1/4	3-1/2	5-1/4	5-1/2	1/2	3-1/2	3.8 mm	1-1/2	3/8 x 1-3/4	1/2 x 6	7
254T	17-3/4	15-1/8	2	10-3/4	5	4-1/8	6-1/4	6-5/8	5/8	4	4.6 mm	1-7/16	1/2 x 1-3/4	5/8 x 6	5-5/16
256T	17-3/4	16-7/8	2	12-1/2	5	5	6-1/4	7-1/2	5/8	4	4.6 mm	1-7/16	1/2 x 1-3/4	5/8 x 6	7
284T	19-3/4	16-7/8	2	12-1/2	5-1/2	4-3/4	7	7-1/2	5/8	4-1/2	4.6 mm	1-11/16	1/2 x 2	5/8 x 6	7
286T	19-3/4	18-3/8	2	14	5-1/2	5-1/2	7	8-1/4	5/8	4-1/2	4.6 mm	1-11/16	1/2 x 2	5/8 x 6	8
324T	22-3/4	19-1/4	2-1/2	14	6-1/4	5-1/4	8	8-1/2	3/4	5-1/4	4.6 mm	2-3/16	5/8 x 2-1/2	3/4 x 9	7
326T	22-3/4	20-3/4	2-1/2	15-1/2	6-1/4	6	8	9-1/4	3/4	5-1/4	4.6 mm	2-3/16	5/8 x 2-1/2	3/4 x 9	8-1/2
364T	25-1/2	20-1/2	2-1/2	15-1/2	7	5-5/8	9	9-1/8	3/4	6	5.8 mm	2-1/16	5/8 x 2-1/2	3/4 x 9	7-3/4
365T	25-1/2	21-1/2	2-1/2	16-1/2	7	6-1/8	9	9-5/8	3/4	6	5.8 mm	2-1/16	5/8 x 2-1/2	3/4 x 9	8-3/4
404T	28-3/4	22-3/8	3	16-1/2	8	6-1/8	10	9-7/8	7/8	7	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	8-3/4
405T	28-3/4	23-7/8	3	18	8	6-7/8	10	10-5/8	7/8	7	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	10-1/4
444T	31-1/4	24-5/8	3	19-1/4	9	7-1/4	11	11	7/8	7-1/2	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	11
445T	31-1/4	26-5/8	3	21-1/4	9	8-1/4	11	12	7/8	7-1/2	5.8 mm	2-1/2	3/4 x 3	3/4 x 11	13
447T	31-1/4	30-1/8	3	24-3/4	9	10	11	13-3/4	7/8	7-1/2	8 mm	3	3/4 x 3-1/2	3/4 x 11	16-1/2
449T	31-1/4	35-1/8	3	29-3/4	9	12-1/2	11	16-1/4	7/8	7-1/2	8 mm	3	3/4 x 3-1/2	3/4 x 11	21-1/2