

# Enclosure Accessories



## Barrier Kits for HN4WM NEMA 4 Wallmount Enclosures



### Application

- Barrier kits are designed to provide 2 vertical sections within double-door, NEMA 4 enclosures.
- For use with HN4WM wallmount enclosures.
- For application example, can provide separation between power and control sections within one enclosure.
- Does NOT provide complete physical separation as there is space above and below the barrier to run wiring.
- Depth mounted - bolted to the subpanel at rear and the center post at front.
- Subpanels are steel and painted RAL 9003 white.
- Mounting hardware included.

### Shipping Schedule

Same day	1 - 15 days
Color indicates shipping lead time in business days.	

### Barrier Kits for HN4WM NEMA 4 Wallmount Enclosures

Part Number	Price	Enclosure Height	Enclosure Depth
<b>BKWM2408</b>	\$111.00	24 [610]	8 [203]
<b>BKWM3010</b>	\$122.00	30 [762]	10 [254]
<b>BKWM3612</b>	\$138.00	36 [914]	12 [305]
<b>BKWM4212</b>	\$144.00	42 [1067]	12 [305]
<b>BKWM4812</b>	\$164.00	48 [1219]	12 [305]

*Note: Dimensions in inches [millimeters].*

## Barrier Kits for NEMA 4 Floormount Enclosures



### Application

- Barrier kits are designed to provide 2 vertical sections within double-door, NEMA 4 enclosures.
- For use with HN4FM Series and 1422N4 enclosures.
- For application example, can provide separation between power and control sections within one cabinet.
- Does NOT provide complete physical separation as there is space above and below the barrier to run wiring.
- Depth mounted - bolted to the subpanel at rear and the center post at front.
- Certain sizes are depth adjustable.
- Subpanels are steel and painted RAL 9003 white.
- Mounting hardware included.

### Barrier Kits for NEMA 4 Floormount Enclosures

Part Number	Price	Enclosure Height	Enclosure Depth
<b>BKFM6012</b>	\$182.00	60 [1524]	10 [254] or 12 [305]
<b>BKFM6018</b>	\$198.00	60 [1524]	18 [457]
<b>BKFM7218</b>	\$204.00	72 [1829]	12 [305] or 18 [457]
<b>BKFM7224</b>	\$223.00	72 [1829]	24 [610]

*Note: Dimensions in inches [millimeters].*