


# NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding Disconnect with Slope Top



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 stainless steel.
- Flange trough collar (FTC) around odor opening excludes liquids and contaminants.
- Heavy-duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with bullet-style, heavy duty, lift off hinges.
- Formed 10-gauge steel inner panel is provided on collar studs.
- Panel supports are provided.
- Center post is removable, providing easy panel installation.
- Heavy-duty three-point latching mechanism with heavy-duty roller ends is provided for ease of door closing.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket.
- Right hand master door handle complete with screwdriver defeater and padlock hasp.
- Additional door handle complete with padlock hasp.
- A mechanical interlock activated by the master door prevents the auxiliary door from being opened first.
- The pre-installed flange cutout provides mounting for disconnect operators (verify compatibility in advance) - interlock hardware included with enclosure.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 3R, 4X, and 12 [File E65324]
- CSA Type 3R, 4, 4X, and 12 [File LR21001]
- Complies with:
  - NEMA Type 3R, 4X, 12, and 13
  - IEC 60529, IP66



## NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding Disconnect with Slope Top

304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Drawing Link
<a href="#">2STFSD747512SS</a>	\$16,571.00	<a href="#">2STFSD747512S16</a>	\$18,526.00	78.54 x 75.13 x 13.38 [1995 x 1908 x 340]	<a href="#">PDF</a>
<a href="#">2STFSD747518SS</a>	\$18,067.00	<a href="#">2STFSD747518S16</a>	\$20,204.00	80.72 x 75.13 x 19.38 [2050 x 1908 x 492]	<a href="#">PDF</a>
<a href="#">2STFSD747524SS</a>	\$19,470.00	<a href="#">2STFSD747524S16</a>	\$21,777.00	82.91 x 75.13 x 25.38 [2106 x 1908 x 645]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].



# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
<a href="#">MHK1</a>	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD1</a>	\$133.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1</a>	\$144.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2</a>	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD2</a>	\$228.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2</a>	\$246.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3</a>	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD3</a>	\$232.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3</a>	\$251.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK1SS</a>	\$234.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD1SS</a>	\$258.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1SS</a>	\$258.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2SS</a>	\$249.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD2SS</a>	\$274.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2SS</a>	\$274.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3SS</a>	\$362.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD3SS</a>	\$398.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3SS</a>	\$398.00	combination keylocking/ padlocking					<a href="#">PDF</a>