


# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding



## Features

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy-duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- 3-point padlocking door handle.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the subpanel.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 3R, 4X, and 12 [File E65324]
- Complies with:
  - NEMA Type 3R, 4X, 12, and 13
  - IEC 60529, IP66
  - CSA Type 3R, 4X and 12 [File LR21001]




## NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding

Part Number	Price	Enclosure Size HxWxD	Optional Subpanel	Price	Drawing Link
<a href="#">HN4FS604818SS</a>	\$6,543.00	60.06 x 48.06 x 19.25 [1526 x 1221 x 489]	<a href="#">60AWFW</a>	\$787.00	<a href="#">PDF</a>
<a href="#">HN4FS724818SS</a>	\$7,157.00	72.06 x 48.06 x 19.25 [1830 x 1221 x 489]	<a href="#">72ZWFW</a>	\$892.00	<a href="#">PDF</a>
<a href="#">HN4FS724824SS</a>	\$7,806.00	72.06 x 48.06 x 25.25 [1830 x 1221 x 641]	<a href="#">72ZWFW</a>	\$892.00	<a href="#">PDF</a>
<a href="#">HN4FS726018SS</a>	\$8,064.00	72.06 x 60.06 x 19.25 [1830 x 1526 x 489]	<a href="#">72ZXFW</a>	\$1,035.00	<a href="#">PDF</a>
<a href="#">HN4FS726024SS</a>	\$8,756.00	72.06 x 60.06 x 25.25 [1830 x 1526 x 641]	<a href="#">72ZXFW</a>	\$1,035.00	<a href="#">PDF</a>
<a href="#">HN4FS726036SS</a>	\$10,090.00	72.06 x 60.06 x 37.25 [1830 x 1526 x 946]	<a href="#">72ZXFW</a>	\$1,035.00	<a href="#">PDF</a>
<a href="#">HN4FS727218SS</a>	\$8,955.00	72.06 x 72.06 x 19.25 [1830 x 1830 x 489]	<a href="#">72ZYFW</a>	\$1,175.00	<a href="#">PDF</a>
<a href="#">HN4FS727224SS</a>	\$9,681.00	72.06 x 72.06 x 25.25 [1830 x 1830 x 641]	<a href="#">72ZYFW</a>	\$1,175.00	<a href="#">PDF</a>
<a href="#">HN4FS904820SS</a>	\$8,381.00	90.06 x 48.06 x 21.25 [2288 x 1221 x 540]	<a href="#">90BFW</a>	\$1,048.00	<a href="#">PDF</a>
<a href="#">HN4FS907220SS</a>	\$10,573.00	90.06 x 72.06 x 21.25 [2288 x 1830 x 540]	<a href="#">90BYFW</a>	\$1,417.00	<a href="#">PDF</a>
<a href="#">HN4FS907224SS</a>	\$11,113.00	90.06 x 72.06 x 25.25 [2288 x 1830 x 641]	<a href="#">90BYFW</a>	\$1,417.00	<a href="#">PDF</a>
<a href="#">HN4FS907236SS</a>	\$12,786.00	90.06 x 72.06 x 37.25 [2288 x 1830 x 946]	<a href="#">90BYFW</a>	\$1,417.00	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding Dual Access



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Heavy-duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges
- Dual Access versions have doors front and back.
- 3-point 316 stainless steel padlocking door handle.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the subpanel.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 3R, 4X, and 12
- CSA Type 3R, 4, 4X, and 12 [File LR21001]
- Complies with:
  - NEMA Type 3R, 4X, 12, and 13
  - IEC 60529, IP66



## NEMA 3R, 4X, 12, and 13 Stainless Steel Freestanding Two-Door Dual Access


Part Number	Price	Enclosure Size HxWxD	Subpanel	Price	Drawing Link
<a href="#">HN4FS724824DASS</a>	\$8,765.00	72.06 x 48.06 x 26.43 [1830 x 1221 x 671]	<a href="#">72ZWFW</a>	\$892.00	<a href="#">PDF</a>
<a href="#">HN4FS726024DASS</a>	\$9,865.00	72.06 x 60.06 x 26.43 [1830 x 1526 x 671]	<a href="#">72ZXFW</a>	\$1,035.00	<a href="#">PDF</a>
<a href="#">HN4FS726036DASS</a>	\$11,341.00	72.06 x 60.06 x 38.43 [1830 x 1526 x 976]	<a href="#">72ZXFW</a>	\$1,035.00	<a href="#">PDF</a>
<a href="#">HN4FS727224DASS</a>	\$10,937.00	72.06 x 72.06 x 26.43 [1830 x 1830 x 671]	<a href="#">72ZYFW</a>	\$1,175.00	<a href="#">PDF</a>
<a href="#">HN4FS907224DASS</a>	\$12,556.00	90.06 x 72.06 x 26.43 [2288 x 1830 x 671]	<a href="#">90BYFW</a>	\$1,417.00	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top



powder coating.



## Features

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for larger free-standing applications.
- Sloped top prevents water from resting on top as well as providing potential for controls mounting.

## Construction

- Formed 12-gauge 304 or 316L stainless steel.
- Continuously welded seams are ground smooth.
- Flange trough collar around door opening excludes flowing liquids and contaminants.
- Heavy-duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with bullet style, heavy-duty, lift off hinges.
- Panel supports are provided.
- Center post is removable, providing easy panel installation.
- Heavy-duty three point latching mechanism with heavy-duty roller ends is provided for ease of door closing.
- Uses 1/4 turn latch handles.
- Seamless poured-in-place gasket
- Stainless steel door handles are complete with padlock hasp.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.
- Cover and enclosure are natural stainless steel with a smooth, brushed finish.
- Subpanel is finished in white

## Listings

- UL 508A Type 3R, 4, and 4X [UL File E65324]
- Complies with
  - NEMA Type 3R, 4, 4X, and 12
  - IEC 60529, IP66



## NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Freestanding with Slope Top

304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Drawing Link
<a href="#">2STFS747512SS</a>	\$15,226.00	<a href="#">2STFS747512S16</a>	\$17,019.00	78.54 x 75.13 x 15.58 [1995 x 1908 x 396]	<a href="#">PDF</a>
<a href="#">2STFS747518SS</a>	\$16,595.00	<a href="#">2STFS747518S16</a>	\$18,554.00	80.72 x 75.13 x 22.38 [2050 x 1908 x 568]	<a href="#">PDF</a>
<a href="#">2STFS747524SS</a>	\$17,872.00	<a href="#">2STFS747524S16</a>	\$19,986.00	82.91 x 75.13 x 29.17 [2106 x 1908 x 741]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Enclosure Accessories

## Locks and Latches



### 1/4-Turn Latch Handles



#### Features

- Durable zinc diecast or stainless steel.
- Removable handle stop for clockwise / counter-clockwise operation.
- Textured powder coat Black finish on zinc cast handle.
- Maintains NEMA rating of enclosure.
- Padlock "trigger" design for security requirements.
- Optional key lock or defeater available. Key lock versions include two keys.

1/4-Turn Latch Handles							
Part Number	Price	Security Type	Latch Points	Material	Finish	For Use With These Hammond Enclosures Only	Drawing Link
<a href="#">MHK1</a>	\$127.00	padlocking	1	die-cast zinc	black matte	single-door NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD1</a>	\$133.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1</a>	\$144.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2</a>	\$217.00	padlocking	3	die-cast zinc	black matte	less than 60in (H) NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD2</a>	\$228.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2</a>	\$246.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3</a>	\$221.00	padlocking	3	die-cast zinc	black matte	60in (H) or greater NEMA 4 and NEMA 12	<a href="#">PDF</a>
<a href="#">MHKD3</a>	\$232.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3</a>	\$251.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK1SS</a>	\$234.00	padlocking	1	316 stainless steel	#4 brush	single-door NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD1SS</a>	\$258.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL1SS</a>	\$258.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK2SS</a>	\$249.00	padlocking	3	316 stainless steel	#4 brush	less than 60in (H) NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD2SS</a>	\$274.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL2SS</a>	\$274.00	combination keylocking/ padlocking					<a href="#">PDF</a>
<a href="#">MHK3SS</a>	\$362.00	padlocking	3	316 stainless steel	#4 brush	60in (H) or greater NEMA 4X	<a href="#">PDF</a>
<a href="#">MHKD3SS</a>	\$398.00	padlocking with defeater					<a href="#">PDF</a>
<a href="#">MHKL3SS</a>	\$398.00	combination keylocking/ padlocking					<a href="#">PDF</a>