

# Disconnect Handle Applications for Freestanding and Floor-Mount Painted Steel Disconnect Enclosures



Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F\_SO\_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C.** Requires operator adapter plate kit **AKU**.
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft). Requires operator adapter plate kit **AKU**.
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9FOCA-15A, BW9FOCA-20A, BW9FOGA-15A, BW9FOGA-20A, BW9FOHA-15A, BW9FOHA-20A, BW9FOJA-15A, and BW9FOJA-20A.** Requires operator adapter panel kit **AKU**.

## Available at AutomationDirect.com

Disconnect Enclosure Series	AutomationDirect F_SO_C Series	Socomec 37299002 & 37299003	Fuji BW9F Series
<b>2U D_FFTC Series</b>	✓	✓	✓
<b>2UDPC_FFTC Series</b>	✓	✓	✓
<b>UHD_FFTC Series</b>	✓	✓	✓
Note: Each of these Disconnect enclosures requires an AKU Operator Adapter Kit from AutomationDirect.			


## Designed to house other brands

- Allen-Bradley Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. Requires operator adapter plate kit **AKU**.
- Allen-Bradley** Bulletin 1494F flange-mounted disconnect switches and Bulletin 149D flange-mounted operators for circuit breakers. Requires operator adapter plate kit **AK1494FD**.
- ABB** Controls flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers. Requires operator adapter plate kit **AKU**.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers. Requires operator adapter plate kit **AKU**.
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers. Requires operator adapter plate kit **AKU**.
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers. Requires operator adapter plate kit **AKU**.
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices. Requires operator adapter plate kit **AKU**.

## Other Brands

Disconnect Enclosure Series	Square D 9422 Series	Allen-Bradley 1494F & 1494D Series*	Allen-Bradley 1494V & 140U Series	ABB Controls	Eaton/Cutler-Hammer C361 & C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
<b>2U_FFTC Series</b>	✓	✓	✓	✓	✓	✓	✓
<b>2UDPC_FFTC Series</b>	✓	✓	✓	✓	✓	✓	✓
<b>UHD_FFTC Series</b>	✓	✓	✓	✓	✓	✓	✓
Note: Each of these Disconnect enclosures requires an AKU Operator Adapter Kit from AutomationDirect. *Requires AK1494FD Adapter Kit from AutomationDirect.							

# NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Freestanding Disconnect



*Note: Disconnect switches, circuit breakers and operators are not provided with the enclosure, and must be ordered separately from the manufacturer.*

## Applications

Designed to house the following safety disconnect equipment:

- ABB Controls flange mounted variable depth operating mechanisms for disconnect switches and circuit breakers.
- Allen Bradley 1494V and 1494U variable depth flange mounted disconnect switches and circuit breaker mechanisms. NOT COMPATIBLE WITH 1494V-R1, R2, W2 operating handles nor with Allen Bradley 1494F flange mounted disconnect switches and 1494D flange mounted operators for circuit breakers.
- C-H Westinghouse type C361 disconnect switches and operator mechanism. Cutler Hammer Type C371 circuit breaker operating mechanisms. Flex-Shaft™ handle operators for circuit breakers.
- General Electric type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers. Also Spectra-Flex™ cable operators for circuit breakers.
- Siemens I-T-E Max-Flex™ flange mounted variable depth operating handles for disconnect switches and circuit breakers.
- Square D disconnect switches and circuit breakers used with Class 9422 flange mounted variable depth operating mechanisms or cable mechanisms. These enclosures will not receive Class 9422 bracket mounted disconnect devices or class 9422TG1 or TG2 devices. NOT COMPATIBLE WITH Class 9422 bracket mounted devices nor Class 9422TG1/TG2 devices.

## Construction

- Formed from 12 gauge 304 stainless steel with smooth, continuously welded seams.
- Body stiffeners are provided in the larger enclosures for extra rigidity.
- Flange trough collar (FTC) around door opening excludes liquids and contaminants.
- Heavy duty lifting eyes are anchored into reinforced top corners.
- Removable doors are secured with heavy duty lift-off hinges.
- Formed 10 gauge steel subpanels are provided on collar studs.
- Panel supports are provided.

- Center post is removable, providing easy panel installation.
- Heavy duty 3-point latching mechanism with heavy duty roller ends is provided for ease of door closing.
- Oil-resistant gaskets are permanently secured.
- The right-hand door on all enclosures is the master door.
- Master door handle complete with screw defeater and padlock hasp.
- Slave door handle complete with padlock hasp.
- A mechanical interlock activated by the master door prevents the auxiliary door from being opened first.
- The pre-installed flange cutout provides mounting for disconnect operators (verify compatibility in advance) - interlock hardware included with enclosure.
- A provision for mounting fluorescent lighting is provided.
- A bonding stud is provided in the door, and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided for the inside of the door.

## Finish

- Door and enclosure are natural stainless steel with a #4 smooth, brushed finish..
- Subpanel(s) is finished RAL 9003 white powder coating.

## Listings

- UL 508A Type 4, 12 and 13 [UL File E65324]
- CSA Type 4, 12 and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4, 4X, 12 and 13
  - IEC 60529, IP54
- Appropriate components are required to maintain these standards.



# NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Freestanding Disconnect



## Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

## Single-Door

Part Number	Price	Enclosure Size HxWxD	Included Subpanel HxW	Drawing Link
<a href="#">1UHD722918N4SS</a>	\$6,070.00	72.13 x 28.50 x 19.35 [1832 x 724 x 491]	60.00 x 21.75 [1524 x 552]	<a href="#">PDF</a>
<a href="#">1UHD723518N4SS</a>	\$6,736.00	72.13 x 28.75 x 19.35 [1832 x 730 x 491]	60.00 x 27.75 [1524 x 705]	<a href="#">PDF</a>
<a href="#">1UHD724118N4SS</a>	\$7,409.00	72.13 x 34.75 x 19.35 [1832 x 883 x 491]	60.00 x 33.75 [1524 x 857]	<a href="#">PDF</a>
<a href="#">1UHD844118N4SS</a>	\$8,207.00	84.13 x 40.75 x 19.35 [2137 x 1035 x 491]	72.00 x 33.75 [1829 x 857]	<a href="#">PDF</a>
<a href="#">1UHD844124N4SS</a>	\$8,353.00	84.13 x 40.75 x 25.35 [2137 x 1035 x 644]	72.00 x 33.75 [1829 x 857]	<a href="#">PDF</a>
<a href="#">1UHD904118N4SS</a>	\$8,682.00	90.13 x 40.75 x 19.35 [2289 x 1035 x 491]	78.00 x 33.75 [1981 x 857]	<a href="#">PDF</a>
<a href="#">1UHD904120N4SS</a>	\$8,886.00	90.13 x 40.75 x 21.35 [2289 x 1035 x 542]	78.00 x 33.75 [1981 x 857]	<a href="#">PDF</a>
<a href="#">1UHD904124N4SS</a>	\$9,428.00	90.13 x 40.75 x 25.35 [2289 x 1035 x 644]	78.00 x 33.75 [1981 x 857]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Double-Door

Part Number	Price	Enclosure Size HxWxD	Included Subpanel HxW	Drawing Link
<a href="#">2UHD725518N4SS</a>	\$10,681.00	72.13 x 40.75 x 19.35 [1832 x 1035 x 491]	60.00 x 48.00 [1524 x 1219]	<a href="#">PDF</a>
<a href="#">2UHD726718N4SS</a>	\$12,020.00	72.13 x 55.00 x 19.35 [1832 x 1397 x 491]	60.00 x 60.00 [1524 x 1524]	<a href="#">PDF</a>
<a href="#">2UHD727918N4SS</a>	\$13,386.00	72.13 x 67.00 x 19.35 [1832 x 1702 x 491]	60.00 x 72.00 [1524 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD727924N4SS</a>	\$14,322.00	72.13 x 79.00 x 25.35 [1832 x 2007 x 644]	60.00 x 72.00 [1524 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD847918N4SS</a>	\$14,803.00	84.13 x 79.00 x 19.35 [2137 x 2007 x 491]	72.00 x 72.00 [1829 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD847924N4SS</a>	\$15,278.00	84.13 x 79.00 x 25.35 [2137 x 2007 x 644]	72.00 x 72.00 [1829 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD907918N4SS</a>	\$15,641.00	90.13 x 79.00 x 19.35 [2289 x 2007 x 491]	78.00 x 72.00 [1981 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD907920N4SS</a>	\$15,912.00	90.13 x 79.00 x 21.35 [2289 x 2007 x 542]	78.00 x 72.00 [1981 x 1829]	<a href="#">PDF</a>
<a href="#">2UHD907924N4SS</a>	\$16,617.00	90.13 x 79.00 x 25.35 [2289 x 2007 x 644]	78.00 x 72.00 [1981 x 1829]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Three-Door

Part Number	Price	Enclosure Size HxWxD	Included Subpanel 1 HxW	Included Subpanel 2 HxW	Drawing Link
<a href="#">3UHD7210118N4SS</a>	\$16,387.00	72.13 x 100.25 x 19.35 [1832 x 2546 x 491]	60.00 x 72.00 [1524 x 1829]	60.00 x 27.75 [1524 x 705]	<a href="#">PDF</a>
<a href="#">3UHD7211918N4SS</a>	\$18,451.00	72.13 x 118.25 x 19.35 [1832 x 3004 x 491]	60.00 x 72.00 [1524 x 1829]	60.00 x 33.75 [1524 x 857]	<a href="#">PDF</a>
<a href="#">3UHD8411918N4SS</a>	\$20,543.00	84.13 x 118.25 x 19.35 [2137 x 3004 x 491]	72.00 x 72.00 [1829 x 1829]	72.00 x 33.75 [1829 x 857]	<a href="#">PDF</a>
<a href="#">3UHD8411924N4SS</a>	\$21,176.00	84.13 x 118.25 x 25.35 [2137 x 3004 x 644]	72.00 x 72.00 [1829 x 1829]	72.00 x 33.75 [1829 x 857]	<a href="#">PDF</a>
<a href="#">3UHD9011924N4SS</a>	\$22,931.00	90.13 x 118.25 x 25.35 [2289 x 3004 x 644]	72.00 x 72.00 [1829 x 1829]	72.00 x 33.75 [1829 x 857]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Four-Door

Part Number	Price	Enclosure Size HxWxD	Included Subpanels HxW	Drawing Link
<a href="#">4UHD8415718N4SS</a>	\$23,464.00	84.13 x 156.50 x 19.35 [2137 x 3975 x 491]	(2) 72.00 x 72.00 [1829 x 1829]	<a href="#">PDF</a>
<a href="#">4UHD9015718N4SS</a>	\$28,360.00	90.13 x 156.50 x 19.35 [2289 x 3975 x 491]	(2) 72.00 x 72.00 [1829 x 1829]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 3R, 4, 4X, 12 and 13 Stainless Steel Freestanding Disconnect



## Dimensions

