

# NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

## Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws fasten into threaded, sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see drawings).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Natural stainless steel with a #4 smooth brushed finish.

## Listings

- UL 508A Type 4 and 4X [UL File E65324]
- CSA Type 4 and 4X [CSA File LR21001]
- Complies with
  - NEMA Type 4 and 4X
  - IEC 60529, IP66
- All appropriate components are required to maintain these standards.



## NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton


304 Stainless Steel		316 Stainless Steel				Console Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged		
22 mm	Price	30 mm	Price	22 mm	Price						30 mm	Price
<a href="#">1437MSSA</a>	\$216.00	<a href="#">1437SSA</a>	\$211.00	<a href="#">1437MS16A</a>	\$281.00	<a href="#">1437S16A</a>	\$260.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	<a href="#">PDF</a>	1	16	No
<a href="#">1437MSSB</a>	\$265.00	<a href="#">1437SSB</a>	\$258.00	<a href="#">1437MS16B</a>	\$345.00	<a href="#">1437S16B</a>	\$319.00	6.31 x 4.31 x 4.92 [160 x 109 x 125]	<a href="#">PDF</a>	2	14	Yes
<a href="#">1437MSSC</a>	\$307.00	<a href="#">1437SSC</a>	\$299.00	<a href="#">1437MS16C</a>	\$400.00	<a href="#">1437S16C</a>	\$370.00	8.31 x 4.31 x 4.92 [211 x 109 x 125]	<a href="#">PDF</a>	3		
<a href="#">1437MSSD</a>	\$345.00	<a href="#">1437SSD</a>	\$336.00	<a href="#">1437MS16D</a>	\$451.00	<a href="#">1437S16D</a>	\$416.00	10.31 x 4.31 x 4.92 [262 x 109 x 125]	<a href="#">PDF</a>	4		
—	—	<a href="#">1437SSS</a>	\$659.00	—	—	<a href="#">1437S16S</a>	\$787.00	12.06 x 11.06 x 4.92 [306 x 281 x 125]	<a href="#">PDF</a>	16		

Note: Dimensions in inches [millimeters].


# NEMA 4 and 4X Extra Deep Stainless Steel Pushbutton



## Dimensions



### 22 mm [0.87in] Hole Placement



### 30 mm [1.18in] Hole Placement

