

# NEMA 12 and 13 Small Continuous Hinge Wall Mount



## Applications

Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Provides protection from dust, dirt, oil, and water.

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, Types 12 and 13 [UL Files E6924]
- CSA Certified, Type 12 [CSA File LL66078]
- NEMA/EEMAC Types 12 and 13
- JIC EL-1-71




## Construction

- Bodies fabricated from 14 gauge steel
- Doors fabricated from 16 gauge steel
- Continuously welded seams ground smooth, less knockouts or holes
- Lids are sealed with closed cell oil resistant neoprene gasket
- External mounting plates, top and bottom of enclosure
- Weldnuts provided for mounting optional subpanels securely on models 6"x4" and larger
- External screw clamps are quick and easy to operate
- Standard continuous hinge
- Grounding provisions provided

## Dimensions

in [mm]



### NOTES:

1. PANELS ARE 14GA STEEL.
2. PANEL SCREWS ARE #10-32 PAN HEAD.
3. TWO CLAMPS ARE USED IF W=8" OR MORE.

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# NEMA 12 and 13 Small Continuous Hinge Wall Mount

Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

NEMA 12 and 13 Small Continuous Hinge Wall Mount					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Steel Subpanel
<b>B040403CH</b>	\$32.50	4x4x3 [102x102x76]	–	–	–
<b>B040404CH</b>	\$37.50	4x4x4 [102x102x102]	–	–	–
<b>B060403CH</b>	\$37.00	6x4x3 [152x102x76]	<b>P0604</b>	<b>P0604SS</b>	<b>P0604G</b>
<b>B060404CH</b>	\$39.50	6x4x4 [152x102x102]	<b>P0604</b>	<b>P0604SS</b>	<b>P0604G</b>
<b>B060604CH</b>	\$40.00	6x6x4 [152x152x102]	<b>P0606</b>	<b>P0606SS</b>	<b>P0606G</b>
<b>B080603CH</b>	\$46.00	8x6x3.50 [203x152x89]	<b>P0806</b>	<b>P0806SS</b>	<b>P0806G</b>
<b>B080606CH</b>	\$59.00	8x6x6 [203x152x152]	<b>P0806</b>	<b>P0806SS</b>	<b>P0806G</b>
<b>B080804CH</b>	\$52.00	8x8x4 [203x203x102]	<b>P0808</b>	–	<b>P0808G</b>
<b>B100804CH</b>	\$52.00	10x8x4 [254x203x102]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>B100804CHS</b>	\$64.00	8x10x4 [203x254x102]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>B100806CH</b>	\$64.00	10x8x6 [254x203x152]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>B101006CH</b>	\$79.00	10x10x6 [254x254x152]	<b>P1010</b>	–	<b>P1010G</b>
<b>B120604CH</b>	\$61.00	12x6x4 [305x152x102]	<b>P1206</b>	–	<b>P1206G</b>
<b>B121005CH</b>	\$81.00	12x10x5 [305x254x127]	<b>P1210</b>	<b>P1210SS</b>	<b>P1210G</b>
<b>B121005CHS</b>	\$81.00	10x12x5 [254x305x127]	<b>P1210</b>	<b>P1210SS</b>	<b>P1210G</b>
<b>B121008CH</b>	\$96.00	12x10x8 [305x254x203]	<b>P1210</b>	<b>P1210SS</b>	<b>P1210G</b>
<b>B121206CH</b>	\$85.00	12x12x6 [305x305x152]	<b>P1212</b>	<b>P1212SS</b>	<b>P1212G</b>
<b>B140806CH</b>	\$84.00	14x8x6 [356x203x152]	<b>P1408</b>	–	<b>P1408G</b>
<b>B141206CH</b>	\$92.00	14x12x6 [356x305x152]	<b>P1412</b>	<b>P1412SS</b>	<b>P1412G</b>
<b>B141206CHS</b>	\$102.00	12x14x6 [305x356x152]	<b>P1412</b>	<b>P1412SS</b>	<b>P1412G</b>
<b>B141208CH</b>	\$114.00	14x12x8 [356x305x203]	<b>P1412</b>	<b>P1412SS</b>	<b>P1412G</b>
<b>B161006CH</b>	\$100.00	16x10x6 [406x254x152]	<b>P1610</b>	–	<b>P1610G</b>
<b>B161406CH</b>	\$100.00	16x14x6 [406x356x152]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>
<b>B161406CHS</b>	\$120.00	14x16x6 [356x406x152]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>
<b>B161408CH</b>	\$120.00	16x14x8 [406x356x203]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>
<b>B161410CH</b>	\$147.00	16x14x10 [406x356x254]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>

Note: Subpanels must be ordered separately. Dimensions in inches [millimeters]; letters in table correspond to letters on dimensional drawings.

# Enclosure Subpanels



## Subpanels

Subpanels are not included with most enclosures and must be purchased separately. The specifications table for each enclosure family lists the part number of the subpanel that goes with each enclosure.

## Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14 gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B\_CH, BN4, BN4\_CH, BN4\_CHQT, BN4\_SS, BN4\_CHSS, BN4\_CHSSA, BN4\_CHQTSS, BN4\_CHQTSSA ("\_" refers to dimensions).




Subpanels for B and BN4 Enclosures							
Painted Steel	Price	304 Stainless Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
P0604	\$3.00	P0604SS	\$10.75	P0604G	\$3.00	6 x 4	4.88 x 2.88 [124 x 73]
P0606	\$3.25	P0606SS	\$13.25	P0606G	\$3.25	6 x 6	4.88 x 4.88 [124 x 124]
P0806	\$4.00	P0806SS	\$15.50	P0806G	\$4.00	8 x 6	6.88 x 4.88 [175 x 124]
P0808	\$4.75	-		P0808G	\$4.75	8 x 8	6.88 x 6.88 [175 x 175]
P1008	\$5.25	P1008SS	\$22.50	P1008G	\$5.25	10 x 8	8.88 x 6.88 [226 x 175]
P1010	\$7.25	-		P1010G	\$7.25	10 x 10	8.88 x 8.88 [226 x 226]
P1206	\$5.75	-		P1206G	\$5.75	12 x 6	10.88 x 4.88 [276 x 124]
P1210	\$7.50	P1210SS	\$30.00	P1210G	\$7.50	12 x 10	10.88 x 8.88 [276 x 226]
P1212	\$9.00	P1212SS	\$37.50	P1212G	\$9.00	12 x 12	10.88 x 10.88 [276 x 276]
P1408	\$8.00	-		P1408G	\$8.00	14 x 8	12.88 x 6.88 [327 x 175]
P1412	\$9.75	P1412SS	\$43.00	P1412G	\$9.75	14 x 12	12.88 x 10.88 [327 x 276]
P1610	\$10.75	-		P1610G	\$10.75	16 x 10	14.88 x 8.88 [378 x 226]
P1614	\$12.00	P1614SS	\$57.00	P1614G	\$12.00	16 x 14	14.88 x 12.88 [378 x 327]

*Notes: Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawing.*

## Dimensions

in [mm]



Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.