

22mm Pushbutton NEMA 12 and 13 Wall Mount



Applications

Designed to hold all standard 22mm brands of miniature oil-tight pushbuttons, switches and pilot lights. Provide protection from dirt, dust, oil and water.

Construction

- Fabricated from 14 gauge steel
- Closed cell oil-resistant neoprene gasket
- Continuously welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 6 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508, Types 12 & 13 [UL File E64791]
- CSA Certified, Types 12 & 13 [CSA File LL66078]
- NEMA/EEMAC Types 12 & 13

Enclosure Shipping Schedule

Same day	1 - 7 days
----------	------------

Color indicates shipping lead time in business days.


22mm Pushbutton NEMA 12 and 13 Wall Mount			
Part Number	Price	# Holes	Size HxWxD
PBGX1	\$43.00	1	3.56 x 3.06 x 3.83 [90 x 78 x 97]
PBGX2	\$49.00	2	5.44 x 3.06 x 3.83 [138 x 78 x 97]
PBGX3	\$55.00	3	7.31 x 3.06 x 3.83 [186 x 78 x 97]
PBGX4	\$67.00	4	9.19 x 3.06 x 3.83 [233 x 78 x 97]
PBGX6	\$83.00	6	8.81 x 5.31 x 4.58 [224 x 135 x 116]
PBGX9	\$93.00	9	8.81 x 6.81 x 4.58 [224 x 173 x 116]
PBGX12	\$103.00	12	10.69 x 6.81 x 4.58 [272 x 173 x 116]
PBGX20	\$114.00	20	12.56 x 8.31 x 4.58 [319 x 211 x 116]
PBGX25	\$123.00	25	12.56 x 9.81 x 4.58 [319 x 249 x 116]

*Notes: Dimensions in inches [millimeters]
Letters in table correspond to letters on dimensional drawings.*


22mm Pushbutton NEMA 12 and 13 Wall Mount



Dimensions



PBGX HOLE ARRANGEMENTS



See our website: www.AutomationDirect.com for complete engineering drawings.