

# 22mm Pushbutton NEMA 12 and 13 Wall-Mount



## Applications

Designed to hold all standard 22mm brands of miniature oil-tight pushbuttons, switches and pilot lights. Provide protection from dirt, dust, oil and water.

## Construction

- Fabricated from 14 gauge steel
- Closed cell oil-resistant neoprene gasket
- Continuously welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" miniature pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 6 or more holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

## Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces

## Listings

- UL 508, Types 12 & 13 [UL File E64791]
- NEMA/EEMAC Types 12 & 13



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## 22mm Pushbutton NEMA 12 and 13 Wall-Mount


Part Number	Price	# Holes	Size HxWxD
<a href="#">PBGX1</a>	\$71.00	1	3.56 x 3.06 x 3.83 [90 x 78 x 97]
<a href="#">PBGX2</a>	\$74.00	2	5.44 x 3.06 x 3.83 [138 x 78 x 97]
<a href="#">PBGX3</a>	\$89.00	3	7.31 x 3.06 x 3.83 [186 x 78 x 97]
<a href="#">PBGX4</a>	\$98.00	4	9.19 x 3.06 x 3.83 [233 x 78 x 97]
<a href="#">PBGX6</a>	\$124.00	6	8.81 x 5.31 x 4.58 [224 x 135 x 116]
<a href="#">PBGX9</a>	\$166.00	9	8.81 x 6.81 x 4.58 [224 x 173 x 116]
<a href="#">PBGX12</a>	\$153.00	12	10.69 x 6.81 x 4.58 [272 x 173 x 116]
<a href="#">PBGX20</a>	\$169.00	20	12.56 x 8.31 x 4.58 [319 x 211 x 116]
<a href="#">PBGX25</a>	\$184.00	25	12.56 x 9.81 x 4.58 [319 x 249 x 116]

Note: Dimensions in inches [millimeters].

# 22mm Pushbutton NEMA 12 and 13 Wall-Mount



## Dimensions



### PBGX HOLE ARRANGEMENTS

