


# 30mm Pushbutton NEMA 4, 4X, 12 and 13 Wall Mount



## Application

Designed to hold standard 30mm pushbuttons, switches, and pilot lights. Provides protection from dirt, dust, oil and water. Also used in areas where serious corrosion problems exist.

internal detachable hinges to hold cover open during service, yet permit quick removal

## Finish

- Stainless steel cover and outside of enclosure have #3 intermediate polished finish

## Construction

- Fabricated from 14 gauge 304 stainless steel
- Continuously welded seams ground smooth
- Cover secured by stainless steel captive screws threaded into sealed wells
- Closed cell oil-resistant neoprene gasket
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches, and pilot lights
- External mounting plate on top and bottom of enclosure
- Grounding provisions provided
- PBSS Enclosures with 6 or more holes have

## Listings

- UL 508, Types 4, 4X, 12 and 13 [UL file E64791]
- NEMA/EEMAC Types 4, 4X, 12 and 13




Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.


30mm Pushbutton NEMA 4, 4X, 12 and 13 Stainless Steel Wall Mount					
304 Stainless Steel	Price	316L Stainless Steel	Price	# Holes	Enclosure Size HxWxD
<b>PBSS1</b>	\$125.00	<b>PBSS1A</b>	\$159.00	1	3.75 x 3.56 x 3.01 [95 x 90 x 76]
<b>PBSS2</b>	\$148.00	<b>PBSS2A</b>	\$188.00	2	6.00 x 3.56 x 3.01 [152 x 90 x 76]
<b>PBSS3</b>	\$171.00	<b>PBSS3A</b>	\$217.00	3	8.25 x 3.56 x 3.01 [230 x 90 x 76]
<b>PBSS4</b>	\$199.00	<b>PBSS4A</b>	\$246.00	4	10.50 x 3.56 x 3.01 [267 x 90 x 76]
<b>PBSS6</b>	\$262.00	<b>PBSS6A</b>	\$325.00	6	9.75 x 6.56 x 3.29 [248 x 167 x 84]
<b>PBSS9</b>	\$311.00	<b>PBSS9A</b>	\$385.00	9	9.75 x 8.81 x 3.29 [248 x 224 x 84]
<b>PBSS12</b>	\$356.00	<b>PBSS12A</b>	\$441.00	12	12.00 x 8.81 x 3.29 [305 x 224 x 84]

Note: Dimensions in inches [millimeters].

## Dimensions



PBSS HOLE ARRANGEMENTS



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.