


# 30mm Pushbutton NEMA 4, 4X, 12 and 13 Wall-Mount



## Application

Designed to hold standard 30mm pushbuttons, switches, and pilot lights. Provides protection from dirt, dust, oil and water. Also used in areas where serious corrosion problems exist.

## Finish

- Stainless steel cover and outside of enclosure have #3 intermediate polished finish

## Listings

- UL 508, Types 4, 4X, 12 and 13 [UL file E64791]
- NEMA/EEMAC Types 4, 4X, 12 and 13



## Construction

- Fabricated from 14 gauge 304 stainless steel
- Continuously welded seams ground smooth
- Cover secured by stainless steel captive screws threaded into sealed wells
- Closed cell oil-resistant neoprene gasket
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches, and pilot lights
- External mounting plate on top and bottom of enclosure
- Grounding provisions provided
- PBSS Enclosures with 6 or more holes have internal detachable hinges to hold cover open during service, yet permit quick removal

### Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------


Color indicates shipping lead time in business days.

### 30mm Pushbutton NEMA 4, 4X, 12 and 13 Stainless Steel Wall-Mount

304 Stainless Steel	Price	316L Stainless Steel	Price	# Holes	Enclosure Size HxWxD
<b>PBSS1</b>	\$130.00	<b>PBSS1A</b>	\$165.00	1	3.75 x 3.56 x 3.01 [95 x 90 x 76]
<b>PBSS2</b>	\$154.00	<b>PBSS2A</b>	\$196.00	2	6.00 x 3.56 x 3.01 [152 x 90 x 76]
<b>PBSS3</b>	\$178.00	<b>PBSS3A</b>	\$226.00	3	8.25 x 3.56 x 3.01 [230 x 90 x 76]
<b>PBSS4</b>	\$207.00	<b>PBSS4A</b>	\$256.00	4	10.50 x 3.56 x 3.01 [267 x 90 x 76]
<b>PBSS6</b>	\$273.00	<b>PBSS6A</b>	\$338.00	6	9.75 x 6.56 x 3.29 [248 x 167 x 84]
<b>PBSS9</b>	\$324.00	<b>PBSS9A</b>	\$455.00	9	9.75 x 8.81 x 3.29 [248 x 224 x 84]
<b>PBSS12</b>	\$371.00	<b>PBSS12A</b>	\$521.00	12	12.00 x 8.81 x 3.29 [305 x 224 x 84]

Note: Dimensions in inches [millimeters].

## Dimensions



PBSS HOLE ARRANGEMENTS

