

# NEMA 1 Small Single-Door Wall-Mount 1/4-Turn Latch



## Applications

Designed for use as control enclosures and instrument cases in areas not requiring oil-tight and dust-tight specifications.

## Construction

- Bodies and doors fabricated from 14- or 16- gauge steel
- Continuous hinged door
- Weldnuts provided for mounting optional subpanels
- Doors furnished standard with flush-mount quarter-turn latch, which can be operated by a coin or screwdriver
- Mounting holes on back of enclosure
- Grounding provisions provided
- Uses N1C14 series latches

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surface
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels are a conductive finish (unpainted)

## Listings

- UL 50, 1 [UL File E6924]
- NEMA/EEMAC 1



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## NEMA 1 Small Single-Door Wall-Mount with 1/4-Turn Latch


Part Number	Price	Body/ Door/ Gauge	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel
<a href="#">N1C060604</a>	\$60.00	16/16	6.50 x 6.50 x 4.14 [165 x 165 x 105]	<a href="#">N1P0606</a>	<a href="#">N1P0606G</a>	<a href="#">N1P0606PP</a>
<a href="#">N1C060804</a>	\$65.00	16/16	8.50 x 6.50 x 4.14 [216 x 165 x 105]	<a href="#">N1P0608</a>	<a href="#">N1P0608G</a>	<a href="#">N1P0608PP</a>
<a href="#">N1C060806</a>	\$70.00	16/16	8.50 x 6.50 x 6.14 [216 x 165 x 156]	<a href="#">N1P0608</a>	<a href="#">N1P0608G</a>	<a href="#">N1P0608PP</a>
<a href="#">N1C080804</a>	\$72.00	16/16	8.50 x 8.50 x 4.14 [216 x 216 x 105]	<a href="#">N1P0808</a>	<a href="#">N1P0808G</a>	<a href="#">N1P0808PP</a>
<a href="#">N1C080806</a>	\$81.00	16/16	8.50 x 8.50 x 6.14 [216 x 216 x 156]	<a href="#">N1P0808</a>	<a href="#">N1P0808G</a>	<a href="#">N1P0808PP</a>
<a href="#">N1C081004</a>	\$79.00	16/16	10.50 x 8.50 x 4.14 [267 x 216 x 105]	<a href="#">N1P0810</a>	<a href="#">N1P0810G</a>	<a href="#">N1P0810PP</a>
<a href="#">N1C081006</a>	\$90.00	16/16	10.50 x 8.50 x 6.14 [267 x 216 x 156]	<a href="#">N1P0810</a>	<a href="#">N1P0810G</a>	<a href="#">N1P0810PP</a>
<a href="#">N1C101004</a>	\$87.00	16/16	10.50 x 10.50 x 4.14 [267 x 267 x 105]	<a href="#">N1P1010</a>	<a href="#">N1P1010G</a>	<a href="#">N1P1010PP</a>
<a href="#">N1C101006</a>	\$99.00	16/16	10.50 x 10.50 x 6.14 [267 x 267 x 156]	<a href="#">N1P1010</a>	<a href="#">N1P1010G</a>	<a href="#">N1P1010PP</a>
<a href="#">N1C101204</a>	\$96.00	16/16	12.50 x 10.50 x 4.14 [318 x 267 x 105]	<a href="#">N1P1012</a>	<a href="#">N1P1012G</a>	<a href="#">N1P1012PP</a>
<a href="#">N1C101206</a>	\$108.00	16/16	12.50 x 10.50 x 6.14 [318 x 267 x 156]	<a href="#">N1P1012</a>	<a href="#">N1P1012G</a>	<a href="#">N1P1012PP</a>
<a href="#">N1C121204</a>	\$105.00	16/16	12.50 x 12.50 x 4.14 [318 x 318 x 105]	<a href="#">N1P1212</a>	<a href="#">N1P1212G</a>	<a href="#">N1P1212PP</a>
<a href="#">N1C121206</a>	\$119.00	16/16	12.50 x 12.50 x 6.14 [318 x 318 x 156]	<a href="#">N1P1212</a>	<a href="#">N1P1212G</a>	<a href="#">N1P1212PP</a>
<a href="#">N1C121208</a>	\$133.00	16/16	12.50 x 12.50 x 8.14 [318 x 318 x 207]	<a href="#">N1P1212</a>	<a href="#">N1P1212G</a>	<a href="#">N1P1212PP</a>
<a href="#">N1C121404</a>	\$113.00	16/16	14.50 x 12.50 x 4.14 [368 x 318 x 105]	<a href="#">N1P1214</a>	<a href="#">N1P1214G</a>	<a href="#">N1P1214PP</a>
<a href="#">N1C121406</a>	\$129.00	16/16	14.50 x 12.50 x 6.14 [368 x 318 x 156]	<a href="#">N1P1214</a>	<a href="#">N1P1214G</a>	<a href="#">N1P1214PP</a>
<a href="#">N1C121408</a>	\$144.00	14/14	14.50 x 12.50 x 8.14 [368 x 318 x 207]	<a href="#">N1P1214</a>	<a href="#">N1P1214G</a>	<a href="#">N1P1214PP</a>
<a href="#">N1C121606S</a>	\$140.00	16/16	16.50 x 12.50 x 6.14 [419 x 318 x 156]	<a href="#">N1P1216</a>	<a href="#">N1P1216G</a>	<a href="#">N1P1216PP</a>
<a href="#">N1C122006</a>	\$161.00	14/14	20.50 x 12.50 x 6.14 [521 x 318 x 156]	<a href="#">N1P1220</a>	<a href="#">N1P1220G</a>	<a href="#">N1P1220PP</a>

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].

# NEMA 1 Small Single-Door Wall-Mount 1/4-Turn Latch



## Dimensions



# Enclosure Subpanels



## Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14-gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
  - NEMA 1 small (N1C)
  - NEMA 3R small (RHC)
  - NEMA 12 WA\_GIE



### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.


### Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

Painted Steel	Price	Galvanized	Price	Perforated	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<a href="#">N1P0606</a>	\$5.00	<a href="#">N1P0606G</a>	\$5.00	<a href="#">N1P0606PP</a>	\$6.50	6 x 6	4.25 x 4.25 [108 x 108]
<a href="#">N1P0608</a>	\$5.75	<a href="#">N1P0608G</a>	\$5.75	<a href="#">N1P0608PP</a>	\$6.75	6 x 8	6.25 x 4.25 [159 x 108]
<a href="#">N1P0808</a>	\$6.75	<a href="#">N1P0808G</a>	\$6.75	<a href="#">N1P0808PP</a>	\$8.00	8 x 8	6.25 x 6.25 [159 x 159]
<a href="#">N1P0810</a>	\$8.00	<a href="#">N1P0810G</a>	\$8.00	<a href="#">N1P0810PP</a>	\$9.25	8 x 10	8.25 x 6.25 [210 x 159]
<a href="#">N1P1010</a>	\$9.50	<a href="#">N1P1010G</a>	\$9.50	<a href="#">N1P1010PP</a>	\$10.75	10 x 10	8.25 x 8.25 [210 x 210]
<a href="#">N1P1012</a>	\$11.00	<a href="#">N1P1012G</a>	\$11.00	<a href="#">N1P1012PP</a>	\$12.75	10 x 12	10.25 x 8.25 [260 x 210]
<a href="#">N1P1212</a>	\$13.25	<a href="#">N1P1212G</a>	\$13.25	<a href="#">N1P1212PP</a>	\$15.00	12 x 12	10.25 x 10.25 [260 x 260]
<a href="#">N1P1214</a>	\$14.75	<a href="#">N1P1214G</a>	\$14.75	<a href="#">N1P1214PP</a>	\$17.00	12 x 14	12.25 x 10.25 [311 x 260]
<a href="#">N1P1216</a>	\$16.50	<a href="#">N1P1216G</a>	\$16.50	<a href="#">N1P1216PP</a>	\$19.75	12 x 16	14.25 x 10.25 [362 x 260]
<a href="#">N1P1220</a>	\$23.00	<a href="#">N1P1220G</a>	\$23.00	<a href="#">N1P1220PP</a>	\$26.00	12 x 20	18.25 x 10.25 [464 x 260]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

## Dimensions



Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.