



HydroMode™ Potable Water Push-to-Connect Fittings

HydroMode push-to-connect plug fitting with acetel body and synthetic rubber o-ring. Five fittings per package.



| HydroMode™ Plug | | | | | | | | |
|---|--------|-------------|-----------|------|------|------|----------------------|---------------|
| <i>Inch Sizes - dimensions in millimeters (mm) unless otherwise noted</i> | | | | | | | | |
| Part No. | Price | Size (inch) | ØD (inch) | ØP | A | L | Package Weight (lbs) | Qty. per pack |
| PLUG14-P | \$2.50 | 1/4 in. | 1/4 | 13.0 | 21.0 | 24.5 | 0.1 | 5 |
| PLUG38-P | \$2.75 | 3/8 in. | 3/8 | 18.0 | 26.0 | 30.0 | 0.1 | 5 |

HydroMode push-to-connect union elbow fitting with acetel body and synthetic rubber o-ring. For use with polyethylene and other flexible tubing. Five fittings per package.




| HydroMode™ Union Elbow | | | | | | | | | | | |
|---|---------|---------------------|------------|------------|------|------|------|------|------|----------------------|---------------|
| <i>Inch Sizes - dimensions in millimeters (mm) unless otherwise noted</i> | | | | | | | | | | | |
| Part No. | Price | Size (inch) | ØD1 (inch) | ØD2 (inch) | B1 | B2 | ØE | L | H | Package Weight (lbs) | Qty. per pack |
| UL532-P | \$5.50 | 5/32 in. x 5/32 in. | 5/32 | 5/32 | 14.7 | 14.7 | 13.2 | 24.5 | 24.5 | 0.1 | 5 |
| UL14-P | \$6.50 | 1/4 in. x 1/4 in. | 1/4 | 1/4 | 16.9 | 16.9 | 15.5 | 28.8 | 28.8 | 0.1 | 5 |
| UL516-P | \$7.50 | 5/16 in. x 5/16 in. | 5/16 | 5/16 | 17.5 | 17.5 | 17.6 | 30.7 | 30.7 | 0.1 | 5 |
| UL38-P | \$9.75 | 3/8 in. x 3/8 in. | 3/8 | 3/8 | 20.2 | 20.2 | 20.0 | 35.9 | 35.9 | 0.1 | 5 |
| UL12-P | \$12.00 | 1/2 in. x 1/2 in. | 1/2 | 1/2 | 25.1 | 25.1 | 23.0 | 43.4 | 43.4 | 0.2 | 5 |

HydroMode™ Potable Water Push-to-Connect Fittings

HydroMode push-to-connect fittings are designed to work with potable water and beverages. Installing or removing flexible tubing is quick and easy. All fittings are made of NSF approved materials with NSF-51® and NSF-61® certifications. The body and collet of the fittings are made from polyoxymethylene (POM) also known as acetal, while the o-rings are made from ethylene propylene diene monomer (EPDM) which is a type of synthetic rubber.

Features

- Designed for potable water and beverages
- NSF-51 and NSF-61 certified
- Easy tubing installation and removal
- Optional retaining clips prevent accidental tube removal
- Fittings rated for up to 145psi at 70°C (158°F)



*Push-to-Connect Fitting
Cut-away Diagram*