

NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount



Applications

These two-door enclosures provide industry-leading protection for systems incorporating large components or complex configurations in highly corrosive environments. It is typically used in the following areas: food processing plants, pharmaceutical manufacturing facilities, petrochemical plants, pulp and paper processing, and waste water treatment facilities.



Construction

- Bodies and doors fabricated from 12 gauge 304 stainless steel
- Continuously welded seams ground smooth
- X-type body stiffeners are included for extra strength
- Rolled lip around three sides of door and along top of enclosure opening excludes liquids and contaminants from entering
- Quick and easy to operate stainless steel door clamps around three sides of doors are provided
- Heavy gauge stainless steel continuous hinges are provided
- Doors are removable by pulling stainless steel continuous hinge pin
- Hasp and staple are provided for padlocking
- Print pocket is provided
- Standard 12" high floor kits are welded to bottom of enclosure
- Heavy duty removable lifting eyes
- Doors are sealed with poured in place polyurethane gasket
- Grounding provisions provided
- Easily removable center post permits easy panel installations
- Collar studs for mounting optional subpanels
- Uses WAN4XRA clamp

Finish

- Enclosures have a smooth grained finish on all exterior surfaces

Listings

- UL 508, Types 4, 4X and 12 [UL file E64791]
- Meets NEMA/EEMAC Types 4, 4X and 12 requirements



Note: For current listings, please see www.Automationdirect.com

Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount Enclosures



Part Number	Price	Enclosure SizeHxWxD[not incl. 12" legs]	Painted Steel Subpanel	Galvanized Subpanel
SSN4D624812	\$7,856.00	62.12 x 48.12 x 12.12 [1578 x 1222 x 308]	NPDD6048	NPDD6048G
SSN4D626012	\$7,954.00	62.12 x 60.12 x 12.12 [1578 x 1527 x 308]	NPDD6060	NPDD6060G
SSN4D746012	\$9,416.00	74.12 x 60.12 x 12.12 [1883 x 1527 x 308]	NPDD7260	NPDD7260G
SSN4D747212	\$9,802.00	74.12 x 72.12 x 12.12 [1883 x 1832 x 308]	NPDD7272	—
SSN4D747224	\$12,494.00	74.12 x 72.12 x 24.12 [1883 x 1832 x 613]	NPDD7272	—

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount



Dimensions



Enclosure Subpanels



Subpanels for Double-door Floor Mount Enclosures

- Subpanels are fabricated from 10 gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor mount enclosures and some double-door wall-mount enclosures



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Double-door Floor Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<u>NPDD4242</u>	\$228.00	<u>NPDD4242G</u>	\$247.00	42 x 42	39.00 x 39.00 [991 x 991]
<u>NPDD4260</u>	\$334.00	<u>NPDD4260G</u>	\$334.00	42 x 60	38.00 x 56.00 [965 x 1422]
<u>NPDD4842</u>	\$258.00	<u>NPDD4842G</u>	\$258.00	48 x 42	45.00 x 39.00 [1143 x 991]
<u>NPDD4848</u>	\$309.00	<u>NPDD4848G</u>	\$309.00	48 x 48	44.00 x 44.00 [1118 x 1118]
<u>NPDD5442</u>	\$276.00	<u>NPDD5442G</u>	\$276.00	54 x 42	50.00 x 38.00 [1270 x 965]
<u>NPDD6048</u>	\$375.00	<u>NPDD6048G</u>	\$375.00	60 x 48	44.00 x 56.00 [1118 x 1422]
<u>NPDD6060</u>	\$463.00	<u>NPDD6060G</u>	\$463.00	60 x 60	56.00 x 56.00 [1422 x 1422]
<u>NPDD7260</u>	\$552.00	<u>NPDD7260G</u>	\$552.00	72 x 60	56.00 x 68.00 [1422 x 1727]
<u>NPDD7272</u>	\$658.00	—	—	72 x 72	68.00 x 68.00 [1727 x 1727]

Notes: Dimensions in inches [millimeters].
 Letters in table correspond to letters on dimensional drawing.
 *Some floor mount enclosures may be up to 2 inches [51mm] taller than height listed in this table.
 Disconnect enclosures will be up to 2 inches [51 mm] wider than width dimensions listed in this table.

Dimensions

