

IDEM CPR, CMR, and CMR-F Heavy Duty Non-Contact Magnetic Safety Switches



CPR Series Plastic Housing

CMR Series Stainless Steel Housing

CMR-F Series Stainless Steel Housing Rear Mount

- Slim 20mm wide housing can be fitted into narrow channels
- Can be high-pressure hosed at high temperature - IP69K rated
- Wide 12 mm sensing, high tolerance to misalignment
- High switching capability - up to 2A
- Will operate with most safety relays
- Codes are not unique and can be used with other models of the same series
- Available with 2m, 5m, or 10m cable or 250mm pigtail with quick-disconnect cable

CMR Series, CMR-F Only

- Specifically designed for food processing applications
- Suitable for CIP SIP cleaning - Food Splash Zones per EHEDG guidelines
- 316 Stainless steel mirror polished finish

CMR-F Only

- Same as CMR series, but with no-food-trap housing - rear mounting holes
- 5m cable only

See Dimensions later in this section.

Actuator Operating Direction



CPR, CMR
CMR-F

| CPR, CMR, and CMR-F Non-Contact Magnetic Safety Switches | | | | | |
|--|----------|-----------------|--------------|------------|-----------------------|
| Part Number | Price | Body Material | Cable Length | Circuits | Contact Type / Rating |
| Pigtail Version | | | | | |
| CPR-113013 | \$100.00 | Plastic | 2m | 1 NC, 1 NO | Heavy duty / 2A |
| CPR-113014 | \$111.00 | | 5m | | |
| CPR-113015 | \$121.00 | | 10m | | |
| CMR-138030 | \$145.00 | Stainless steel | 5m | | |
| CMR-138031 | \$158.00 | | 10m | | |
| CMR-F-135030 | \$145.00 | | 5m | | |
| Quick Disconnect Version (M12 8-pin) | | | | | |
| CPR-113008 | \$145.00 | Plastic | 250mm | 1 NC, 1 NO | Heavy duty / 2A |
| CMR-138024 | \$184.00 | Stainless steel | 250mm | | |

| Female Quick Disconnect Lead | | | |
|------------------------------|---------|----------------|------------------------|
| Part Number | Price | Description | Exit Type/Cable Length |
| 140101 | \$32.00 | Female QD Lead | M12 Female 5m, 8-pin |
| 140102 | \$50.00 | | M12 Female 10m, 8-pin |




IDEM CPR, CMR, and CMR-F Heavy Duty Non-Contact Magnetic Safety Switches

Dimensions


mm [inch]

CPR Series

Pigtail



Quick Disconnect



SEE OUR WEBSITE: WWW.AUTOMATIONDIRECT.COM FOR COMPLETE ENGINEERING DRAWINGS.


IDEM CPR, CMR, and CMR-F Heavy Duty Non-Contact Magnetic Safety Switches

Dimensions

mm [inch]

CMR-F Series

Pigtail



SEE OUR WEBSITE: WWW.AUTOMATIONDIRECT.COM FOR COMPLETE ENGINEERING DRAWINGS.


IDEM CPR, CMR, and CMR-F Heavy Duty Non-Contact Magnetic Safety Switches

Dimensions


mm [inch]

CMR Series

Pigtail



Quick Disconnect




SEE OUR WEBSITE: WWW.AUTOMATIONDIRECT.COM FOR COMPLETE ENGINEERING DRAWINGS.

IDEM Non-Contact Safety Switches Electrical Connections and Dimensions


Electrical Connections

Magnetic Switches




| Magnetic Switches - Electrical Connections | | |
|--|------------|------------------------------------|
| Quick Disconnect Connector Pin Out | Lead Color | Type of Circuit (Actuator Present) |
| 4 | Yellow | NO |
| 6 | Green | NO |
| 7 | Black | NC2 |
| 1 | White | NC2 |
| 2 | Red | NC1 |
| 3 | Blue | NC1 |

Coded Magnetic and RFID Switches



| Coded Magnetic Switches - Electrical Connections | | | |
|--|------------|------------------------------------|----------------------------------|
| Quick Disconnect Connector Pin Out | Lead Color | Type of Circuit (Actuator Present) | Output Types (Solid State) |
| 8 | Orange | Auxiliary (NO) | 200 mA max. 24 VDC |
| 5 | Brown | Auxiliary (NO) | |
| 4 | Yellow | NC2 + | 200 mA max. 24 VDC (Optocoupler) |
| 6 | Green | NC2 - | |
| 7 | Black | NC1 + | 200 mA max. 24 VDC (Optocoupler) |
| 1 | White | NC1 - | |
| 2 | Red | Supply +24 VDC | Supply 24 VDC +10% / -15% |
| 3 | Blue | Supply 0VDC | |

Connection Colors




Pin View from Switch
M12 Male

IDEM Non-Contact Safety Switches Specifications

| Non-contact Safety Switches Specifications | | | |
|---|---|-------------------------------------|------------------------------------|
| | Non-Contact Magnetic Switches | Non-Contact Coded Magnetic Switches | Non-Contact RFID Coded Switches |
| Safety Classification and Reliability Data | | | |
| Switching Reliability (B10d) | 3.3 x 10 ⁶ operations at 100 mA load | | No mechanical parts implemented |
| ISO 13849-1 | Up to category 4 with safety relay | | |
| ISO 13849-1 | Up to PLe depending upon system architecture | | |
| EN 62061 | Up to SIL3 depending upon system architecture | | |
| Safety Data - Annual Usage | 8 cycles per hour / 24 hours per day / 365 days | | |
| PFHd | 2.8 x 10 ⁻¹⁰ | 2.6 x 10 ⁻¹⁰ | 4.77 x 10 ⁻¹⁰ |
| Proof Test Interval (Life) | 20 Years | | |
| MTTFd | 866 Years | | 1100 years |
| Agency Approvals | CE, cULus | | |
| Electrical and General Specifications | | | |
| Contact Ratings: Safety Contact NC | MPR: Voltage free: 250 VAC, 0.5 A Max. | | 24 VDC, 0.2A Max. (Optocoupler) |
| | LPR, LMR, SPR, SMR, SMR-F: Voltage free: 250 VAC, 1.0A Max. | | |
| | CPR, CMR, CMR-F, WPR: Voltage free: 250 VAC, 2.0A Max. | | |
| Contact Ratings: Monitoring (Auxiliary) Contact NO | Voltage free: 24 VDC, 0.2A Max. | | 24 VDC, 0.2A Max. |
| Recommended Fuses (NC Circuits) | MPR: Fuse externally 0.4A (F) | | NA |
| | LPR, LMR, SPR, SMR, SMR-F, CMR, CMR-F: Fuse externally 0.8A (F) | | |
| | CPR, WPR: Fuse externally 1.6A (F) | | |
| Contact Release Time | <2ms | | NA |
| Initial Contact Resistance | <500 milliohm | | NA |
| Minimum Switched Current | 10 VDC, 1mA | | |
| Dielectric Withstand | 250 VAC | | |
| Insulation Resistance | 100 Megohms | | |
| Recommended Setting Gap | 5mm | | |
| NC Switching Distance | Sao (assured ON) 8mm close; Sar (assured OFF) 20 mm open | | |
| NC Switching Operation | For all switches the NC circuits are closed when the guard is closed and the actuator is present. | | |
| NO Switching Operation | Opens before NC circuits close | | |
| Tolerance to Misalignment | 5mm in any direction from 5mm setting gap (See Misalignment Range drawing on this page) | | |
| Switching Frequency | 1.0 Hz Max. | | |
| Approach Speed | 200 mm per minute to 1000 mm per second | | |
| Body Material - Polyester | CPR, LPR, MPR, SPR, WPR | CPC, LPC, MPC, SPC, WPC | LPF, SPF |
| Body Material - 316 Stainless Steel | CMR, CMR-F, LMR, SMR, SMR-F | CMC, CMC-F, LMC, SMC, SMC-F | NA |
| Operating Temperature Range | Polyester: -25° to +80°C (-13° to +176° F) | | |
| | 316 Stainless Steel: -25° to +105° C (-13° to +221° F) | | NA |
| Storage Temperature (Low) | -55° to -40° C (-67° to -40° F) | | |
| Enclosure Protection | IP67, IP69K | | |
| Shock Resistance | IEC 68-2-27 11 ms 30g | | |
| Vibration Resistance | IEC 68-2-6 10-55 Hz 1mm | | |
| Cable Type | PVC, 6.5 mm outside diameter max. | | PVC, 6mm outer diameter max. |
| Mounting Bolts (recommended) | 2 x M4; Tightening torque: 1.0 Nm | | |

Note: Always mount onto non-Ferrous materials.



Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application. AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.