

# DIN Rail Receptacles

## Overview

The FA-REC3 is a 3-outlet straight blade AC receptacle, 15A, 125 VAC used for powering laptop computers and test equipment. This unit can be mounted on 35mm, 32mm, or 15mm DIN rail.




## Specifications

Part Number	FA-REC3
Price	
Output Voltage	125 VAC
Configuration	NEMA 5-15
Output Current	15A maximum
Total Current	Must not exceed 15A if all outlets are used
GFCI	None
Number of Phases	1
Number of Poles	2
Number of Wires	3
Mounting	35mm DIN rail 32mm DIN rail 15mm DIN rail
Wire Capacity	14-12 AWG solid or stranded [2.5-4.0 mm <sup>2</sup> ]
Screw Torque	0.5 N·m [4.4 lbf·in]
Operating Temperature	0 to 60 °C [32 to 140 °F]
Circuit Protection	None
Housing Material	Plastic
Agency Approvals	cULus E139594

## Dimensions

inches [mm]



See our website: [www.automationdirect.com](http://www.automationdirect.com) for complete engineering drawings.

# DIN Rail Receptacles

## Overview

Straight blade AC receptacles are 35mm DIN Rail or panel mounted used for powering laptop computers and test equipment. The [FA-REC2](#) is a standard 125 VAC, 15A receptacle and [FA-GFCI](#) is a 125 VAC, 15A Ground-Fault Circuit Interrupter.




FA-GFCI

Specifications		
Part Number	FA-REC2	FA-GFCI
Price		
Output Voltage	125 VAC	
Configuration	NEMA 5-15	
Output Current	15A maximum	
Mounting	Panel mount or 35mm DIN rail	
Number of Phases	1	
Number of Poles	2	
Number of Wires	3	
Wire Capacity	14–12 AWG solid or stranded [2.5–4.0 mm <sup>2</sup> ]	
Wire Strip Length	6–7 mm	
Tightening Torque	0.51 N·m [4.5 lbf·in]	
Operating Temperature	0 to 60 °C [32 to 140 °F]	
Circuit Protection	None	Ground-fault circuit interruption
Wire Type	Copper or Copper Clad	
Housing Material	PA66/6, Nylon	
Weight	180g [6.35 oz]	230g [8.11 oz]
Agency Approvals	cULus E139594	

## Dimensions

inches [mm]



See our website: [www.automationdirect.com](http://www.automationdirect.com) for complete engineering drawings.