



Wiring Accessories

Crimping Tools

Crimping Tools			
Part Number	Description	Weight	Price
<u>K70ZA000113</u>	Crimping tool for use with single ferrules AWG 20 - 10 [0.5 - 6 mm ²] and twin ferrules AWG 2 x 18 - 2 x 12 [2 x 0.75 - 2 x 4 mm ²]. 5 crimping positions. With and without insulating collar. Conforms to DIN 46228 part 1 and 2.	0.74 lb [335g]	
<u>K70ZA000117</u>	Crimping tool for use with single ferrules AWG 10 - 4 [6 - 25 mm ²] and twin ferrules AWG 2 x 12 - 2 x 8 [2 x 4 - 2 x 10 mm ²]. 4 crimping positions. Conforms to DIN 46228 part 1 and 4.	1.19 lb [540g]	
<u>K70ZA000118</u>	Crimping tool for use with single ferrules AWG 2 - 1 [35 - 50 mm ²] and twin ferrules AWG 2 x 6 [2 x 16 mm ²]. 2 crimping positions. Conforms to DIN 46228 part 1 and 4.	1.19 lb [540g]	
<u>K70ZA000130</u>	Crimping tool for PVC-insulated terminals AWG 20 - 10 [0.5 - 6 mm ²]. 3 crimping positions.	1.12 lb [510g]	

[K70ZA000113](#)



[K70ZA000117](#)



Note: Z&F crimping tools recommended by the ferrule manufacturer before terminating in terminal blocks, wire connectors, or end-product terminals (such as starters, etc.).

Crimping Tools Cross Reference					
	Part Number		<u>K70ZA000113</u>	<u>K70ZA000117</u>	<u>K70ZA000118</u>
	Standard	DIN			
Single Ferrules	<u>V30AE000006</u>	<u>V30AE000038</u>	X	—	—
	<u>V30AE000009</u>	<u>V30AE000041</u>	X	—	—
	<u>V30AE000013</u>	<u>V30AE000045</u>	X	—	—
	<u>V30AE000016</u>	<u>V30AE000048</u>	X	—	—
	<u>V30AE000017</u>	<u>V30AE000049</u>	X	—	—
	<u>V30AE000052</u>	<u>V30AE000052</u>	X	—	—
	<u>V30AE000053</u>	<u>V30AE000053</u>	X	—	—
	<u>V30AE000055</u>	<u>V30AE000055</u>	X	—	—
	<u>V30AE000056</u>	<u>V30AE000056</u>	X	—	—
	<u>V30AE000025</u>	<u>V30AE000058</u>	X	X	—
	<u>V30AE000026</u>	<u>V30AE000059</u>	X	X	—
	<u>V30AE000027</u>	<u>V30AE000060</u>	—	X	—
	<u>V30AE000028</u>	<u>V30AE000061</u>	—	X	—
	<u>V30AE000029</u>	<u>V30AE000062</u>	—	X	—
	<u>V30AE000030</u>	<u>V30AE000063</u>	—	X	—
	<u>V30AE000031</u>	<u>V30AE000064</u>	—	X	—
	<u>V30AE000033</u>	<u>V30AE000067</u>	—	—	X
	<u>V30AE000035</u>	<u>V30AE000070</u>	—	—	X
Twin Ferrules	<u>V30AE001134</u>	<u>V30AE001145</u>	X	—	—
	<u>V30AE000606</u>	<u>V30AE000607</u>	X	—	—
	<u>V30AE000733</u>	<u>V30AE000734</u>	X	—	—
	<u>V30AE000608</u>	<u>V30AE000609</u>	X	—	—
	<u>V30AE000735</u>	<u>V30AE000736</u>	X	—	—
	<u>V30AE000623</u>	<u>V30AE000625</u>	X	—	—
	<u>V30AE000737</u>	<u>V30AE000738</u>	X	—	—
	<u>V30AE000611</u>	<u>V30AE000611</u>	X	—	—
	<u>V30AE000748</u>	<u>V30AE000748</u>	X	—	—
	<u>V30AE001148</u>	<u>V30AE001148</u>	X	X	—
	<u>V30AE001139</u>	<u>V30AE001150</u>	—	X	—
	<u>V30AE001141</u>	<u>V30AE001152</u>	—	X	—
	<u>V30AE001143</u>	<u>V30AE001154</u>	—	—	X

[K70ZA000118](#)



[K70ZA000130](#)



Wiring Accessories – Crimping Tools

Crimping Tools Overview

Our high-quality industrial crimping tools are designed to crimp a wide range of insulated and non-insulated crimping terminals, ferrules, and connectors. They feature ergonomic handles and controlled-cycle ratcheting mechanisms to guarantee a uniform crimp every time. Choose from fixed or interchangeable die tools or tool/die sets with multiple dies.

Interchangeable-Die Crimping Tools			
Part #	Description *	Qty	Price
<u>DN-CT-HDL</u>	Crimping tool handle for DN-CT-Dx dies (dies NOT included) Approximate dimensions: 9.75 x 2.52 x 0.95 in (234 x 64 x 24 mm); 16.2 oz (460g)	1	
<u>DN-CT-D1</u>	Die set for <u>DN-CT-HDL</u> : 26-22 & 12-10 AWG (0.1-0.4 & 4-6 mm ²) green & yellow insulated terminals	1	
<u>DN-CT-D2</u>	Die set for <u>DN-CT-HDL</u> : 22-14 AWG (0.5-2.5 mm ²) red & blue insulated terminals	1	
<u>DN-CT-D3</u>	Die set for <u>DN-CT-HDL</u> : 22-10 AWG (0.5-6 mm ²) non-insulated terminals	1	
<u>DN-CT-D4</u>	Die set for <u>DN-CT-HDL</u> : 24-8 AWG (0.25-10 mm ²) wire ferrules	1	
<u>DN-CT-D5</u>	Die set for <u>DN-CT-HDL</u> : 6-4 AWG (16-25 mm ²) wire ferrules	1	
<u>DN-CT-D6</u>	Die set for <u>DN-CT-HDL</u> : 2-1/0 AWG (35-50 mm ²) wire ferrules	1	
<u>DN-CT-D7</u>	Die set for <u>DN-CT-HDL</u> : 22-10 AWG (0.5-6 mm ²) open barrel non-insulated terminals	1	
<u>DN-CT-D8</u>	Die set for <u>DN-CT-HDL</u> : 8-pin (RJ45) modular plugs	1	
<u>DN-CT-D9</u>	Die set for <u>DN-CT-HDL</u> : 6-pin (RJ11/RJ12) modular plugs	1	
<u>DN-CT-SET</u>	Crimping tool modular system; includes handle and three die sets (<u>DN-CT-HDL</u> + <u>DN-CT-D2</u> + <u>DN-CT-D4</u> + <u>DN-CT-D5</u>) The die pairs are held together for easy handling, and interchange without separate tools.	1	

* The DN-CT-xx series features a crimping tool with multiple interchangeable dies separately available. The die pairs are held together for easy handling, and can be interchanged without separate tools.



DN-CT-HDL
Crimping Tool



DN-CT-SET
Crimping Tool & Die Set


Wiring Accessories – Crimping Tool

DN-CT-Dx Interchangeable Crimping Dies (for DN-CT-xxx crimping tool only)


These dies are held together for easy handling, and can be interchanged without additional tools.

All DN-CT-Dx dies have been tested on leading brands of connectors to ensure quality connections.


Dies come in modular holders that can be connected together when not in use.




DN-CT-Dx die & holder



DN-CT-D1 (4300-3128)
Insulated Terminals & Connectors
26–22 AWG & 12–10 AWG
[Green & Yellow] (0.1–0.4 & 4–6 mm²)




DN-CT-D2 (4300-3129)
Insulated Terminals & Connectors
22–14 AWG
[Red & Blue] (0.5–2.5 mm²)




DN-CT-D3 (4300-3142)
Non-Insulated Terminals & Connectors
22–10 AWG (0.5–6 mm²)



DN-CT-D4 (4300-3127)
Wire Ferrules
24–8 AWG (0.25–10 mm²)




DN-CT-D5 (4300-3153)
Wire Ferrules
6–4 AWG (16–25 mm²)




DN-CT-D6 (4300-3154)
Wire Ferrules
2–1/0 AWG (35–50 mm²)




DN-CT-D7 (4300-3146)
Non-Insulated Open-Barrel Terminals
22–10 AWG (0.5–6 mm²)



DN-CT-D8 (4300-3144)
8-pin Modular Plugs
RJ45



DN-CT-D9 (4300-3132)
6-pin Modular Plugs
RJ11/RJ12



Wiring Accessories – Self-Adjusting Crimping Tools

Lightweight, compact, comfortable and self-adjusting tool for crimping ferrules/wire end sleeves.


Features

- Ratchet (with emergency release) to ensure crimps are completed according to specification
- Well balanced to avoid slipping out of the hand
- Non-slip grip pad for applying pressure against a surface
- Ergonomically shaped handles with hardness and surface textures selected for comfortable frequent use
- Low handle force for larger ferrule sizes
- Compact and light-weight design for easy access within confined spaces
- Hole for attaching a safety strap
- Square or Hexagonal crimp profile

Self-Adjusting Crimping Tools Specifications	
Connectors	Insulated and non-insulated ferrules/wire end sleeves
Capacity	0.14 - 10.0 mm²/AWG 26-8
Crimp Length	Up to 0.47 in [12mm]
Lifespan	Tested to 50,000 cycles
Length	6.93 in [176mm]
Width	1.02 in [26mm]
Height	2.44 in [62mm]
Handle spread (closed)	1.81 in [46mm]
Handle spread (open)	5.59 in [142mm]
Weight	Square: 0.80 lb [362g] Hexagonal: 0.81 lb [371g]

Self-Adjusting Crimping Tools		
Part Number	Description	Price
DN-FE-16S	Wire crimping tool, self-adjusting, square profile, 26 to 8 AWG capacity. For use with insulated and non-insulated wire ferrules.	
DN-FE-16H	Wire crimping tool, self-adjusting, hexagonal profile, 26 to 8 AWG capacity. For use with insulated and non-insulated wire ferrules.	

The finished square and hexagonal crimps have the same cross-sectional area. Choosing between the square and hexagonal crimp tools depends on the shape of the hole where the wire will be inserted. Square crimps fit better in rectangular holes while hexagonal crimps fit better in round holes.



Wiring Accessories – Self-Adjusting Crimping Tool with Rotatable Die

Lightweight, compact, comfortable and self-adjusting tool for crimping ferrules/wire end sleeves



DN-FE-16T



DN-FE-16T in Side Crimp Setting



DN-FE-16T in Front Crimp Setting

Features

- Rotatable die for front or side crimping
- Ratchet (with emergency release) to ensure crimps are completed according to specification
- Well balanced to avoid slipping out of the hand
- Non-slip grip pad for applying pressure against a surface
- Ergonomically shaped handles with hardness and surface textures selected for comfortable frequent use
- Low handle force for larger ferrule sizes
- Compact and light-weight design for easy access within confined spaces
- Hole for attaching a safety strap
- Trapezoidal crimp profile

Self-Adjusting Crimping Tool with Rotatable Die Specifications	
Connectors	Insulated and non-insulated ferrules/wire end sleeves
Capacity	0.14 - 10.0 mm ² / AWG 26-8
Crimp Length	Up to 0.47 in [12mm]
Lifespan	Tested to 50,000 cycles
Length	7.09 in [180mm]
Width	1.02 in [26mm]
Height	2.56 in [65mm]
Handle spread (closed)	1.81 in [46mm]
Handle spread (open)	5.31 in [135mm]
Weight	0.66 lb [300g]

Self-Adjusting Crimping Tools		
Part Number	Description	Price
DN-FE-16T	Wire crimping tool, self-adjusting, rotatable die, trapezoidal profile, 26 to 8 AWG capacity. For use with insulated and non-insulated wire ferrules.	



Wiring Accessories – Cutting & Stripping Tools

Wire Cutting and Stripping Tools

Wire Cutting and Stripping Tools			
Part Number	Description	Qty	Price
<u>DN-WS</u>	Cutting and stripping tool with replaceable blades and jaw inserts; includes (1) <u>DN-WSJ</u> blade Approximate dimensions: 7.5 x 4.8 x 0.8 in [191 x 123 x 20 mm]; Weight: 4.8 oz (136g)	1	
<u>DN-WSJ</u>	<u>DN-WS</u> replacement straight-blade insert; for PVC insulations; 34-8 AWG [0.02-10 mm ²]	1	
<u>DN-WSMMC</u>	<u>DN-WS</u> 16 mm ² blade insert; 10-5 AWG [4-16 mm ²]	1	
<u>DN-WSVBC</u>	<u>DN-WS</u> V-blade insert; for harder insulations such as PTFE & PVC; 28-12 AWG [0.1-4 mm ²]	1	
<u>DN-WSRJ</u>	<u>DN-WS</u> replacement jaw inserts	2	
<u>DN-CST</u>	Cable stripping tool; cable diameters 0.1-0.43 in [2.5-11 mm] with insulation up to 0.04 in [1.0 mm] thick Approximate dimensions: 3.6 x 1.6 x 0.8 in [90.5 x 39.5 x 19 mm]; Weight: 0.9 oz [28g]	1	
<u>DN-CST-BLADE</u>	<u>DN-CST</u> replacement blade	1	

Self-Adjusting Cut and Strip Tool **DN-WS**


- Widest stripping capacity of any tool of its type
- Easily interchangeable stripping cassettes are available for stripping a wide range of most modern insulation types, from PVC to PTFE; color coded by stripping blade type
- No additional tools required to change stripping blade cassettes
- Precise adjustability allows stripping of various insulation thicknesses without damage to conductors
- Easy snag-free wire removal after stripping
- Ergonomic design with soft-grip handle
- Light weight and strong; molded in high-strength plastic with twice the strength of standard nylon; tested 150k cycles
- Cutting capacity:
Stranded conductors to 8AWG (10 mm²)
Solid conductors to 16AWG (1.5 mm²)



DN-WS stripping blade replacement



DN-WS wire cutting




DN-WSxxx
Blade inserts color coded by type



DN-WSRJ

DN-WS Cutting & Stripping Tool



Cable Stripping Tool **DN-CST**

Small, simple, safe, and precise tool for removing insulation from copper and fiber optic audiovisual, data transmission, instrumentation, signal, and telephone cables.

- Precise: 9-position blade height adjustment wheel for fine adjustability and repeatability
- Easy to use: Squeeze the tool together to open the stripping cavity, insert cable, rotate once, and remove tool from cable. Separately pull scrap insulation off of cable.
- Safe: Smooth, rounded, pocketable, and lightweight design; no exposed blades
- Tough: Impact resistant nylon tested to over 50k cycles
- Economical: Replacement blades available
- Cable capacity: Ø 0.1-0.43 in [2.5-11 mm]
- Insulation thickness: Up to 0.04 in [1.0 mm]



DN-CST Precision Stripping Tool
[Squeeze, insert cable, rotate, & remove]

DN-CST-BLADE Replacement Blade



Precision Stripping Tool
Easily replaceable blade