

# Field Wireable Connectors

## M12 Field Wireable Screw Connectors

### Features

- IP67 rated once properly assembled
- Various cable gauges and diameters accepted
- Plastic housings with good resistance against chemicals and oils



Field Wireable M12 Screw Connectors								
Part Number	Price	Voltage	Poles	Connection Type	Conductor Wire	Housing Material	Outside Cable Ø	
7000-12701-0000000	\$7.75	250V AC/DC	4	Axial male	18AWG [0.75 mm <sup>2</sup> ] max	Polyamide (PA)	4 to 6 mm [0.157 to 0.236 in]	
7000-12721-0000000	\$9.50	125V AC/DC	5	Axial male				
7000-12901-0000000	\$7.75	250V AC/DC	4	Axial female				
7000-12921-0000000	\$9.50	125V AC/DC	5	Axial female				
7000-12741-0000000	\$7.75	250V AC/DC	4	Axial male				
7000-12761-0000000	\$9.50	125V AC/DC	5	Axial male				
7000-12941-0000000	\$7.75	250V AC/DC	4	Axial female			20AWG [0.5 mm <sup>2</sup> ] max	PUR
7000-12961-0000000	\$9.50	125V AC/DC	5	Axial female				
7000-12821-0000000	\$7.75	250V AC/DC	4	Right-angle male				
7000-12981-0000000	\$7.75	250V AC/DC	4	Right-angle female				
7000-13041-0000000	\$9.75	125V AC/DC	5	Right-angle female				
7000-17301-0000000	\$21.50	60V AC/DC	8	Axial male				
7000-17311-0000000	\$21.50	60V AC/DC	8	Right-angle male	20AWG [0.5 mm <sup>2</sup> ] max	PUR		
7000-17321-0000000	\$21.50	60V AC/DC	8	Axial female				
7000-17331-0000000	\$21.50	60V AC/DC	8	Right-angle female				
<b>Shielded</b>								
7000-14581-0000000	\$23.50	250V AC/DC	4	Right-angle male, D-coded	18AWG [0.75 mm <sup>2</sup> ] max	CuZn Nickel Plated	6 to 8 mm [0.236 to 0.315 in]	
7000-13321-0000000	\$19.50	125V AC/DC	5	Axial male				
7000-13361-0000000	\$25.50	125V AC/DC	5	Right-angle male				
7000-17341-0000000	\$25.50	60V AC/DC	8	Axial male				

NOTE: Dimensions for these connectors are located on the following drawing pages.

Specifications		
Outside Cable Ø (mm)	4.0 to 6.0	6.0 to 8.0
Nominal Voltage	4-pin: 250V 5-pin: 125V	4-pin: 250V 5-pin: 125V 8-pin: 60V
Current (max)	4A	4-pin and 5-pin: 4A 8-pin: 2A
Temperature	-25° to 85°C [13° to 185°F]	
Environmental Protection	IP67	
Isolation Materials	N/A	
Wire Diameter	N/A	
Isolation Resistance	Category III per IEC 60664-1	
Screw	M2.5x0.45 mm <sup>2</sup> torque to 40 N·m [29.5 ft·lb]	
Weight	0.05 oz [1.42 g]	0.06 oz [1.7 g]
Agency Approvals	UL Recognized. File E224242	








To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

# Field Wireable Connectors

## M12 Screw Connectors Dimensions and Wiring


### Wiring Diagrams

#### Screw Connection Technique




### Dimensions mm [in]


#### 7000-12701-000000




#### 7000-12721-000000




#### 7000-12901-000000




#### 7000-12921-000000




#### 7000-12741-000000




#### 7000-12761-000000



#### 7000-12941-000000



#### 7000-12961-000000




# Field Wireable Connectors


## M12 Screw Connectors Dimensions and Wiring

### Dimensions mm [in]


**7000-12821-000000**




**7000-12981-000000**




**7000-13041-000000**




**7000-13321-000000**




**7000-13361-000000**




**7000-17301-000000**




**7000-17311-000000**



**7000-17321-000000**



**7000-17331-000000**



**7000-17341-000000**

