

Connection Cables - Sensor and Signal

Shielded M12 A-coded Cable to Pigtail


Features

- Industry standard axial and 90-degree M12 screw-lock connectors with open leads
- Braided shield located inside the cord jacket and connected to the coupling nut
- 5m [16.4 ft] and 10m [32.8 ft] cable lengths
- PVC (polyvinyl chloride) jacketed cable for general use and chemical wash-down applications, ex. food & beverage industry
- PUR (polyurethane) jacketed cable for applications with exposure to oil and dynamic applications requiring more flexibility



Shielded M12 A-coded Cable to Pigtail											
Part Number	Price	Number of Wires	Connector	Cable Jacket/Wire Insulation Material	Jacket Color	Dimensions					
						A	B	C	L		
						mm			m [ft]		
7000-13201-3310500	\$28.50	4	Axial female	PUR-PVC/ PVC	Gray	43.5	15	-	5		
7000-13261-3310500	\$28.50		90-degree female			39	15	32	[16.4]		
7000-13201-3311000	\$44.00		Axial female			43.5	15	-	10		
7000-13261-3311000	\$44.00		90-degree female			39	15	32	[32.8]		
7000-13221-3490500	\$32.50	5	Axial female			PUR/PP	Gray	43.5	15	-	5
7000-13281-3490500	\$32.50		90-degree female					39	15	32	[16.4]
7000-13221-3491000	\$51.00		Axial female					43.5	15	-	10
7000-13281-3491000	\$51.00		90-degree female					39	15	32	[32.8]
7000-17121-2910500	\$50.00	8	Axial female	PUR/PP	Gray			44.5	15	-	5
7000-17141-2910500	\$50.00		90-degree female					39	15	32	[16.4]
7000-17121-2911000	\$71.00		Axial female					44.5	15	-	10
7000-17141-2911000	\$73.00		90-degree female					39	15	32	[32.8]
7000-17121-2940500	\$50.00		Axial female			44.5	15	-	5		
7000-17141-2940500	\$50.00		90-degree female			39	15	32	[16.4]		
7000-17121-2941000	\$76.00		Axial female			44.5	15	-	10		
7000-17141-2941000	\$76.00		90-degree female			39	15	32	[32.8]		

Dimensions




See our website: www.AutomationDirect.com for complete engineering drawings.

Connection Cables - Sensor and Signal

Shielded M12 A-coded Cable to Pigtail Specifications						
Model	13201	13261	13221	13281	17121	17141
Type	4-Wire, 5-Pole		5-Wire, 5-Pole		8-Wire, 8-Pole	
Max Voltage	60 VAC/VDC				30 VAC/VDC	
Max Voltage - UL Rating	30 VAC/VDC					
Max Current Per Contact	4A				2A	
Protection Degree	IP65 / IP66K / IP67					
Nut Material	Female threads are nickel plated die cast zinc					
Cable Jacket/Wire Insulation Material	PUR-PVC/PVC				PUR/PP	
Contacts Material	Copper Alloy					
Tightening Torque	0.6 N·m [0.44 ft·lb]					
Conductors Cross Section	0.34 mm ² [22AWG]				0.25 mm ² [24AWG]	
Ø Outer Cable	PUR-PVC/PVC 5.9 mm [0.23 in]				PUR/PP 7mm [0.28 in]	
Temperature Range - Stationary Use	-25 to 85°C [-13 to 185°F]			-40 to 80°C [-40 to 80°F]		
Temperature Range - Flexible Use	-5 to 70°C [23 to 158°F]				-25 to 80°C [-13 to 176°F]	
Min Bend Radius	Stationary use: 5 x cable diameter; Flexible use: 10 x cable diameter					
Approvals*	CE, UKCA, cCSAus				cULus, UKCA, cCSAus	

*To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Contact Diagrams



Wiring Diagrams

