

# marathon<sup>®</sup> Motors General Purpose, 1-phase, Totally Enclosed, 4-in-1<sup>®</sup> Motors



## C-Face Footed (Removable Base)

### Features

- Double-sealed ball bearings, mechanically locked on shaft ends
- Heavy gauge steel construction
- Bolt-on, removable rigid base
- Suitable for horizontal or vertical mounting
- Capacitor start/capacitor run design for higher efficiency
- 1.15 Service Factor (except as noted)
- Will accept brake kits (available from Marathon)
- Will accept drip cover kits (available from Marathon)
- UL recognized and CSA certified

### Applications

- Typical uses include machine tools, conveyors, packaging machines, batching machines, food and beverage equipment, pumps, and fans.

### Motor Shipping Schedule \*

Same or one day \*    Up to 7 days    Up to 10 days

Color indicates shipping lead time in business days. Check stock status online.

\* Certain heavy and oversized items can be shipped only via LTL.

Check our website for current shipping method constraints by part number.

### Motor Specifications – General Purpose, 1-phase, Totally Enclosed, 4-in-1 Motors

Part Number*	Price	HP	Base RPM	Volts	Service Factor	Encl.	NEMA Design	NEMA Frame	Model No.	Weight (lb)*	Drawing Links
<a href="#">G570</a>	\$334.00	1/3	1800	115 / 208-230 // 110 / 220	1.15	TEFC	N	56C	056C17F5320	17	<a href="#">PDF</a>
<a href="#">D311</a>	\$276.00	1/2	3600	115 / 208-203					056C34F5301	22	<a href="#">PDF</a>
<a href="#">G571</a>	\$382.00		1800						056C17F5321	24	<a href="#">PDF</a>
<a href="#">D312</a>	\$336.00	3/4	3600	115 / 208-230					056C34F5302	27	<a href="#">PDF</a>
<a href="#">G572</a>	\$461.00		1800	115 / 208-230 // 110 / 220					056C17F5322	30	<a href="#">PDF</a>
<a href="#">D313</a>	\$384.00	1	3600	115 / 208-230					056C34F5303	30	<a href="#">PDF</a>
<a href="#">G573</a>	\$473.00		1800	115 / 208-230 // 110 / 220				56HC	056C17F5323	31	<a href="#">PDF</a>
<a href="#">D314</a>	\$489.00	1-1/2	3600	115 / 208-230				56C	056B34F5326	32	<a href="#">PDF</a>
<a href="#">G574</a>	\$543.00		1800	115 / 208-230 // 110 / 220				56HC	056B17F5305	40	<a href="#">PDF</a>
<a href="#">D315</a>	\$593.00	2	3600	115 / 208-230					056B34F5327	37	<a href="#">PDF</a>
<a href="#">G575</a>	\$697.00		1800	115 / 208-230 // 110 / 220					1.0	056B17F5306	51
<a href="#">D316</a>	\$784.00	3	3600	208-230					1.15	056B34F5328	50

\* Refer to the Motor Shipping Schedule table for shipping information.

Certain heavy and oversized items can be shipped only via LTL. Check our website for current shipping method constraints by part number.

Note: Please review the AutomationDirect Terms & Conditions for warranty and service on this product. Warranty service can be arranged through numerous Marathon Electric service centers. See list of service centers on our website at [www.automationdirect.com](http://www.automationdirect.com).

# General Purpose, 1-phase, Totally Enclosed, 4-in-1<sup>®</sup> Motors

## C-Face Footed (Removable Base)

General Purpose, 1-phase, Totally Enclosed, 4-in-1 Motors											
Part Number	HP	F.L. RPM	Current @ 115V/230V (Amps)			Torque (lb-ft)			F.L. Effic. %	F.L. Power Factor	Rotor Inertia (lb-ft <sup>2</sup> )
			No Load 230V	Full Load 115/230V	Locked Rotor	Full Load	Locked Rotor	Break-down			
<b>G570</b>	1/3	1725	2.8	6.6 / 3.3	32.4 / 16.2	1.00	3.48	2.79	68.5	60	N/A*
<b>D311</b>	1/2	3450	3.2	8.4 / 4.2	49 / 24.5	0.75	2.81	2.22	59.5	70	
<b>G571</b>	1/2	1725	3.5	8.8 / 4.4	42.6 / 21.3	1.51	5.24	4.52	66	58	
<b>D312</b>	3/4	3450	3.7	10.6 / 5.3	69.4 / 34.7	1.13	3.73	3.38	66	71.9	
<b>G572</b>	3/4	1725	3.8	11 / 5.5	61 / 30.5	2.25	8.31	6.12	70.5	71	
<b>D313</b>	1	3450	3.1	11.2 / 5.6	81.8 / 40.9	1.49	4.95	4.22	78.5	76	
<b>G573</b>	1	1725	4.4	13.4 / 6.7	69.4 / 34.7	3.02	9.06	7.63	72	69.5	
<b>D314</b>	1-1/2	3450	2.6	14.2 / 7.1	96 / 48	2.24	5.2	6.0	78.5	87.5	
<b>G574</b>	1-1/2	1725	4.1	15.2 / 7.6	107.6 / 53.8	4.51	14.8	12.4	80	80	
<b>D315</b>	2	3450	2.1	19.2 / 9.6	122.6 / 61.3	2.98	7.37	7.73	79	98.3	
<b>G575</b>	2	1725	4.9	20 / 10	136 / 68	6.02	19.4	15.7	80	81	
<b>D316</b>	3	3450	2.6	13.1 -11.8**	91	4.46	8.46	13.2	84	99.2	

\* Data not available from manufacturer

\*\* 208-230V (Amps)