



# Tools – Jobber Length Drill Bits

Jobber Length Drill Bits - Metric Sizes Continued									
Metric	Part # High Speed Steel	Pcs/Pkg	Price	Part # Cobalt 5	Pcs/Pkg	Price	Drill Size A (mm)	Flute Length B (in.)	Overall Length C (in.)
	214075	10	<--->	215075	10	<--->	7.5	69.0	109.0
	214080	10	<--->	215080	10	<--->	8.0	75.0	117.0
	214085	10	<--->	215085	10	<--->	8.5	75.0	117.0
	214090	10	<--->	215090	10	<--->	9.0	81.0	125.0
	214095	10	<--->	215095	10	<--->	9.5	81.0	125.0
	214100	10	<--->	215100	10	<--->	10.0	87.0	133.0
	214102	10	<--->	215102	10	<--->	10.2	87.0	133.0
	214105	5	<--->	215105	5	<--->	10.5	87.0	133.0
	214110	5	<--->	215110	5	<--->	11.0	94.0	142.0
	214115	5	<--->	215115	5	<--->	11.5	94.0	142.0
	214120	5	<--->	215120	5	<--->	12.0	101.0	151.0
	214125	5	<--->	215125	5	<--->	12.5	101.0	151.0
	214130	5	<--->	215130	5	<--->	13.0	101.0	151.0



# Tools – Drill Bit Sets



Jobber length drill set  
214214RO shown

Drill Bit Sets		
Part #	Price	Description
101026USRO	<--->	<b>Three-piece Step Drill Bit Set</b> High Speed Steel, bright finish, spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
101026USERO	<--->	<b>Three-piece Step Drill Bit Set</b> HSS-Co5 spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
101026USTRO	<--->	<b>Three-piece Step Drill Bit Set</b> HSS-TiN coated spiral fluted with split point. Drill size 1: 6 steps from 3/16" to 1/2" with 1/16" increments. Shank size 1/4" Drill size 2: 13 steps from 1/8 to 1/2" with 1/32" increments. Shank size 1/4" Drill size 3: 9 steps from 1/4" to 3/4" with 1/16" increments. Shank size 3/8"
214214RO	<--->	<b>19-piece jobber Length Drill Set</b> Metric sizes 1.0 to 10.0 mm in increments of 0.5 mm High-speed steel, 118 degrees point
214215RO	<--->	<b>25-piece jobber Length Drill Set</b> Metric sizes 1.0 to 13.0 mm in increments of 0.5 mm High-speed steel, 118 degrees point
215214RO	<--->	<b>19-piece jobber Length Drill Set</b> Metric sizes 1.0 to 10.0 mm in increments of 0.5 mm High-speed steel Cobalt 5 alloy, 135 degrees point
215215RO	<--->	<b>25-piece jobber Length Drill Set</b> Metric sizes 1.0 to 13.0 mm in increments of 0.5 mm High-speed steel Cobalt 5 alloy, 135 degrees point
214850RO	<--->	<b>21-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel, 118 degrees point
214851RO	<--->	<b>29-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel, 118 degrees point.
215850RO	<--->	<b>21-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 3/8" in increments of 1/64" High-speed steel Cobalt 5 alloy, 135 degrees point
215851RO	<--->	<b>29-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 1/2" in increments of 1/64" High-speed steel Cobalt 5 alloy, 135 degrees point.
250850TRO	<--->	<b>21-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 3/8" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point
250851TRO	<--->	<b>29-piece jobber Length Drill Set</b> Fractional sizes 1/16" to 1/2" in increments of 1/64" TiN-coated high-speed steel, 118 degrees point