

# Disconnect Handle Applications for Freestanding and Floor Mount Painted Steel Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F\_SO\_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C.** Requires operator adapter plate **WA21CHVA**.
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft). Requires operator adapter plate **WA21SDA**.
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9FOCA-15A, BW9FOCA-20A, BW9FOGA-15A, BW9FOGA-20A, BW9FOHA-15A, BW9FOHA-20A, BW9FOJA-15A, and BW9FOJA-20A.** Requires operator adapter panel **WA21FUFA**.

Disconnect Enclosure Series	Available at AutomationDirect.com		
	AutomationDirect F_SO_C Series	Socomec 37299002 & 37299003	Fuji BW9F Series
<b>WAX_U Series</b>	✓	✓	✓
adapter plate required	<b>WA21CHVA</b>	<b>WA21SDA</b>	<b>WA21FUFA</b>
<b>WACPX_U Series</b>	✓	✓	✓
adapter plate required	<b>WA21CHVA</b>	<b>WA21SDA</b>	<b>WA21FUFA</b>
<b>WAXM_U Series</b>	✓	✓	✓
adapter plate required	<b>WA21CHVA</b>	<b>WA21SDA</b>	<b>WA21FUFA</b>

## Designed to house other brands

- Allen-Bradley** Bulletin 1494V, 1494C, 140U, & 194RC disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. Requires operator adapter plate **WA21ABVA**.
- Allen-Bradley** Bulletin 1494F flange-mounted disconnect switches and Bulletin 149D flange-mounted operators for circuit breakers. Requires operator adapter plate **WA21ABA**.
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers. Requires operator adapter plate **WA21CHVA**.
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers. Requires operator adapter plate **WA21CHVA**.
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers. Requires operator adapter plate **WA21GETDA**.
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers. Requires operator adapter plate **WA21ITE**.
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices. Requires operator adapter plate **WA21SDA**.

Disconnect Enclosure Series	Other Brands						
	Square D 9422 Series	Allen-Bradley 1494F & 1494D Series	Allen-Bradley 1494V, 1494C, 140U, 194RC Series	ABB Controls	Eaton/Cutler-Hammer C361 & C371 Series	General Electric STDA Series	Siemens I-T-E Max-Flex Series
<b>WAX_U Series</b>	✓	✓	✓	✓	✓	✓	✓
adapter plate required	<b>WA21SDA</b>	<b>WA21ABA</b>	<b>WA21ABVA</b>	<b>WA21CHVA</b>	<b>WA21CHVA</b>	<b>WA21GETDA</b>	<b>WA21ITE</b>
<b>WACPX_U Series</b>	✓	✓	✓	✓	✓	✓	✓
adapter plate required	<b>WA21SDA</b>	<b>WA21ABA</b>	<b>WA21ABVA</b>	<b>WA21CHVA</b>	<b>WA21CHVA</b>	<b>WA21GETDA</b>	<b>WA21ITE</b>
<b>WAXM_U Series</b>	✓	✓	✓	✓	✓	✓	✓
adapter plate required	<b>WA21SDA</b>	<b>WA21ABA</b>	<b>WA21ABVA</b>	<b>WA21CHVA</b>	<b>WA21CHVA</b>	<b>WA21GETDA</b>	<b>WA21ITE</b>

# NEMA 12 Heavy Duty Double-Door Right-Flange Floor Mount Disconnect



## Construction

- 10 gauge steel bodies and doors
- Continuous welded seams ground smooth
- Body stiffeners included for extra rigidity
- Heavy gauge continuous hinges to secure doors
- Heavy duty 3-point padlocking handles on all doors
- 15-inch floor stands welded to enclosure
- Poured in place polyurethane gasket.
- Heavy duty lifting eyes and provisions for fluorescent lighting
- Panel supports
- Collar studs for mounting optional subpanels
- Grounding provisions
- The right door is considered to be the "master" door on the "Right Flange" mount enclosures and the left door is the "master" door on the "Center Post" mount enclosures
- A mechanical interlock to prevent the slave door from opening before opening the master door
- Disconnects come with a universal cutout which provides mounting for most disconnects operators by using operator adapters
- Removable center post permits easy panel installation
- FTC rolled lip around all sides of opening keeps out liquids and contaminants

## Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

## Listings

- UL 508, Type 12 [UL File E64791]
- CSA Certified Type 12 [CSA File LL66078]
- NEMA/EEMAC Type 12



### Notes:

- Disconnect switch or circuit breakers, operating handle and operating mechanism must be ordered separately.
- **Operator adapter plates are required with this enclosure series and must be purchased separately.** Select the proper operator adapter for the brand and type of disconnect being used.
- Make sure the disconnect device you are using will fit the enclosure size you choose.

### Enclosure Shipping Schedule

Same day	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

### NEMA 12 Heavy Duty Double-Door Right-Flange Floor Mount Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
WA60X4912U	\$2,003.00	60.13 x 49.75 x 13.36 [1527 x 1264 x 339]	NPDD6048	NPDD6048G
WA60X4918U	\$2,246.00	60.13 x 49.75 x 19.36 [1527 x 1264 x 492]	NPDD6048	NPDD6048G
WA60X4924U	\$2,199.00	60.13 x 49.75 x 25.36 [1527 x 1264 x 644]	NPDD6048	NPDD6048G
WA60X6112U	\$2,240.00	60.13 x 61.75 x 13.36 [1527 x 1568 x 339]	NPDD6060	NPDD6060G
WA60X6118U	\$2,512.00	60.13 x 61.75 x 19.36 [1527 x 1568 x 492]	NPDD6060	NPDD6060G
WA60X6124U	\$2,434.00	60.13 x 61.75 x 25.36 [1527 x 1568 x 644]	NPDD6060	NPDD6060G
WA72X6112U	\$2,482.00	72.13 x 61.75 x 13.36 [1832 x 1568 x 339]	NPDD7260	NPDD7260G
WA72X6118U	\$2,776.00	72.13 x 61.75 x 19.36 [1832 x 1568 x 492]	NPDD7260	NPDD7260G
WA72X7312U	\$2,756.00	72.13 x 73.75 x 13.36 [1832 x 1873 x 339]	NPDD7272	-
WA72X7318U	\$2,994.00	72.13 x 73.75 x 19.36 [1832 x 1873 x 492]	NPDD7272	-
WA72X7324U	\$3,326.00	72.13 x 73.75 x 25.36 [1832 x 1873 x 644]	NPDD7272	-

Notes: Subpanels must be ordered separately.  
 Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawings.

# NEMA 12 Heavy Duty Double-Door Center Post Floor Mount Disconnect



## Construction

- 10 gauge steel bodies and doors
- Continuous welded seams ground smooth
- Body stiffeners included for extra rigidity
- Heavy gauge continuous hinges to secure doors
- Heavy duty 3-point padlocking handles on all doors
- 15-inch floor stands welded to enclosure
- Poured in place polyurethane gasket.
- Heavy duty lifting eyes and provisions for fluorescent lighting
- Panel supports
- Collar studs for mounting optional subpanels
- Grounding provisions
- The right door is considered to be the “master” door on the “Right Flange” mount enclosures and the left door is the “master” door on the “Center Post” mount enclosures
- A mechanical interlock to prevent the slave door from opening before opening the master door
- Disconnects come with a universal cutout which provides mounting for most disconnects operators by using operator adapters
- Removable center post permits easy panel installation
- FTC rolled lip around all sides of opening keeps out liquids and contaminants

## Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized panels are a conductive finish (unpainted)

## Listings

- UL 508, Type 12 [UL File E64791]
- CSA Certified Type 12 [CSA File LL66078]
- NEMA/EEMAC Type 12

### Notes:

- Disconnect switch or circuit breakers, operating handle and operating mechanism must be ordered separately.
- **Operator adapter plates are required with this enclosure series and must be purchased separately.** Select the proper operator adapter for the brand and type of disconnect being used.
- Make sure the disconnect device you are using will fit the enclosure size you choose.

### Enclosure Shipping Schedule

Same day	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

### NEMA 12 Heavy Duty Double-Door Center Post Floor Mount Disconnect

Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel
WA60CPX4912U	\$2,003.00	60.13 x 49.75 x 13.36 [1527 x 1264 x 339]	NPDD6048	NPDD6048G
WA60CPX4924U	\$2,037.00	60.13 x 49.75 x 25.36 [1527 x 1264 x 644]	NPDD6048	NPDD6048G
WA60CPX6112U	\$2,244.00	60.13 x 61.75 x 13.36 [1527 x 1568 x 339]	NPDD6060	NPDD6060G
WA60CPX6124U	\$2,392.00	60.13 x 61.75 x 25.36 [1527 x 1568 x 644]	NPDD6060	NPDD6060G
WA72CPX7312U	\$2,763.00	72.13 x 73.75 x 13.36 [1832 x 1873 x 339]	NPDD7272	-
WA72CPX7318U	\$3,002.00	72.13 x 73.75 x 19.36 [1832 x 1873 x 492]	NPDD7272	-


Notes: Subpanels must be ordered separately.  
 Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawings.

# NEMA 12 Heavy Duty Double-Door Floor Mount Disconnect




## Dimensions


WAX-U



WACPX-U



### Space Occupied by Disconnect



- When ordering 24.13 (613mm) deep enclosures, long connecting rods must be ordered. Long connecting rods are available from disconnect manufacturers.
- ABB Controls flange-operated devices
  - Cutler-Hammer C361 devices
  - Cutler-Hammer C371 operating mechanisms C371E and C371F, order catalog number C371CS1 connecting rod. For C371G and C371K, order catalog number C371CS2 connecting rod.
  - General Electric TDA devices, order catalog number TDSR extended length drive rod
  - For Square D 9422 devices, order catalog number 9422-R2 extra long operating rod(s). Some devices require two rods.

Refer to National Electrical Code ® 1996 article 430-10(b) for wiring space required for line side conductors to be connected to disconnect. Verify your application to determine if wiring space is adequate.

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Enclosure Subpanels



## Subpanels for Double-door Floor Mount Enclosures

- Subpanels are fabricated from 10 gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor mount enclosures and some double-door wall mount enclosures



Enclosure Shipping Schedule				
Same day	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days


Color indicates shipping lead time in business days.

Subpanels for Double-door Floor Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<b>NPDD4242</b>	\$173.00	<b>NPDD4242G</b>	\$173.00	42 x 42	39.00 x 39.00 [991 x 991]
<b>NPDD4260</b>	\$254.00	<b>NPDD4260G</b>	\$254.00	42 x 60	38.00 x 56.00 [965 x 1422]
<b>NPDD4842</b>	\$197.00	<b>NPDD4842G</b>	\$197.00	48 x 42	45.00 x 39.00 [1143 x 991]
<b>NPDD4848</b>	\$236.00	<b>NPDD4848G</b>	\$236.00	48 x 48	44.00 x 44.00 [1118 x 1118]
<b>NPDD5442</b>	\$210.00	<b>NPDD5442G</b>	\$210.00	54 x 42	50.00 x 38.00 [1270 x 965]
<b>NPDD6048</b>	\$286.00	<b>NPDD6048G</b>	\$286.00	60 x 48	44.00 x 56.00 [1118 x 1422]
<b>NPDD6060</b>	\$353.00	<b>NPDD6060G</b>	\$353.00	60 x 60	56.00 x 56.00 [1422 x 1422]
<b>NPDD7260</b>	\$420.00	<b>NPDD7260G</b>	\$420.00	72 x 60	56.00 x 68.00 [1422 x 1727]
<b>NPDD7272</b>	\$502.00	—		72 x 72	68.00 x 68.00 [1727 x 1727]

**Notes: Dimensions in inches [millimeters].**  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor mount enclosures may be up to 2 inches [51mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 inches [51 mm] wider than width dimensions listed in this table.

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.