

# NEMA 12 and 13 Hinged Screw Cover Wall-Mount



## Applications

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil and water.

## Construction

- Bodies and doors fabricated from 14 gauge steel
- Lids are sealed with closed cell oil resistant neoprene gasket
- Continuously welded seams ground smooth, less knockouts of holes
- Captive door screws thread into sealed wells
- Grounding provisions provided
- Weldnuts are provided for mounting optional subpanel
- No mounting feet or mounting holes are provided

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, Types 12 & 13 [UL File E6924]
- NEMA/EEMAC Types 12 & 13
- JIC EL-1-71



### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

### NEMA 12 and 13 Hinged Screw Cover Wall-Mount

Part Number	Price	Enclosure SizeHxWxD	Painted Steel Subpanel	Perforated Subpanel	Galvanized Steel Subpanel
<a href="#">WA060604GIE</a>	\$79.00	6.31 x 6.31 x 4.15 [160 x 160 x 105]	<a href="#">N1P0606</a>	<a href="#">N1P0606PP</a>	<a href="#">N1P0606G</a>
<a href="#">WA080604GIE</a>	\$87.00	8.31 x 6.31 x 4.15 [211 x 160 x 105]	<a href="#">N1P0608</a>	<a href="#">N1P0608PP</a>	<a href="#">N1P0608G</a>
<a href="#">WA080804GIE</a>	\$90.00	8.31 x 8.31 x 4.15 [211 x 211 x 105]	<a href="#">N1P0808</a>	<a href="#">N1P0808PP</a>	<a href="#">N1P0808G</a>
<a href="#">WA080806GIE</a>	\$95.00	8.31 x 8.31 x 6.15 [211 x 211 x 156]	<a href="#">N1P0808</a>	<a href="#">N1P0808PP</a>	<a href="#">N1P0808G</a>
<a href="#">WA100804GIE</a>	\$87.00	10.31 x 8.31 x 4.15 [262 x 211 x 105]	<a href="#">N1P0810</a>	<a href="#">N1P0810PP</a>	<a href="#">N1P0810G</a>
<a href="#">WA100806GIE</a>	\$100.00	10.31 x 8.31 x 6.15 [262 x 211 x 156]	<a href="#">N1P0810</a>	<a href="#">N1P0810PP</a>	<a href="#">N1P0810G</a>
<a href="#">WA101006GIE</a>	\$108.00	10.31 x 10.31 x 6.15 [262 x 262 x 156]	<a href="#">N1P1010</a>	<a href="#">N1P1010PP</a>	<a href="#">N1P1010G</a>
<a href="#">WA121004GIE</a>	\$103.00	12.31 x 10.31 x 4.15 [313 x 262 x 105]	<a href="#">N1P1012</a>	<a href="#">N1P1012PP</a>	<a href="#">N1P1012G</a>
<a href="#">WA121006GIE</a>	\$113.00	12.31 x 10.31 x 6.15 [313 x 262 x 156]	<a href="#">N1P1012</a>	<a href="#">N1P1012PP</a>	<a href="#">N1P1012G</a>
<a href="#">WA121206GIE</a>	\$127.00	12.31 x 12.31 x 6.15 [313 x 313 x 156]	<a href="#">N1P1212</a>	<a href="#">N1P1212PP</a>	<a href="#">N1P1212G</a>
<a href="#">WA141206GIE</a>	\$137.00	14.31 x 12.31 x 6.15 [363 x 313 x 156]	<a href="#">N1P1214</a>	<a href="#">N1P1214PP</a>	<a href="#">N1P1214G</a>

Notes: Subpanels must be ordered separately.


Dimensions in inches [millimeters]

Letters in table correspond to letters on dimensional drawings.

# NEMA 12 and 13 Hinged Screw Cover Wall-Mount



## Dimensions



### NOTES:


1. PANELS ARE 14GA STEEL.
2. PANEL SCREWS ARE #10-32 PAN HEAD.

# Enclosure Subpanels



## Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14 gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
  - NEMA 1 small (N1C)
  - NEMA 3R small (RHC)
  - NEMA 12 WA\_GIE




Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures							
Painted Steel	Price	Galvanized	Price	Perforated	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<a href="#">N1P0606</a>	\$4.25	<a href="#">N1P0606G</a>	\$4.00	<a href="#">N1P0606PP</a>	\$7.00	6 x 6	4.25 x 4.25 [108 x 108]
<a href="#">N1P0608</a>	\$5.25	<a href="#">N1P0608G</a>	\$5.25	<a href="#">N1P0608PP</a>	\$5.25	6 x 8	6.25 x 4.25 [159 x 108]
<a href="#">N1P0808</a>	\$6.00	<a href="#">N1P0808G</a>	\$6.00	<a href="#">N1P0808PP</a>	\$6.00	8 x 8	6.25 x 6.25 [159 x 159]
<a href="#">N1P0810</a>	\$7.00	<a href="#">N1P0810G</a>	\$7.00	<a href="#">N1P0810PP</a>	\$7.00	8 x 10	8.25 x 6.25 [210 x 159]
<a href="#">N1P1010</a>	\$8.25	<a href="#">N1P1010G</a>	\$7.50	<a href="#">N1P1010PP</a>	\$8.75	10 x 10	8.25 x 8.25 [210 x 210]
<a href="#">N1P1012</a>	\$9.75	<a href="#">N1P1012G</a>	\$8.75	<a href="#">N1P1012PP</a>	\$9.75	10 x 12	10.25 x 8.25 [260 x 210]
<a href="#">N1P1212</a>	\$11.50	<a href="#">N1P1212G</a>	\$10.25	<a href="#">N1P1212PP</a>	\$12.75	12 x 12	10.25 x 10.25 [260 x 260]
<a href="#">N1P1214</a>	\$13.00	<a href="#">N1P1214G</a>	\$11.50	<a href="#">N1P1214PP</a>	\$13.00	12 x 14	12.25 x 10.25 [311 x 260]
<a href="#">N1P1216</a>	\$14.50	<a href="#">N1P1216G</a>	\$13.00	<a href="#">N1P1216PP</a>	\$14.50	12 x 16	14.25 x 10.25 [362 x 260]
<a href="#">N1P1220</a>	\$20.00	<a href="#">N1P1220G</a>	\$17.75	<a href="#">N1P1220PP</a>	\$20.00	12 x 20	18.25 x 10.25 [464 x 260]

Notes: Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawing.

## Dimensions



Note: Perforated panels have 0.13 in [3 mm] diameter holes at 0.25in [6 mm] spacing.