

Disconnect Handle Applications for Disconnect Enclosures

Designed to house the following available at AutomationDirect.com

Available at AutomationDirect.com

- AutomationDirect.com NEMA 1/12 Flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series F_SO_C flex handle mechanisms are available in four sizes to actuate all AutomationDirect MCCBs from 15 amps up to 600 amps. **F0S03C, F0S06C, F1S03C, F1S06C, F3S03C, F3S06C, F4S04C, and F4S06C**
- Socomec Disconnect switches with cable, flange-mounted cable operator and handles. Handles **37299002** and **37299003**, cable operator **37299903**, and cables **37299992** (3ft) or **37299993** (5ft)
- Fuji Electric NEMA 12 flexible shaft handle for Molded Case Circuit Breakers (MCCBs). Series BW9F flex handle mechanisms are available in four sizes to actuate all Fuji Electric MCCBs from 15 Amps to 800 Amps. **BW9F0CA-15A, BW9F0CA-20A, BW9F0GA-15A, BW9F0GA-20A, BW9F0HA-15A, BW9F0HA-20A, BW9F0JA-15A, and BW9F0JA-20A.**
- Gladiator Molded Case Circuit Breakers (MCCBs) flange mounted cable operator and handles. See Gladiator sections for handles and cable options. **GCBX1-FHC-N3R4-M, GCBX1-FHC-N4X-M, GCBX5-FHC-N3R4-M, and GCBX5-FHC-N4X-M**

Disconnect Enclosure Series	AutomationDirect F_SO_C Series	Socomec 37299002 and 37299003	Fuji BW9F series	Gladiator GCBX
N412_CD Series	✓	✓	✓	✓
N412_CDSS Series	✓	✓	✓	✓
N412_CDSSA Series	✓	✓	✓	✓
N412_CSTD Series	✓	✓	✓	✓
N412_CSSSTD Series	✓	✓	✓	✓
SDN_PL Series	✓	✓	✓	✓
SN4 Series	✓	✓	✓	✓
ABN12 Series	✗	✗	✗	✗
SSN4X Series	✓	✓	✓	✓
SSN4X_A Series	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✓	✓	✓

Designed to house other brands

- Allen-Bradley** Bulletin 1494V and 140U disconnect switches with flange-mounted variable-depth operating mechanisms and Bulletin 1494V flange-mounted variable-depth operating mechanisms for circuit breakers. These enclosures will not accept Allen-Bradley Bulletin 1494F disconnect devices or Bulletin 1494D circuit breaker operators
- ABB Controls** flange-mounted variable-depth operating mechanisms for disconnect switches and circuit breakers
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable depth
- Eaton / Cutler-Hammer** Type C361 flange-mounted variable-depth operating mechanisms with disconnect switches and Type C371 flange-mounted variable depth operating mechanisms for circuit breakers; also Flex Shaft™ handle mechanisms for circuit breakers
- General Electric** Type STDA flange handles and variable depth operating
- General Electric** Type STDA flange handles and variable depth operating mechanisms for disconnect switches and circuit breakers; also Spectra Flex™ cable operators for circuit breakers
- SIEMENS** I-T-E Max-Flex flange-mounted variable depth operating handle for disconnect switches and circuit breakers
- Square D** Class 9422 disconnect switches with flange-mounted variable depth operating mechanisms or cable Industry Standards mechanisms and Class 9422 flange-mounted variable depth operating mechanisms or cable mechanisms for circuit breakers. These enclosures will not accept Square D Class 9422 bracket-mounted disconnect devices, Class 9422TG1, or TG2 devices.

Disconnect Enclosures Series	Other Brands						
	Square D 9422 series	Allen-Bradley 1494F and 1494D series	Allen-Bradley 1494V, 1494C, 140U, 194RC series	ABB Controls	Eaton/Cutler-Hammer C361 and C371 series	General Electric STDA series	Siemens I-T-E Max-Flex Series
N412_CD Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSS Series	✓	✗	✓	✓	✓	✓	✓
N412_CDSSA Series	✓	✗	✓	✓	✓	✓	✓
N412_CSTD Series	✓	✗	✓	✓	✓	✓	✓
N412_CSSSTD Series	✓	✗	✓	✓	✓	✓	✓
SDN_PL Series	✓	✗	✓	✓	✓	✓	✓
SN4 Series	✓	✗	✓	✓	✓	✓	✓
ABN12 Series	✗	✓	✗	✗	✗	✗	✗
SSN4X Series	✓	✗	✓	✓	✓	✓	✓
SSN4X_A Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FS4 Series	✓	✗	✓	✓	✓	✓	✓
WRD-XM_FSD4 Series	✓	✗	✓	✓	✓	✓	✓

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Construction

- 14-gauge steel bodies and doors
- Plasma welded seams
- Rolled lip around all sides of opening keeps out liquids and contaminants
- Stainless steel exterior hardware
- Stainless steel door clamps around three sides of doors for a watertight seal; no additional door hardware required
- Remove doors easily by pulling continuous hinge pin
- Polyurethane poured-in-place gasket
- External mounting feet
- Collar studs for mounting optional subpanel
- Grounding provisions provided
- Bracket welded to door for attaching disconnect interlock door catch
- Holes in body for mounting disconnect operating handle and operating mechanism. These enclosures are designed to operate properly without the use of door hardware



Listings

- UL 508 4, 12, and 13 [UL File E64791]
- NEMA/EEMAC 3, 4, 12, and 13



Notes: Disconnect switch or circuit breakers, operating handle, operating mechanism must be ordered separately.

Operator adapter plates are not required with this enclosure series.

Make sure the disconnect device you are using will fit the enclosure size you choose.

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized and stainless steel subpanels are a conductive finish (unpainted)

Shipping Schedule

Same day | 1 - 5 days | 1 - 7 days | 1 - 15 days | 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect

Part Number	PriceCode	Enclosure Size HxWxD	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel	Stainless Steel Subpanel
SN4242108	Retired	24.00 x 21.38 x 8.97 [610 x 543 x 228]	NP2420	NP2420G	NP2420PP	NP2420SS
SN4242508	Retired	24.00 x 25.38 x 8.97 [610 x 645 x 228]	NP2420	NP2424G	NP2424PP	NP2424SS
SN4302508	Retired	30.00 x 25.38 x 8.97 [762 x 645 x 228]	NP3024	NP3024G	NP3024PP	NP3024SS
SN4363108	Retired	36.00 x 31.38 x 8.97 [914 x 797 x 228]	NP3630	NP3630G	NP3630PP	NP3630SS
SN4423112	Retired	42.00 x 31.38 x 12.97 [1067 x 797 x 329]	NP4230	NP4230G	NP4230PP	NP4230SS
SN4423712	Retired	42.00 x 37.37 x 12.97 [1067 x 949 x 329]	NP4236	NP4236G	NP4236PP	NP4236SS
SN4483712**	Retired	48.00 x 37.38 x 12.97 [1219 x 949 x 329]	NP4836	NP4836G	NP4836PP	NP4836SS
SN4603712**	Retired	60.00 x 37.38 x 12.97 [1524 x 949 x 329]	NP6036	NP6036G	NP6036PP	NP6036SS

Notes: Subpanels must be ordered separately.

Dimensions in inches [millimeters].


Letters in table correspond to letters on dimensional drawings.

**These enclosures have a closed-cell neoprene gasket, not poured-in-place.

NEMA 4, 12, and 13 Single-Door Wall-Mount Right-Flanged Disconnect



Dimensions



NOTES:

1. SUBPANELS ARE MADE FROM 12 GA. STEEL.
2. SUBPANELS HAVE FLANGES ALONG ALL SIDES WHEN EITHER DIMENSION EXCEEDS 17".

Enclosure Subpanels




Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

- 12-gauge steel (perforated subpanels are 14-gauge)
- Subpanels with any side over 17 in [432 mm] have 0.25 in [6mm] flange on all sides
- Painted steel and perforated subpanels white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint) Panels listed fit the following enclosures:
- NEMA 1 large (N1C, 42 in [1067 mm] width and wider)
- NEMA 12 single door wall-mount (N12)
- NEMA 12 two-door wall-mount (WA_WF)
- NEMA 12 single door flush wall-mount (WA_FM)
- NEMA 4 (N4) and 4X (SSN) single door wall-mount
- NEMA 12 operator consoles (WC9)
- NEMA 12 Wall Disconnect (SDN12_PL and ABN12)
- NEMA 4 and 4X Wall-Mount Disconnect (SSN4 and SSN4X)



Note: Use NPxxxx subpanels in NEMA 1, NEMA 4 and 4X, and NEMA 12 enclosures only. Do NOT use NPxxxx subpanels in N412 Ultimate Series enclosures with a C in the suffix.

Dimensions



NOTE:
SUBPANELS LARGER THAN
20 X 20 HAVE (2) 0.31"
GROUND HOLES.

Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25 in [6 mm] spacing.

Enclosure Subpanels



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Subpanels for NEMA 1, 12, 4 and 4X Wall-Mount Enclosures and WC9 NEMA 12 Operator Consoles

Painted Steel	Price	Galvanized	Price	Perforated	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
NP1212	—	NP1212G	Retired	—	—	—	—	12 x 12	9.00 x 9.00 [229 x 229]
NP1224	—	NP1224G	Retired	—	—	—	—	24 x 12	9.00 x 21.00 [229 x 533]
NP1612	—	NP1612G	Retired	NP1612PP	Retired	NP1612SS	—	12 x 16 16 x 12	13.00 x 9.00 [330 x 229]
NP1616	—	NP1616G	Retired	NP1616PP	Retired	NP1616SS	—	16 x 16	13.00 x 13.00 [330 x 330]
NP2012	—	NP2012G	Retired	—	—	—	—	20 x 12	17.00 x 9.00 [432 x 229]
NP2016	—	NP2016G	Retired	NP2016PP	Retired	NP2016SS	—	20 x 16	17.00 x 13.00 [432 x 330]
NP2020	—	NP2020G	Retired	NP2020PP	Retired	NP2020SS	—	20 x 20	17.00 x 17.00 [432 x 432]
NP2416	—	NP2416G	Retired	—	—	NP2416SS	—	24 x 16	21.00 x 13.00 [533 x 330]
NP2420	—	NP2420G	Retired	NP2420PP	Retired	NP2420SS	—	24 x 20	21.00 x 17.00 [533 x 432]
NP2424	—	NP2424G	Retired	NP2424PP	Retired	NP2424SS	—	24 x 24	21.00 x 21.00 [533 x 533]
NP3016	—	NP3016G	Retired	—	—	—	—	30 x 16	27.00 x 13.00 [686 x 330]
NP3020	—	NP3020G	Retired	—	—	NP3020SS	—	30 x 20	27.00 x 17.00 [686 x 432]
NP3024	—	NP3024G	Retired	NP3024PP	Retired	NP3024SS	—	24 x 30 30 x 24	27.00 x 21.00 [686 x 533]
NP3030	—	NP3030G	Retired	NP3030PP	Retired	NP3030SS	—	30 x 30	27.00 x 27.00 [686 x 686]
NP3624	—	NP3624G	Retired	NP3624PP	Retired	NP3624SS	—	36 x 24	33.00 x 21.00 [838 x 533]
NP3630	—	NP3630G	Retired	NP3630PP	Retired	NP3630SS	—	30 x 36 36 x 30	33.00 x 27.00 [838 x 686]
NP3636	—	NP3636G	Retired	NP3636PP	Retired	NP3636SS	—	36 x 36	33.00 x 33.00 [838 x 838]
NP4024	—	—	—	—	—	—	—	40 x 24	37.00 x 21.00 [940 x 533]
NP4224	—	NP4224G	Retired	—	—	—	—	42 x 24	39.00 x 21.00 [991 x 533]
NP4230	—	NP4230G	Retired	NP4230PP	Retired	NP4230SS	—	42 x 30	39.00 x 27.00 [991 x 686]
NP4236	—	NP4236G	Retired	NP4236PP	Retired	NP4236SS	—	42 x 36	39.00 x 33.00 [991 x 838]
NP4824	—	NP4824G	Retired	—	—	—	—	48 x 24	45.00 x 21.00 [1143 x 533]
NP4830	—	NP4830G	Retired	—	—	—	—	48 x 30	45.00 x 27.00 [1143 x 686]
NP4836	—	NP4836G	Retired	NP4836PP	Retired	NP4836SS	—	48 x 36	45.00 x 33.00 [1143 x 838]
NP6030	—	NP6030G	Retired	—	—	—	—	60 x 30	57.00 x 27.00 [1448 x 686]
NP6036	—	NP6036G	Retired	NP6036PP	Retired	NP6036SS	—	60 x 36	57.00 x 33.00 [1448 x 838]
NP7230	—	NP7230G	—	—	—	—	—	72 x 30	69.00 x 27.00 [1753 x 686]
NP7236	—	NP7236G	—	—	—	—	—	72 x 36	69.00 x 33.00 [1753 x 838]

Notes: Dimensions in inches [millimeters].
 Letters in table correspond to letters on dimensional drawing.
 Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions in this table.