

# NEMA 3, 4 and 12 Two-Door Floor Mount with 3-Point Handle



## Application

Designed to house electrical and electronic controls, components, and instruments in wet non-corrosive environments.

Typical applications for these enclosures include dairies, breweries and other food processing activities that may require hose down. Enclosures are also suitable for outdoor applications.

## Construction

- Bodies and doors fabricated from 10 gauge steel
- Continuously welded seams ground smooth
- Body stiffeners added for extra strength
- Rolled lip around three sides of door and along top of enclosure's opening excludes liquids and contaminants from entering
- 3-point keylocking/padlocking combo handle
- Heavy gauge continuous hinges are provided to secure doors
- Doors are removable by pulling stainless steel continuous hinge pin

- Removable print pocket is provided
- Standard 12" high floor kits are welded to bottom of enclosure
- Heavy duty removable lifting eyes
- Collar studs for mounting optional panels
- Easily removable center post permits easy panel installations
- Doors are sealed with poured in place polyurethane gasket
- Grounding provisions provided
- [Uses WAL4 series handles and WAEMK44 replacement key](#)

## Finish

ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces.

## Listings

- UL 508, Types 3, 4 & 12 [UL File E64791]
- CSA Certified, Type 12 [CSA File LL66078]
- NEMA/EEMAC Types 3, 4 & 12




FOR CURRENT LISTINGS,  
PLEASE SEE [WWW.AUTOMATIONDIRECT.COM](http://WWW.AUTOMATIONDIRECT.COM)

| Enclosure Shipping Schedule                          |            |             |
|--|------------|-------------|
| Same day   | 1 - 7 days | 1 - 15 days |
| Color indicates shipping lead time in business days. |            |             |

| NEMA 3, 4 and 12 Two-Door Floor Mount Enclosure with 3-Point Handle |            |  |                        |                     |
|---|------------|--|------------------------|---------------------|
| Part Number   | Price      | Enclosure Size HxWxD<br>[not including 12" legs] | Painted Steel Subpanel | Galvanized Subpanel |
| <b>N4D6248103PT</b>   | \$1,960.00 | 62.12 x 48.12 x 11.08 [1578 x 1222 x 284]        | <b>NPDD6048</b>        | <b>NPDD6048G</b>    |
| <b>N4D6260123PT</b>   | \$2,267.00 | 62.12 x 60.12 x 13.29 [1578 x 1527 x 338]        | <b>NPDD6060</b>        | <b>NPDD6060G</b>    |
| <b>N4D7460123PT</b>   | \$2,516.00 | 74.12 x 60.12 x 13.29 [1883 x 1527 x 338]        | <b>NPDD7260</b>        | <b>NPDD7260G</b>    |
| <b>N4D7472123PT</b>   | \$2,803.00 | 74.12 x 72.12 x 13.29 [1883 x 1832 x 338]        | <b>NPDD7272</b>        | -                   |
| <b>N4D7472243PT</b>   | \$3,290.00 | 74.12 x 72.12 x 25.29 [1883 x 1832 x 642]        | <b>NPDD7272</b>        | -                   |

# NEMA 3, 4 and 12 Two-Door Floor Mount with 3-Point Handle

Dimensions  
in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Enclosure Subpanels



## Subpanels for Double-door Floor Mount Enclosures

- Subpanels are fabricated from 10 gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor mount enclosures and some double-door wall mount enclosures




| Enclosure Shipping Schedule                          |            |
|--|------------|
| Same day   | 1 - 7 days |
| Color indicates shipping lead time in business days. |            |

| Subpanels for Double-door Floor Mount Enclosures |          |                  |          |                             |                             |
|--|----------|------------------|----------|-----------------------------|-----------------------------|
| Painted Steel                                    | Price    | Galvanized       | Price    | Nominal Enclosure Size HxW* | Subpanel Size AxB           |
| <b>NPDD4242</b>                                  | \$171.00 | <b>NPDD4242G</b> | \$171.00 | 42 x 42                     | 39.00 x 39.00 [991 x 991]   |
| <b>NPDD4260</b>                                  | \$251.00 | <b>NPDD4260G</b> | \$251.00 | 42 x 60                     | 38.00 x 56.00 [965 x 1422]  |
| <b>NPDD4842</b>                                  | \$194.00 | <b>NPDD4842G</b> | \$194.00 | 48 x 42                     | 45.00 x 39.00 [1143 x 991]  |
| <b>NPDD4848</b>                                  | \$232.00 | <b>NPDD4848G</b> | \$232.00 | 48 x 48                     | 44.00 x 44.00 [1118 x 1118] |
| <b>NPDD5442</b>                                  | \$207.00 | <b>NPDD5442G</b> | \$207.00 | 54 x 42                     | 50.00 x 38.00 [1270 x 965]  |
| <b>NPDD6048</b>                                  | \$282.00 | <b>NPDD6048G</b> | \$282.00 | 60 x 48                     | 44.00 x 56.00 [1118 x 1422] |
| <b>NPDD6060</b>                                  | \$348.00 | <b>NPDD6060G</b> | \$348.00 | 60 x 60                     | 56.00 x 56.00 [1422 x 1422] |
| <b>NPDD7260</b>                                  | \$414.00 | <b>NPDD7260G</b> | \$414.00 | 72 x 60                     | 56.00 x 68.00 [1422 x 1727] |
| <b>NPDD7272</b>                                  | \$495.00 | —                |          | 72 x 72                     | 68.00 x 68.00 [1727 x 1727] |

**Notes: Dimensions in inches [millimeters].**  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor mount enclosures may be up to 2 inches [51mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 inches [51 mm] wider than width dimensions listed in this table.

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.