

# NEMA 4, 12 and 13 Lift-Off Cover Wall Mount



## Applications

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection where equipment is hosed down, very wet or in outdoor applications.



## Construction

- Bodies fabricated from 14 gauge steel; Doors fabricated from 16 gauge steel
- Continuously welded seams ground smooth
- Poured-in-place polyurethane gasket
- External mounting feet, top and bottom of enclosure
- Weldnuts are provided for mounting optional subpanels securely on models 6" x 4" and larger
- Stainless steel screws and clamps on four sides of cover to assure watertight seal
- Optional subpanels and terminal kits must be ordered separately
- Grounding provisions provided
- **Uses WABN4JIC clamp**

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, Types 4, 12 & 13 (6x6x4 and above)
- UL 508, Types 4,12 & 13 (6x4x3 and smaller) [UL Files E23553, E64791]
- NEMA/EEMAC Types 4, 12 & 13



FOR CURRENT LISTINGS, PLEASE SEE [WWW.AUTOMATIONDIRECT.COM](http://WWW.AUTOMATIONDIRECT.COM)

Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.


NEMA 4, 12 and 13 Lift-Off Cover Wall Mount					
Part Number	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Subpanel
<b>BN4040403</b>	\$44.00	4.31 x 4.31 x 3.16 [109 x 109 x 80]	-	-	-
<b>BN4060403</b>	\$50.00	6.31 x 4.31 x 3.16 [160 x 109 x 80]	<b>P0604</b>	<b>P0604SS</b>	<b>P0604G</b>
<b>BN4060604</b>	\$58.00	6.31 x 6.31 x 4.16 [160 x 160 x 106]	<b>P0606</b>	<b>P0606SS</b>	<b>P0606G</b>
<b>BN4080603</b>	\$62.00	8.31 x 6.31 x 3.16 [211 x 160 x 80]	<b>P0806</b>	<b>P0806SS</b>	<b>P0806G</b>
<b>BN4100804</b>	\$77.00	10.31 x 8.31 x 4.16 [262 x 211 x 106]	<b>P1008</b>	<b>P1008SS</b>	<b>P1008G</b>
<b>BN4121005</b>	\$98.00	12.31 x 10.31 x 5.16 [313 x 262 x 131]	<b>P1210</b>	<b>P1210SS</b>	<b>P1210G</b>
<b>BN4141206</b>	\$124.00	14.31 x 12.31 x 6.16 [363 x 313 x 156]	<b>P1412</b>	<b>P1412SS</b>	<b>P1412G</b>
<b>BN4161406</b>	\$146.00	16.31 x 14.31 x 6.16 [414 x 363 x 156]	<b>P1614</b>	<b>P1614SS</b>	<b>P1614G</b>

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].

# NEMA 4, 12 and 13 Lift-Off Cover Wall Mount



## Dimensions



*See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.*

# Enclosure Subpanels



## Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

## Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14 gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B\_CH, BN4, BN4\_CH, BN4\_CHQT, BN4\_SS, BN4\_CHSS, BN4\_CHSSA, BN4\_CHQTSS, BN4\_CHQTSSA ("\_" refers to dimensions).



Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days


Color indicates shipping lead time in business days.

Subpanels for B and BN4 Enclosures							
Painted Steel	Price	304 Stainless Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<b>P0604</b>	\$4.00	<b>P0604SS</b>	\$13.50	<b>P0604G</b>	\$4.00	6 x 4	4.88 x 2.88 [124 x 73]
<b>P0606</b>	\$4.75	<b>P0606SS</b>	\$16.75	<b>P0606G</b>	\$4.75	6 x 6	4.88 x 4.88 [124 x 124]
<b>P0806</b>	\$5.50	<b>P0806SS</b>	\$19.75	<b>P0806G</b>	\$5.50	8 x 6	6.88 x 4.88 [175 x 124]
<b>P0808</b>	\$6.50	-	-	<b>P0808G</b>	\$6.50	8 x 8	6.88 x 6.88 [175 x 175]
<b>P1008</b>	\$7.00	<b>P1008SS</b>	\$28.50	<b>P1008G</b>	\$7.00	10 x 8	8.88 x 6.88 [226 x 175]
<b>P1010</b>	\$9.00	-	-	<b>P1010G</b>	\$9.00	10 x 10	8.88 x 8.88 [226 x 226]
<b>P1206</b>	\$7.00	-	-	<b>P1206G</b>	\$7.00	12 x 6	10.88 x 4.88 [276 x 124]
<b>P1210</b>	\$10.25	<b>P1210SS</b>	\$40.00	<b>P1210G</b>	\$10.25	12 x 10	10.88 x 8.88 [276 x 226]
<b>P1212</b>	\$12.00	<b>P1212SS</b>	\$47.00	<b>P1212G</b>	\$12.00	12 x 12	10.88 x 10.88 [276 x 276]
<b>P1408</b>	\$9.75	-	-	<b>P1408G</b>	\$9.75	14 x 8	12.88 x 6.88 [327 x 175]
<b>P1412</b>	\$13.25	<b>P1412SS</b>	\$54.00	<b>P1412G</b>	\$13.25	14 x 12	12.88 x 10.88 [327 x 276]
<b>P1610</b>	\$13.00	-	-	<b>P1610G</b>	\$13.00	16 x 10	14.88 x 8.88 [378 x 226]
<b>P1614</b>	\$17.75	<b>P1614SS</b>	\$71.00	<b>P1614G</b>	\$17.75	16 x 14	14.88 x 12.88 [378 x 327]

Notes: Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawing.

### Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.