

NEMA 4, 4X, 12 and 13 Stainless Steel Lift-Off Cover Wall Mount



Applications

Provides unmatched protection for housing electrical components in highly corrosive environments. This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids, or contaminants.

Construction

- Bodies and doors are fabricated from 16 gauge type 304 or 316L stainless steel
- Continuously welded seams ground smooth
- Poured-in-place polyurethane gasket
- External mounting feet, top and bottom of enclosure
- Weldnuts are provided on models 6" x 4" and larger to secure optional subpanel
- Stainless steel screws and clamps on four sides of cover assure water-tight seal
- Grounding provisions provided
- Optional panels and terminal kits must be ordered separately
- **Uses WABN4JIC clamp**

Finish

Cover and outside of enclosure have a smooth grained finish

Listings

- UL 50, Types 4, 4X, 12 & 13 [6x6x4 and above]
- UL 508, Types 4, 4X, 12 & 13 [6x4x3 and smaller]
- UL File E23553, E64791
- CSA Certified, Types 4 & 12
- CSA File LL66078
- NEMA/EEMAC Types 4, 4X, 12 & 13
- JIC EL-1-71



FOR CURRENT LISTINGS,
PLEASE SEE WWW.AUTOMATIONDIRECT.COM

Enclosure Shipping Schedule

Same day	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days
----------	------------	-------------	-------------	-------------

Color indicates shipping lead time in business days.




NEMA 4, 4X, 12 and 13 Stainless Steel Lift-Off Cover Wall Mount Enclosure

304 Stainless Steel	Price	316L Stainless Steel	Price	Enclosure Size HxWxD	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Subpanel
BN4040403SS	\$119.00	BN4040403SSA	\$154.00	4.31 x 4.31 x 3.31 [109 x 109 x 84]	-	-	-
BN4060403SS	\$159.00	BN4060403SSA	\$210.00	6.31 x 4.31 x 3.31 [160 x 109 x 84]	P0604	P0604SS	P0604G
BN4060604SS	\$181.00	BN4060604SSA	\$238.00	6.31 x 6.31 x 4.31 [160 x 160 x 110]	P0606	P0606SS	P0606G
BN4080604SS	\$204.00	BN4080604SSA	\$262.00	8.31 x 6.31 x 4.31 [211 x 160 x 109]	P0806	P0806SS	P0806G
BN4100804SS	\$256.00	BN4100804SSA	\$326.00	10.31 x 8.31 x 4.31 [262 x 211 x 109]	P1008	P1008SS	P1008G
BN4121005SS	\$366.00	BN4121005SSA	\$456.00	12.31 x 10.31 x 5.31 [313 x 262 x 135]	P1210	P1210SS	P1210G
BN4141206SS	\$447.00	BN4141206SSA	\$551.00	14.31 x 12.31 x 6.31 [363 x 313 x 160]	P1412	P1412SS	P1412G
BN4161406SS	\$536.00	BN4161406SSA	\$655.00	16.31 x 14.31 x 6.31 [414 x 363 x 160]	P1614	P1614SS	P1614G

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, 12 and 13 Stainless Steel Lift-Off Cover Wall Mount

Dimensions in [mm]



NOTES;

- 1.) SUBPANELS ARE 14GA STEEL
- 2.) SUBPANELS SCREWS ARE #10-32 PAN HEAD.

See our website: www.AutomationDirect.com for complete engineering drawings.

Enclosure Subpanels




Subpanels

Subpanels are not included with most enclosures and must be purchased separately. The specifications table for each enclosure family lists the part number of the subpanel that goes with each enclosure.

Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14 gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B_CH, BN4, BN4_CH, BN4_CHQT, BN4_SS, BN4_CHSS, BN4_CHSSA, BN4_CHQTSS, BN4_CHQTSSA ("_" refers to dimensions).



Subpanels for B and BN4 Enclosures							
Painted Steel	Price	304 Stainless Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
P0604	\$3.00	P0604SS	\$11.00	P0604G	\$3.00	6 x 4	4.88 x 2.88 [124 x 73]
P0606	\$3.25	P0606SS	\$13.50	P0606G	\$3.25	6 x 6	4.88 x 4.88 [124 x 124]
P0806	\$4.00	P0806SS	\$16.00	P0806G	\$4.00	8 x 6	6.88 x 4.88 [175 x 124]
P0808	\$4.75	-		P0808G	\$4.75	8 x 8	6.88 x 6.88 [175 x 175]
P1008	\$5.50	P1008SS	\$23.00	P1008G	\$5.50	10 x 8	8.88 x 6.88 [226 x 175]
P1010	\$7.50	-		P1010G	\$7.50	10 x 10	8.88 x 8.88 [226 x 226]
P1206	\$6.00	-		P1206G	\$6.00	12 x 6	10.88 x 4.88 [276 x 124]
P1210	\$7.75	P1210SS	\$30.00	P1210G	\$7.75	12 x 10	10.88 x 8.88 [276 x 226]
P1212	\$9.25	P1212SS	\$38.00	P1212G	\$9.25	12 x 12	10.88 x 10.88 [276 x 276]
P1408	\$8.25	-		P1408G	\$8.25	14 x 8	12.88 x 6.88 [327 x 175]
P1412	\$10.00	P1412SS	\$43.50	P1412G	\$10.00	14 x 12	12.88 x 10.88 [327 x 276]
P1610	\$11.00	-		P1610G	\$11.00	16 x 10	14.88 x 8.88 [378 x 226]
P1614	\$12.00	P1614SS	\$57.00	P1614G	\$12.00	16 x 14	14.88 x 12.88 [378 x 327]


Notes: Dimensions in inches (millimeters). Letters in table correspond to letters on dimensional drawing.

Enclosure Shipping Schedule				
Same day	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.