

# NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount



## Applications

These two-door enclosures provide industry-leading protection for systems incorporating large components or complex configurations in highly corrosive environments. It is typically used in the following areas: food processing plants, pharmaceutical manufacturing facilities, petrochemical plants, pulp and paper processing, and waste water treatment facilities.

- Print pocket is provided
- Standard 12" high floor kits are welded to bottom of enclosure
- Heavy duty removable lifting eyes
- Doors are sealed with poured in place polyurethane gasket
- Grounding provisions provided
- Easily removable center post permits easy panel installations
- Collar studs for mounting optional subpanels
- [Uses WAN4XRA clamp](#)

## Construction

- Bodies and doors fabricated from 12 gauge 304 stainless steel
- Continuously welded seams ground smooth
- X-type body stiffeners are included for extra strength
- Rolled lip around three sides of door and along top of enclosure opening excludes liquids and contaminants from entering
- Quick and easy to operate stainless steel door clamps around three sides of doors are provided
- Heavy gauge stainless steel continuous hinges are provided
- Doors are removable by pulling stainless steel continuous hinge pin
- Hasp and staple are provided for padlocking

## Finish

Enclosures have a smooth grained finish on all exterior surfaces

## Listings

- UL 508, Types 4, 4X and 12 [UL file E64791]
- CSA Certified, Types 4 and 12 [CSA file LL66078]
- Meets NEMA/EEMAC Types 4, 4X and 12 requirements



FOR CURRENT LISTINGS, PLEASE SEE [WWW.AUTOMATIONDIRECT.COM](http://WWW.AUTOMATIONDIRECT.COM)

### Enclosure Shipping Schedule

Same day	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days
----------	------------	-------------	-------------	-------------

Color indicates shipping lead time in business days.

### NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount Enclosures


Part Number	Price	Enclosure Size HxWxD [not incl. 12" legs]	Painted Steel Subpanel	Galvanized Subpanel
<b>SSN4D624812</b>	\$7,157.00	62.12 x 48.12 x 12.12 [1578 x 1222 x 308]	<b>NPDD6048</b>	<b>NPDD6048G</b>
<b>SSN4D626012</b>	\$8,028.00	62.12 x 60.12 x 12.12 [1578 x 1527 x 308]	<b>NPDD6060</b>	<b>NPDD6060G</b>
<b>SSN4D746012</b>	\$7,523.00	74.12 x 60.12 x 12.12 [1883 x 1527 x 308]	<b>NPDD7260</b>	<b>NPDD7260G</b>
<b>SSN4D747212</b>	\$9,889.00	74.12 x 72.12 x 12.12 [1883 x 1832 x 308]	<b>NPDD7272</b>	-
<b>SSN4D747224</b>	\$12,603.00	74.12 x 72.12 x 24.12 [1883 x 1832 x 613]	<b>NPDD7272</b>	-

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawings.

# NEMA 4, 4X and 12 Stainless Steel Two-Door Floor Mount

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Enclosure Subpanels



## Subpanels for Double-door Floor Mount Enclosures

- Subpanels are fabricated from 10 gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor mount enclosures and some double-door wall mount enclosures



Enclosure Shipping Schedule				
Same day	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days


Color indicates shipping lead time in business days.

Subpanels for Double-door Floor Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<b>NPDD4242</b>	\$173.00	<b>NPDD4242G</b>	\$173.00	42 x 42	39.00 x 39.00 [991 x 991]
<b>NPDD4260</b>	\$254.00	<b>NPDD4260G</b>	\$254.00	42 x 60	38.00 x 56.00 [965 x 1422]
<b>NPDD4842</b>	\$197.00	<b>NPDD4842G</b>	\$197.00	48 x 42	45.00 x 39.00 [1143 x 991]
<b>NPDD4848</b>	\$236.00	<b>NPDD4848G</b>	\$236.00	48 x 48	44.00 x 44.00 [1118 x 1118]
<b>NPDD5442</b>	\$210.00	<b>NPDD5442G</b>	\$210.00	54 x 42	50.00 x 38.00 [1270 x 965]
<b>NPDD6048</b>	\$286.00	<b>NPDD6048G</b>	\$286.00	60 x 48	44.00 x 56.00 [1118 x 1422]
<b>NPDD6060</b>	\$353.00	<b>NPDD6060G</b>	\$353.00	60 x 60	56.00 x 56.00 [1422 x 1422]
<b>NPDD7260</b>	\$420.00	<b>NPDD7260G</b>	\$420.00	72 x 60	56.00 x 68.00 [1422 x 1727]
<b>NPDD7272</b>	\$502.00	—		72 x 72	68.00 x 68.00 [1727 x 1727]

**Notes: Dimensions in inches [millimeters].**  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor mount enclosures may be up to 2 inches [51mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 inches [51 mm] wider than width dimensions listed in this table.

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.