

IDEM WPR and WMR Heavy Duty Non-Contact Magnetic Safety Switches

WPR Series Plastic Housing

WMR Series Stainless Steel Housing




- Robust wide housing suitable for all industry applications
- Can be high-pressure hosed at high temperature - IP69K rated
- Wide 12 mm sensing, high tolerance to misalignment
- High switching capability - up to 2A
- Will operate with most safety relays
- Codes are not unique and can be used with other models of the same series
- Available with 2m or 5m cable or 250mm pigtail with quick-disconnect cable

WMR Series only

- Specifically designed for food processing applications
- Suitable for CIP SIP cleaning - Food Splash Zones per EHEDG guidelines
- 316 Stainless steel mirror polished finish
- Can be high-pressure hosed at high temperature - IP69K rated

See Dimensions later in this section.

Actuator Operating Direction



WPR

WPR/WMR Non-Contact Magnetic Safety Switches					
Part Number	Price	Body Material	Cable Length	Circuits	Contact Type / Rating
Pigtail Versions					
WPR-112005	\$105.00	Plastic	2m	2 NC, 1 NO	Heavy duty / 2A
WPR-112006	\$115.00		5m		
Quick Disconnect Versions (M12 8-pin)					
WPR-112008	\$144.50	Plastic	250mm	2 NC, 1 NO	Heavy duty / 2A
WMR-136008	\$184.50	Stainless Steel	250mm		

Female Quick Disconnect Lead			
Part Number	Price	Description	Exit Type/Cable Length
140101	\$30.00	Female QD Lead	M12 Female 5m, 8-pin
140102	\$37.50		M12 Female 10m, 8-pin




IDEM WPR and WMR Heavy Duty Non-Contact Magnetic Safety Switches

Dimensions


mm [inch]

WPR Series

Pigtail



Quick Disconnect



SEE OUR WEBSITE: WWW.AUTOMATIONDIRECT.COM FOR COMPLETE ENGINEERING DRAWINGS.


IDEM WPR and WMR Heavy Duty Non-Contact Magnetic Safety Switches

Dimensions

mm [inch]

WMR Series

Quick Disconnect




SEE OUR WEBSITE: WWW.AUTOMATIONDIRECT.COM FOR COMPLETE ENGINEERING DRAWINGS.

IDEM Non-Contact Safety Switches Electrical Connections and Dimensions


Electrical Connections

Magnetic Switches




Magnetic Switches - Electrical Connections		
Quick Disconnect Connector Pin Out	Lead Color	Type of Circuit (Actuator Present)
4	Yellow	NO
6	Green	NO
7	Black	NC2
1	White	NC2
2	Red	NC1
3	Blue	NC1

Coded Magnetic and RFID Switches



Coded Magnetic Switches - Electrical Connections			
Quick Disconnect Connector Pin Out	Lead Color	Type of Circuit (Actuator Present)	Output Types (Solid State)
8	Orange	Auxiliary (NO)	200 mA max. 24 VDC
5	Brown	Auxiliary (NO)	
4	Yellow	NC2 +	200 mA max. 24 VDC (Optocoupler)
6	Green	NC2 -	
7	Black	NC1 +	200 mA max. 24 VDC (Optocoupler)
1	White	NC1 -	
2	Red	Supply +24 VDC	Supply 24 VDC +10% / -15%
3	Blue	Supply 0VDC	

Connection Colors



Pin View from Switch

M12 Male

IDEM Non-Contact Safety Switches Specifications

Non-contact Safety Switches Specifications			
	Non-Contact Magnetic Switches	Non-Contact Coded Magnetic Switches	Non-Contact RFID Coded Switches
Safety Classification and Reliability Data			
Switching Reliability (B10d)	3.3 x 10 ⁶ operations at 100 mA load		No mechanical parts implemented
ISO 13849-1	Up to category 4 with safety relay		
ISO 13849-1	Up to PLe depending upon system architecture		
EN 62061	Up to SIL3 depending upon system architecture		
Safety Data - Annual Usage	8 cycles per hour / 24 hours per day / 365 days		
PFHd	2.8 x 10 ⁻¹⁰	2.6 x 10 ⁻¹⁰	4.77 x 10 ⁻¹⁰
Proof Test Interval (Life)	20 Years		
MTTFd	866 Years		1100 years
Agency Approvals	CE, cULus		
Electrical and General Specifications			
Contact Ratings: Safety Contact NC	MPR: Voltage free: 250 VAC, 0.5 A Max.	24 VDC, 0.2A Max. (Optocoupler)	
	LPR, LMR, SPR, SMR, SMR-F: Voltage free: 250 VAC, 1.0A Max. CPR, CMR, CMR-F, WPR: Voltage free: 250 VAC, 2.0A Max.		
Contact Ratings: Monitoring (Auxiliary) Contact NO	Voltage free: 24 VDC, 0.2A Max.		24 VDC, 0.2A Max.
Recommended Fuses (NC Circuits)	MPR: Fuse externally 0.4A (F)	NA	
	LPR, LMR, SPR, SMR, SMR-F, CMR, CMR-F: Fuse externally 0.8A (F)		
	CPR, WPR: Fuse externally 1.6A (F)		
Contact Release Time	<2ms	NA	
Initial Contact Resistance	<500 milliohm	NA	
Minimum Switched Current	10 VDC, 1mA		
Dielectric Withstand	250 VAC		
Insulation Resistance	100 Megohms		
Recommended Setting Gap	5mm		
NC Switching Distance	Sao (assured ON) 8mm close; Sar (assured OFF) 20 mm open		
NO Switching Operation	Opens before NC circuits close		
Tolerance to Misalignment	5mm in any direction from 5mm setting gap (See Misalignment Range drawing on this page)		
Switching Frequency	1.0 Hz Max.		
Approach Speed	200 mm per minute to 1000 mm per second		
Body Material - Polyester	CPR, LPR, MPR, SPR, WPR	CPC, LPC, MPC, SPC, WPC	LPF, SPF
Body Material - 316 Stainless Steel	CMR, CMR-F, LMR, SMR, SMR-F	CMC, CMC-F, LMC, SMC, SMC-F	NA
Operating Temperature Range	Polyester: -25° to +80°C (-13° to +176° F)		
	316 Stainless Steel: -25° to +105° C (-13° to +221° F)		NA
Storage Temperature (Low)	-55° to -40° C (-67° to -40° F)		
Enclosure Protection	IP67, IP69K		
Shock Resistance	IEC 68-2-27 11 ms 30g		
Vibration Resistance	IEC 68-2-6 10-55 Hz 1mm		
Cable Type	PVC, 6.5 mm outside diameter max.		PVC, 6mm outer diameter max.
Mounting Bolts (recommended)	2 x M4; Tightening torque: 1.0 Nm		

Note: Always mount onto non-Ferrous materials.

