

# RSC Series NEMA 1 and 3R Screw Cover Wall-Mount with Knockouts



## Applications

Designed for use as wiring boxes and junction boxes, these enclosures provide protection against rain, sleet and snow in outdoor applications, or against dripping water indoors.

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces
- Unpainted pre-galvanized steel

## Listings

- UL 50, Types 1 and 3 [UL file E23553]
- NEMA/EEMAC 1 and 3R



## Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

## RSC Series NEMA 1 and 3R Screw Cover Wall-Mount with Knockouts

ANSI 61 Gray Light-Textured	Price	Galvanized	Price	Body/Door Steel Gauge	Enclosure Size HxWxD	Knockout Patterns
<b>RSC040404*</b>	—	<b>RSC040404G*</b>	Retired	16/16	4.25 x 4.63 x 4.63 [108 x 118 x 118]	A
<b>RSC040604*</b>	—	<b>RSC040604G</b>	Retired	16/16	6.25 x 4.63 x 4.63 [159 x 118 x 118]	A
<b>RSC060604</b>	—	<b>RSC060604G</b>	Retired	16/16	6.25 x 6.63 x 4.63 [159 x 168 x 118]	A-B-A
<b>RSC060606</b>	—	<b>RSC060606G</b>	Retired	16/16	6.25 x 6.63 x 6.63 [159 x 168 x 168]	A-B-A
<b>RSC060804</b>	—	<b>RSC060804G</b>	Retired	16/16	8.25 x 6.63 x 4.63 [210 x 168 x 118]	A-B-A
<b>RSC060806</b>	—	<b>RSC060806G</b>	Retired	16/16	8.25 x 6.63 x 6.63 [210 x 168 x 168]	A-B-A
<b>RSC080804</b>	—	<b>RSC080804G</b>	Retired	16/16	8.25 x 8.63 x 4.63 [210 x 219 x 118]	A-B-A
<b>RSC080806</b>	—	<b>RSC080806G</b>	Retired	16/16	8.25 x 8.63 x 6.63 [210 x 219 x 168]	A-B-A
<b>RSC081004</b>	—	<b>RSC081004G</b>	Retired	16/16	10.25 x 8.63 x 4.63 [260 x 219 x 118]	A-B-A
<b>RSC081006</b>	—	<b>RSC081006G</b>	Retired	16/16	10.25 x 8.63 x 6.63 [260 x 219 x 168]	A-B-A
<b>RSC081206</b>	—	<b>RSC081206G</b>	Retired	16/16	12.25 x 8.63 x 6.63 [311 x 219 x 168]	A-B-A
<b>RSC101004</b>	—	<b>RSC101004G</b>	Retired	16/16	10.25 x 10.63 x 4.63 [260 x 270 x 118]	B-A-F-F-A
<b>RSC101006</b>	—	<b>RSC101006G</b>	Retired	16/16	10.25 x 10.63 x 6.63 [260 x 270 x 168]	B-A-F-F-A
<b>RSC101204</b>	—	<b>RSC101204G</b>	Retired	16/16	12.19 x 10.63 x 4.63 [310 x 270 x 118]	B-A-F-F-A
<b>RSC101206</b>	—	<b>RSC101206G</b>	Retired	16/16	12.19 x 10.63 x 6.63 [310 x 270 x 168]	B-A-F-F-A
<b>RSC121204</b>	—	<b>RSC121204G</b>	Retired	16/16	12.19 x 12.63 x 4.63 [310 x 321 x 118]	B-A-F-F-A-B
<b>RSC121206</b>	—	<b>RSC121206G</b>	Retired	16/16	12.19 x 12.63 x 6.63 [310 x 321 x 168]	B-A-F-F-A-B
<b>RSC121504</b>	—	<b>RSC121504G</b>	Retired	16/16	15.19 x 12.63 x 4.63 [386 x 321 x 118]	B-A-F-F-A-B
<b>RSC121506</b>	—	<b>RSC121506G</b>	Retired	16/16	15.19 x 12.63 x 6.63 [386 x 321 x 168]	B-A-F-F-A-B
<b>RSC121806</b>	—	<b>RSC121806G</b>	Retired	16/16	18.19 x 12.63 x 6.63 [462 x 321 x 168]	B-A-F-F-A-B
<b>RSC151806</b>	—	<b>RSC151806G</b>	Retired	16/16	18.19 x 15.63 x 6.63 [462 x 397 x 168]	A-B-A-F-F-A-B-A
<b>RSC181804</b>	—	<b>RSC181804G</b>	Retired	16/16	18.19 x 18.63 x 4.63 [462 x 473 x 118]	A-B-A-F-F-A-B-A
<b>RSC181806</b>	—	<b>RSC181806G</b>	Retired	16/16	18.19 x 18.63 x 6.63 [462 x 473 x 168]	A-B-A-F-F-A-B-A
<b>RSC182406</b>	Retired	<b>RSC182406G</b>	Retired	16/16	24.19 x 18.63 x 6.63 [614 x 473 x 168]	A-B-A-F-F-A-B-A
<b>RSC242406</b>	—	<b>RSC242406G</b>	Retired	14/14	24.19 x 24.62 x 6.63 [614 x 625 x 168]	A-B-A-F-F-A-B-A

Notes: Dimensions in inches [millimeters]; letters in table correspond to letters on dimensional drawings.

\*No hasp or meter seal.


Notes: To remove cover, move down, then out. 4x 4 x 4 in [102 x 102 x 102 mm] only has 2 mounting holes centered horizontally. 4x 6 x 4 in [102 x 152 x 102 mm] only has 2 mounting holes centered vertically.

A WGNDKT must be ordered with each RSC enclosure to meet the CSA standard.

# RSC Series NEMA 1 and 3R Screw Cover Wall-Mount



## Dimensions



### NOTES:

- Enclosures with D=8.00" or more do not have an internal flange.

## Grounding Kit

Part Number	Description	Price
<b>WGNDKT</b>	Grounding Kit	—

Note: Field grounding kit includes necessary parts to properly ground enclosure.

Note: A WGNDKT must be ordered with each RSC enclosure to meet the CSA standard.