

# Inline Pressure Gauges and Pressure Indicators

Pneumatic push-to-connect in-line pressure gauges have a technopolymer body and metal gauge casing. They install easily anywhere in a pneumatic circuit and have a range of 0 to 170 psi.



Pressure Gauge



## Features

- Works with flexible pneumatic tubing
- Easily added to existing circuits

Inline Pressure Gauges									
Part No.	Price	Inlet Port	Outlet Port	Max Operating Pressure	Operating Temperature	Weight (lbs)	Brand	Drawing Link	Manufacturer Specifications
<a href="#">9067016</a>	\$22.00	(1) 6mm push-to-connect	(1) 6mm push-to-connect	174 psi	-4 to +140 °F	0.06		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">PGU14</a>	\$24.50	(1) 1/4in push-to-connect	(1) 1/4in push-to-connect			0.10		<a href="#">PDF</a>	N/A
<a href="#">PGU516</a>	\$26.50	(1) 5/16in (8mm) push-to-connect	(1) 5/16in (8mm) push-to-connect			0.10		<a href="#">PDF</a>	
<a href="#">9067032U</a>	\$32.50	(1) 3/8" push-to-connect	(1) 3/8" push-to-connect			0.12		<a href="#">PDF</a>	<a href="#">PDF</a>

Pneumatic push-to-connect inline pressure indicators have a technopolymer body and nickel-plated brass internal parts, with a range of 29 to 145 psi. When pressure is off, the indicator is clear. When pressure is on, a colored indicator appears.

## Features

- Works with flexible pneumatic tubing
- Easily added to existing circuits
- Green or orange indicator buttons



Pressure Indicator



Inline Pressure Indicators										
Part No.	Price	Inlet Port	Outlet Port	Indicator Color	Operating Pressure	Operating Temperature	Weight (lbs)	Brand	Drawing Link	Manufacturer Specifications
<a href="#">9068016</a>	\$15.00	(1) 6mm push-to-connect	(1) 6mm push-to-connect	Orange	29-145 psi	-4 to +140 °F	0.05		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">9068216</a>	\$16.00	(1) 6mm push-to-connect	(1) 6mm push-to-connect	Green	29-145 psi		0.05		<a href="#">PDF</a>	
<a href="#">PMU14A</a>	\$17.00	(1) 1/4in push-to-connect	(1) 1/4in push-to-connect	Orange	29-145 psi		0.10		<a href="#">PDF</a>	N/A
<a href="#">PMU14G</a>	\$17.00	(1) 1/4in push-to-connect	(1) 1/4in push-to-connect	Green	29-145 psi		0.10		<a href="#">PDF</a>	
<a href="#">PMU516A</a>	\$18.00	(1) 5/16in (8mm) push-to-connect	(1) 5/16in (8mm) push-to-connect	Orange	29-145 psi		0.10		<a href="#">PDF</a>	
<a href="#">PMU516G</a>	\$18.00	(1) 5/16in (8mm) push-to-connect	(1) 5/16in (8mm) push-to-connect	Green	29-145 psi		0.10		<a href="#">PDF</a>	



SLV-PU

NITRA SLV Series Pneumatic Pressure Indicator							
Part No.	Price	Description			Weight (lbs)	Brand	Drawing Link
<a href="#">SLV-PU</a>	\$32.00	NITRA pneumatic pop up pressure indicator, 5 psi, 1/8 in male NPT			0.1		N/A

See our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete Engineering drawings.

# Special Purpose Push-to-Connect Pneumatic Fittings



(Fasteners shown not included)

Pneumatic inline fittings are special purpose products mounted inline with pneumatic circuits. With these small, highly efficient components it is possible to perform many pneumatic functions at any point in a circuit.

- Ultra-modular
- Components can be connected in parallel or series
- Push-to-Connect: No tools required!
- Made of lightweight technopolymer
- Stem adapters connect push-to-connect fittings to NPT ports



**Inline Pilot Valves**



**Inline Pressure Regulators**



**Inline Pressure Gauges**



**Inline Mechanical Pressure Switch**



**Inline Pressure Indicators**



**Inline Manual Shutoff Valves**



**Inline Flow Control Valves**



**Inline Quick Exhaust Valves**



**Inline Filter and Elements**



**Stem Adapters**