



Nickel-Plated Brass Push-to-Connect Fittings



Part No. [MBT14-18N-B](#)

NITRA pneumatic push-to-connect male branch tee fittings with rotating nickel-plated brass body, nickel-plated brass threads, stainless steel tube gripping claws and pre-applied Teflon thread sealant (#10-32, M5 and G threads have O-ring instead of thread sealant). For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

| NITRA™ Nickel-Plated Brass Male Branch T | | | | | |
|--|---------------------------------------|---------|---------------------|---------------|-------------|
| Imperial Tube and Threads | | | | | |
| Part No. | Size | Price | Drawing Link | Qty. per pack | Weight (lb) |
| MBT14-18N-B | (2) 1/4in push-to-connect x 1/8in NPT | \$24.00 | PDF | 5 | 0.32 |
| MBT14-14N-B | (2) 1/4in push-to-connect x 1/4in NPT | \$25.50 | PDF | 5 | 0.35 |
| MBT38-14N-B | (2) 3/8in push-to-connect x 1/4in NPT | \$37.50 | PDF | 5 | 0.59 |
| MBT38-38N-B | (2) 3/8in push-to-connect x 3/8in NPT | \$38.50 | PDF | 5 | 0.61 |
| Hybrid Imperial to Metric R Threads (BSPT) | | | | | |
| MBT14-18R-B | (2) 1/4in push-to-connect x R1/8 BSPT | \$24.00 | PDF | 5 | 0.3 |
| MBT14-14R-B | (2) 1/4in push-to-connect x R1/4 BSPT | \$25.50 | PDF | 5 | 0.35 |
| MBT38-14R-B | (2) 3/8in push-to-connect x R1/4 BSPT | \$37.50 | PDF | 5 | 0.56 |
| Hybrid Imperial to Metric G Threads (BSPP) | | | | | |
| MBT14-18G-B | (2) 1/4in push-to-connect x G1/8 BSPP | \$24.00 | PDF | 5 | 0.31 |
| MBT14-14G-B | (2) 1/4in push-to-connect x G1/4 BSPP | \$25.50 | PDF | 5 | 0.37 |
| MBT38-14G-B | (2) 3/8in push-to-connect x G1/4 BSPP | \$37.50 | PDF | 5 | 0.55 |




Nickel-Plated Brass Push-to-Connect Fittings


NITRA nickel-plated brass push-to-connect fittings are an excellent choice for many industrial applications. They have an attractive, easily maintained finish and have a higher pressure and temperature rating when compared to resin fittings.

Features

- Large selection of fitting configurations
- Inch and metric sizes available
- Hybrid Inch to metric conversion fittings available
- NPT, BSPT (R) and BSPP (G) threads available
- Nickel-plated brass bodies, threads and release rings
- Threaded elbow and tee bodies can be rotated after installation
- For use with air and water
- Working pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)



Ideal for washdown and harsh environments



Fitting Cut-away Diagram