Nickel-Plated Brass Push-to-Connect Fittings

Part No. UY532-B

NITRA pneumatic push-to-connect union Y fittings with nickel plated-brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

NITRA™ Nickel-Plated Brass Union Y					
Imperial Tube					
Part No.	*Size*	*Price*	*Drawing Link*	*Qty. per pack*	*Weight (lb)*
UY532-B	(3) 5/32in (4mm) push-to-connect connection(s)	$44.50	PDF	5	0.15
UY14-B	(3) 1/4in push-to-connect connection(s)	$50.00	PDF	5	0.29
UY38-B	(3) 3/8in push-to-connect connection(s)	$77.00	PDF	5	0.63
Metric Tube					
UY6M-B	(3) 6mm push-to-connect connection(s)	$50.00	PDF	5	0.27
UY8M-B	(3) 5/16in (8mm) push-to-connect connection(s)	$58.00	PDF	5	0.38

Part No. PR14-532-B

NITRA pneumatic push-to-connect plug-in reducer fittings with nickel plated brass body and stainless steel tube gripping claws. For use with flexible tubing. Five fittings per package.

- Performs well in harsh duty or washdown applications
- Working Pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)

NITRA™ Nickel-Plated Brass Plug-In Reducer					
Imperial Tube					
Part No.	*Size*	*Price*	*Drawing Link*	*Qty. per pack*	*Weight (lb)*
PR14-532-B	(1) 1/4in plug-in, (1) 5/32in (4mm) push-to-connect	$10.00	PDF	5	0.09
PR38-14-B	(1) 3/8in plug-in, (1) 1/4in push-to-connect	$13.50	PDF	5	0.17
Metric Tube					
PR6M-4M-B	(1) 6mm plug-in, (1) 5/32in (4mm) push-to-connect	$10.00	PDF	5	0.09
PR8M-6M-B	(1) 5/16in (8mm) plug-in, (1) 6mm push-to-connect	$12.50	PDF	5	0.13

Nickel-Plated Brass Push-to-Connect Fittings

NITRA nickel-plated brass push-to-connect fittings are an excellent choice for many industrial applications. They have an attractive, easily maintained finish and have a higher pressure and temperature rating when compared to resin fittings.

Features

- Large selection of fitting configurations
- Inch and metric sizes available
- Hybrid Inch to metric conversion fittings available
- NPT, BSPT (R) and BSPP (G) threads available
- Nickel-plated brass bodies, threads and release rings
- Threaded elbow and tee bodies can be rotated after installation
- For use with air and water
- Working pressure 0 to 300 psi
- Working Temperature 0 to 175°F (-17.8 to 79.4°C)



Ideal for washdown and harsh environments



Fitting Cut-away Diagram