

## Features

- ANSI Z87.1.2010 rated
- 1/2 frame
- Lightweight, shatterproof, polycarbonate lenses
- De-centered cut lens for superior optical quality
- Scratch-resistant coating
- Accessories sold separately



**SG-1524**



**SG-15415**



**SG-1541**

Cobra Safety Eyewear Specifications						
<b>Part Number</b>	<i>SG-1524</i>	<i>SG-1524-12</i>	<i>SG-15415</i>	<i>SG-15415-12</i>	<i>SG-1541</i>	<i>SG-1541-12</i>
<b>Price</b>	<--->	<--->	<--->	<--->	<--->	<--->
<b>Pieces/package</b>	1	12	1	12	1	12
<b>Frame Color</b>	Shiny Black	Shiny Black	Crystal Black	Crystal Black	Crystal Black	Crystal Black
<b>Lens Color</b>	Clear	Clear	Indoor/Outdoor	Indoor/Outdoor	Smoke	Smoke
<b>Lens Features</b>	-	-	-	-	-	-
<b>Material</b>	1/2 frame, TR90 ThermoPlastic					
<b>Frame</b>	Polycarbonate					
<b>Lens</b>	TPR (ThermoPlastic Rubber)					
<b>Nosepiece</b>						
<b>Temple Width</b>	130 mm					
<b>Light Transmission % (True tested values)</b>	91	91	50	50	18	18
<b>UV Blocking Transmission %</b>	99.9					
<b>Agency Approvals</b>	ANSI Z87.1.2010					



**SG-1583**



**SG-15117**



**SG-1528**

Cobra Safety Eyewear Specifications						
<b>Part Number</b>	<i>SG-1583</i>	<i>SG-1583-12</i>	<i>SG-15117</i>	<i>SG-15117-12</i>	<i>SG-1528</i>	<i>SG-1528-12</i>
<b>Price</b>	<--->	<--->	<--->	<--->	<--->	<--->
<b>Pieces/package</b>	1	12	1	12	1	12
<b>Frame Color</b>	Black Crystal and Burnt Orange	Black Crystal and Burnt Orange	Crystal Brown	Crystal Brown	Matte Black	Matte Black
<b>Lens Color</b>	Silver Mirror	Silver Mirror	Brown Flash Mirror	Brown Flash Mirror	Red Mirror	Red Mirror
<b>Lens Features</b>	-	-	HD	HD	-	-
<b>Material</b>	1/2 frame, TR90 ThermoPlastic					
<b>Frame</b>	Polycarbonate					
<b>Lens</b>	TPR (ThermoPlastic Rubber)					
<b>Nosepiece</b>						
<b>Temple Width</b>	130 mm					
<b>Light Transmission % (True tested values)</b>	16	16	20	20	16	16
<b>UV Blocking Transmission %</b>	99.9					
<b>Agency Approvals</b>	ANSI Z87.1.2010					

Company Information

Systems Overview

Programmable Controllers

Field I/O

Software

C-more & other HMI

Drives

Soft Starters

Motors & Gearbox

Steppers/ Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pressure Sensors

Temperature Sensors

Pushbuttons/ Lights

Process

Relays/ Timers

Comm.

Terminal Blocks & Wiring

Power

Circuit Protection

Enclosures

Tools

Pneumatics

Safety

Appendix

Product Index

Part # Index



# Safety Eyewear



## Features

- All Crossfire lenses meet or exceed ANSI Z87+ requirements for safety eyewear.
- All foam-lined frames use closed-cell Ethylene Vinyl Acetate 35 (EVA 35) which is fire-retardant, non-absorbent and resistant to material breakdown from perspiration.
- Select styles feature de-centered cut lenses, resulting in 100% visual accuracy.
- Bayer's Makrolon<sup>®</sup> polycarbonate or Grilamid<sup>®</sup> TR90 materials provide lightweight, stress-resistant and outstanding impact strength to select Crossfire safety glasses.
- Thermoplastic rubber (TPR) provides maximum durability, hypoallergenic non-slip comfort to select nose pieces and temples.
- Panlite<sup>®</sup> L1250VX polycarbonate lenses provide superior optical quality and impact protection while blocking 99.9% of harmful UVA and UVB rays. (Polycarbonate lenses should not be exposed to temperatures in excess of 200°F.)

Frame construction offered in full, ¾, ½ or frameless based on style.

- Full frame indicates the lens is completely supported by the frame.
- ¾ frame indicates a majority of the frame is supporting the lens.
- ½ frame indicates the lens is supported by the top portion of the frame and no lower frame is present.
- Frameless designs have the hinges mounted directly to a solid lens.

## Style Categories

### Standard

- Infinity
- RPG
- Core
- KP6
- ES4
- ES5
- Cobra
- Sniper
- Viper
- Blade
- Mini-Blade

### Foam-lined

- Eclipse
- \* Raptor
- \* Diamondback
- \* Concept
- \* Shield

### Over-the-glass

- OG3

### Readers

- ES5

### Polarized






- Infinity
- RPG
- Core
- ES4
- ES5
- Sniper

### Accessories

- Microfiber storage bag
- Black cloth zipper pouch
- Adjustable string cord (length: 14 inches)
- 3/16" adjustable woven cord (length: 15.5 inches)

## LENS SELECTION GUIDE

### TRANSMISSION (Typical)

	Smoke: The perfect all-around tint for normal outdoor conditions.	18% of light passes through
	Colored Mirror: The mirrored surface over a smoke base lens diminishes glare by absorbing reflection across the mirror surface. Good for bright outdoor conditions.	16% of light passes through
	Silver Mirror: Similar to a smoke lens, but has the added mirror coating which filters more light, further reducing the glare. Ideal for bright outdoor conditions.	16% of light passes through
	HD Brown: Filters blue light which can cause eye fatigue and a haze effect. Use in normal to bright outdoor conditions.	22% of light passes through
	Indoor/Outdoor: Offers protection from the glare of bright artificial lighting and sunlight. Great for indoor and outdoor use.	50% of light passes through
	Clear: Allows maximum light transmission without changing or distorting sight or colors. Suitable for indoor or low light conditions.	91% of light passes through
	Yellow: Enhances available light. Appropriate for low light conditions in both indoor and outdoor environments.	80% of light passes through
	Orange: Enhances available light. Made for low light conditions in both indoor and outdoor environments.	80% of light passes through
	Ice Blue lens: Counteracts the effects of yellow light which cause glare and eye stress. Used in high yellow light conditions (fluorescent lighting).	80% of light passes through
	Polarized: Filters bent light caused by reflection, reducing glare and eye fatigue. Suitable for sunny outdoor conditions.	18% of light passes through
	HD Copper: Enhances available light. Made for low light conditions in both indoor and outdoor environments.	25% of light passes through
	HD Green: Filters blue light which can cause eye fatigue and a haze effect. Use in normal to bright outdoor conditions.	20% of light passes through



# Safety Eyewear Accessories



**SG-CR1**



**SG-CR3**



**SG-G3**



**SG-G4**

Safety Eyewear Accessories				
Part Number	SG-CR1	SG-CR3	SG-G3	SG-G4
Price	<--->	<--->	<--->	<--->
Pieces/package	1	1	1	1
Description	Black microfiber storage bag	Black cloth zipper pouch with hook and bell loop	Adjustable string cord with loop ends Length: 14 inches	3/16" adjustable woven cord with slip-on woven ends Length: 15.5 inches