

Industrial Gloves




TTP452-8

TTP455-10

Puncture and cut-resistant industrial work gloves

- High level of puncture resistance
- Full palm and inside finger protection
- Cut-resistant with highest rating of puncture resistance
- Good dexterity



Full palm and inside finger protection

Puncture and Cut-resistant Palm Protection Industrial Gloves Specifications			
Part Number	TTP452-8	TTP452-9	TTP452-10
Price			
Pairs/package	1	1	1
Size	8 (M)	9 (L)	10 (XL)
Glove Color	Green with black palm		
Cuff Color	None	None	None
Material			
Glove	Tilsatec Rhino steel core cut-resistant knit		
Coating	Nylon-Polyester outer coating. RhinoGuard palm		
Gauge	13		
Cut Resistance			
Cut Test	ANSI cut level 4 based on 2706g CPPT ASTM test, EN388, cut level 5.		
Puncture Resistance			
Test Compliance	ANSI level 5 EN 388 level 4. ASTM F1342-05 Test: 150N for 4.5 mm probe 86N for 2.03 mm probe. 4.1N for 25 gauge sharpened medical grade needle		

Puncture and Cut-resistant Palm and Knuckle Protection Industrial Gloves Specifications			
Part Number	TTP455-8	TTP455-9	TTP455-10
Price			
Pairs/package	1	1	1
Size	8 (M)	9 (L)	10 (XL)
Glove Color	Green with black palm		
Cuff Color	None	None	None
Material			
Glove	Tilsatec Rhino steel core cut-resistant knit		
Coating	Flexible molded rubber knuckles. RhinoGuard palm		
Gauge	13		
Cut Resistance			
Cut Test	ANSI cut level 4 based on 2706g CPPT ASTM test, EN388, cut level 5.		
Puncture Resistant			
Test Compliance	ANSI level 5 EN 388 level 4. ASTM F1342-05 Test: 150N for 4.5 mm probe 86N for 2.03mm probe. 4.1N for 25 gauge sharpened medical grade needle		

Company
Information

Terminal Blocks

Power
Distribution
BlocksWiring
AccessoriesZIPLink
Connection
SystemMulti-wire
ConnectorsSensor Cables
and ConnectorsM12 Junction
BlocksPanel Interface
Connectors

Wiring Duct

Cable Ties

Wire

Bulk
Multi-conductor
CablesWire
Management
Products

Power Supplies

DC Converters

Transformers
and Filters

Circuit Protection

Tools

Test
Equipment

Enclosures

Enclosure
Climate ControlSafety: Electrical
ComponentsSafety: Protective
WearTerms and
Conditions

Industrial Gloves



Industrial Work Gloves Selection

- General purpose
- Anti-static, pre-washed
- Puncture and cut resistant
- Puncture resistant with knuckle padding
- Cut-resistant, polyurethane-coated or rubber-coated
- Arc flash-rated, cut resistant, full leather
- Mechanic style, cowhide leather palm
- Cut resistant sleeves

Sizing Chart					
6	7	8	9	10	11
X-Small	Small	Medium	Large	X-Large	2X-Large



Measure around your hand across the widest part of your palm.

The reading in inches is an estimate of the equivalent glove size. If your reading is between sizes, order the larger size.

Company Information

Terminal Blocks

Power Distribution Blocks

Wiring Accessories

ZIPLink Connection System

Multi-wire Connectors

Sensor Cables and Connectors

M12 Junction Blocks

Panel Interface Connectors

Wiring Duct

Cable Ties

Wire

Bulk Multi-conductor Cables

Wire Management Products

Power Supplies

DC Converters

Transformers and Filters

Circuit Protection

Tools

Test Equipment

Enclosures

Enclosure Climate Control

Safety: Electrical Components

Safety: Protective Wear

Terms and Conditions